

## MASTERVLELEDBulb D5.9-60W E27 927A60FR G UK MASTER Value GLASS LED bulbs

Featuring a classic heritage design, classic filament LED lamps combine the familiar shapes of incandescent bulbs with the benefits of the long-lasting LED technology. The product offers more energy saving compared with normal LED bulbs, and also provides the customer with a good light experience and superior dimming performance. MASTER Value Glass Led Bulbs deliver significant energy savings, offering 30% more compared to normal LEDs. They provide excellent quality of light. By offering a lifetime of 15,000 hours, they reduce maintenance costs



## Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process, we innovate to reduce our environmental impact by taking climate action and by focusing on circularity and bring wider benefits to the world we operate in via social aspects as food availability, health & wellbeing, and safety & security.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



- Dimmable: Yes
- Energy Efficiency Class: D
- Luminous efficacy (rated) (nom.): 136.00 lm/W
- Power (Rated) (Nom): 5.9 W



• Nominal lifetime (nom.): 15000 h



- SAP Weight Paper Unit (Case): 0.430 kg
- SAP Weight Paper Unit (Piece): 0.022 kg



• EU RoHS compliant: Yes



Weight & Materials

• SAP net weight (piece): 0.030 kg

Energy efficiency ranking / External awards



Further reading at: https://www.philips.com/a-w/about/ sustainability/sustainable-planet/greenproducts-and-green-innovation.html

© 2021 Signify Holding. All rights reserved.