



Classic filament LEDbulbs

LED CLA 40W A60 E27 3000K CL EELA SRT AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information			
Cap-Base	E27	Power Consumption	2.3 W
Nominal lifetime	50,000 hour(s)	Lamp Current (Nom)	30 mA
Switching Cycle	50,000	Wattage Equivalent	40 W
Rated Lifetime (Hours)	50,000 hour(s)	Starting Time (Nom)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	Ambient temperature range	-20 to +45 °C
Color Code	830 [CCT of 3000K]	T-Case Maximum (Nom)	35 °C
Luminous Flux	485 lm	Controls and Dimming	
Color Designation	White (WH)	Dimmable	No
Correlated Color Temperature (Nom)	3000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	210 lm/W	Bulb Finish	Clear
Color Consistency	<6	Bulb Material	Glass
Color rendering index (CRI)	80	Bulb Shape	A60
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
Photobiological safety according to EN 62471	RG1	Energy Consumption kWh/1000 h	- kWh
Operating and Electrical			
Input Frequency	50 to 60 Hz		

Classic filament LEDbulbs

EyeComfort	Yes
Product Data	
Order product name	LED CLA 40W A60 E27 3000K CL EELA SRT AU
Full product name	LED CLA 40W A60 E27 3000K CL EELA SRT AU
Full product code	871951445493400



Order code	929003066419
Material Nr. (12NC)	929003066419
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514454934
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514454941

Dimensional drawing




Product	D	C
LED CLA 40W A60 E27 3000K CL EELA SRT AU	60 mm	105 mm

Photometric data



Light Distribution Diagram - LED CLA 40W A60 E27 3000K CL EELA SRT AU


General uniform lighting - LED CLA 40W A60 E27 3000K CL EELA SRT AU




Spectral Power Distribution Colour - LED CLA 40W A60 E27 3000K CL EELA SRT AU

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LED CLA 40W A60 E27 3000K CL EELA SRT AU



Lumen Maintenance Diagram - LED CLA 40W A60 E27 3000K CL EELA SRT AU

