



Classic filament LEDbulbs

8A19/PER/UD/FR/G/E26/WGD 4/2PFT20

Philips LED vintage-style lamps allow you to maintain a warm, classic light effect while providing longer life and energy savings.

Product data

General Information		Power Consumption	
Cap-Base	E26 [Single Contact Medium Screw]	Lamp Current (Nom)	85 mA
Nominal lifetime	15,000 hour(s)	Wattage Equivalent	60 W
Switching Cycle	20,000	Starting Time (Nom)	0.5 s
Rated Lifetime (Hours)	15,000 hour(s)	Warm-up time to 60% light	0.4 s
Lighting Technology	LED	Power Factor (Fraction)	0.7
EU RoHS compliant	Yes	Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	922-927 [CCT of 2200K-2700K]	Ambient temperature range	-4 to +104 °F
Color Code	922-927 [CCT of 2200K-2700K]	Controls and Dimming	
Beam Angle (Nom)	300 degree(s)	Dimmable	Only with specific dimmers
Luminous Flux	800 lm	Mechanical and Housing	
Color Designation	Warm Glow(WG)	Bulb Finish	Frosted
Correlated Color Temperature (Nom)	2200 2700 K	Bulb Material	Glass
Luminous Efficacy (rated) (Nom)	100 lm/W	Bulb Shape	A19
Color Consistency	<4	UL Wet/ damp/ dry location	Wet location
Color rendering index (CRI)	95	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Certifications	Energy Star
Operating and Electrical			
Input Frequency	60 Hz		

Classic filament LEDbulbs

EyeComfort	Yes
T20 compliant	Yes

Application Conditions


can it be used in closed luminaires	Yes
-------------------------------------	-----

Product Data

Order product name	8A19/PER/UD/FR/G/E26/WGD 4/2PFT20
Full product name	8A19/PER/UD/FR/G/E26/WGD 4/2PFT20



Order code	573436
Material Nr. (12NC)	929003083203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677573430
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677573435

Dimensional drawing



Product	D	C
8A19/PER/UD/FR/G/E26/WGD 4/2PFT20	2-3/8 inch	4-3/16 inch

Photometric data




General uniform lighting - 8A19/PER/UD/FR/G/E26/WGD 4/2PFT20

**Spectral Power Distribution Colour - 8A19/PER/UD/FR/G/E26/WGD
4/2PFT20**


Classic filament LEDbulbs

Photometric data




Light Distribution Diagram - 8A19/PER/UD/FR/G/E26/WGD 4/2PFT20

Lifetime



Life Expectancy Diagram - 8A19/PER/UD/FR/G/E26/WGD 4/2PFT20



Lumen Maintenance Diagram - 8A19/PER/UD/FR/G/E26/WGD 4/2PFT20

