



Classic filament LEDbulbs

LED CLA 60W A60 B22 3000K CL EELA SRT AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


| | | | |
|--|--------------------|---------------------------------|---------------|
| General Information | | Power Consumption | |
| Cap-Base | B22 | | 4 W |
| Nominal lifetime | 50,000 hour(s) | Lamp Current (Nom) | 45 mA |
| Switching Cycle | 50,000 | Wattage Equivalent | 60 W |
| Rated Lifetime (Hours) | 50,000 hour(s) | Starting Time (Nom) | 0.5 s |
| Lighting Technology | LED | Warm-up time to 60% light | 0.5 s |
| EU RoHS compliant | Yes | Power Factor (Fraction) | 0.4 |
| Light Technical | | Voltage (Nom) | 220-240 V |
| Color Code | 830 [CCT of 3000K] | Temperature | |
| Color Code | 830 [CCT of 3000K] | Ambient temperature range | -20 to +45 °C |
| Luminous Flux | 840 lm | T-Case Maximum (Nom) | 35 °C |
| Color Designation | White (WH) | Controls and Dimming | |
| Correlated Color Temperature (Nom) | 3000 K | Dimmable | No |
| Luminous Efficacy (rated) (Nom) | 210 lm/W | Mechanical and Housing | |
| Color Consistency | <6 | Bulb Finish | Clear |
| Color rendering index (CRI) | 80 | Bulb Material | Glass |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % | Bulb Shape | A60 |
| Photobiological safety according to EN 62471 | RG1 | Approval and Application | |
| Operating and Electrical | | Energy Consumption kWh/1000 h | - kWh |
| Input Frequency | 50 to 60 Hz | | |

Classic filament LEDbulbs

| | |
|--------------------|--|
| EyeComfort | Yes |
| Product Data | |
| Order product name | LED CLA 60W A60 B22 3000K CL EELA SRT AU |
| Full product name | LED CLA 60W A60 B22 3000K CL EELA SRT AU |
| Full product code | 871951445826000 |


| | |
|---------------------------------|---------------|
| Order code | 929003539919 |
| Material Nr. (12NC) | 929003539919 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8719514458260 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 8719514458277 |

Dimensional drawing




| Product | D | C |
|--|-------|--------|
| LED CLA 60W A60 B22 3000K CL EELA SRT AU | 60 mm | 105 mm |


Photometric data



General uniform lighting - LED CLA 60W A60 B22 3000K CL EELA SRT AU




Spectral Power Distribution Colour - LED CLA 60W A60 B22 3000K CL EELA SRT AU




Light Distribution Diagram - LED CLA 60W A60 B22 3000K CL EELA SRT AU

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LED CLA 60W A60 B22 3000K CL EELA SRT AU



Lumen Maintenance Diagram - LED CLA 60W A60 B22 3000K CL EELA SRT AU

