



MyCare LED 圆形

LED MOD 20W G3 865

MyCare LED 吸顶灯模块将 LED 光源集成到一个模块中，专为替代采用 G10q 灯头的圆形荧光灯管而设计。该模块节能效果出众，使用寿命长久。

产品数据


一般信息	
底盖	-
标称使用寿命	20,000 小时
切换循环	15,000
照明技术	LED
符合欧盟 RoHS 规范	是
灯技术	
颜色代码	865 [CCT of 6500K]
光束角度 (标称)	150 °
光通量	1,900 lm
颜色名称	冷日光
相关色温 (标称)	6500 K
光效 (额定) (标称)	95 lm/W
颜色一致性	<6
显色指数 (CRI)	83
标称使用寿命结束时灯的光通维持率 (标称)	70 %
光生物学安全性符合 EN 62471	RG1
操作和电气	
输入频率	50 至 60 Hz
功耗	20 W
灯具电流 (标称)	140 mA
瓦数相当	32 W
启动时间 (标称)	0.5 s

60% 灯光下的预热时间	0.5 s
功率系数 (小数)	0.5
电压 (标称)	220-240 V
镇流器兼容性	电源
温度	
环境温度范围	-20 至 +45°C
最大外壳温度 (标称)	85 °C
控制和调光	
可调光	否
机械和外壳	
灯泡外观	磨砂
灯泡材料	塑料
产品长度	200 mm
灯泡外形	其他
审批和申请	
节能产品	是
批准标志	遵从 RoHS
EyeComfort	是
LED 创新	EyeComfort

产品数据	
订单产品名称	LED MOD 20W G3 865
完整的产品名称	LED MOD 20W G3 865
完整产品代码	694197061198500
订购代码	929003765809
材料编号 (12NC)	929003765809


计算器 - 每包数量	1
EAN/UPC - 产品/箱	6941970611985
计算器 - 每个外包装箱中的包数	40
EAN/UPC - 案例	6941970611992

二维绘图




Product	D1	D2	A1	A2	A3
LED MOD 20W G3 865	139 mm	139 mm	18 mm	126 mm	139 mm


光度数据



Light Distribution Diagram - LED MOD 20W G3 865




Spectral Power Distribution Colour - LED MOD 20W G3 865




General uniform lighting - LED MOD 20W G3 865



寿命



Life Expectancy Diagram - LED MOD 20W G3 865




Lumen Maintenance Diagram - LED MOD 20W G3 865



Life Expectancy Diagram - LED MOD 20W G3 865

Lumen Maintenance Diagram - LED MOD 20W G3 865



Life Expectancy Diagram - LED MOD 20W G3 865

