



Developed to bring a considerable presence that unites the styles of days gone by with advanced optical control. Luminaires that fit-in everywhere. The Lumece **Harmonia** pendant luminaire was designed to stand harmoniously in any setting or designed space. Their presence ads an essence of the past while the high-end technology inside provides optimal photometric performance and long life.

Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Ordering guide sample

Luminaire	Lamp	Optical System	Voltage	Options	Mounting & Configuration	Pole*	Finish**
Z65B	175 MH	3	120	HS	M20A-1A	SSM8-24	GNTX

\* Consult the eCatalog for details and the complete line of poles.


The specially formulated Lumital powder coat finish is available in a range of many standard colors.

\*\* Consult Lumece's Color Chart for complete specifications.

### Luminaires

Conform to the UL 1598 and CSA C22.2 No. 250.0-08 standards.


Z65B-CDA



**Weight:** 28 lbs (12.7 kg)

**EPA:** 2.40 sq. ft.


Z65F



**Weight:** 38 lbs (17.2 kg)

**EPA:** 2.47 sq. ft.

Z60A



**Weight:** 32 lbs (14.5 kg)

**EPA:** 2.55 sq. ft.

# Z65B-Z65F-Z60A Harmonia

## Pendant

### Lamp/HID

Wattage	2 / 3 / 5
50 MH, medium	■
70 MH, medium	■
100 MH, medium	■
150 MH, medium	■
35 HPS, medium	■
50 HPS, mogul	■
70 HPS, mogul	■
100 HPS, mogul	■
150 HPS, mogul	■

■ Available.

### Optical System / HID

(Lamps not included)



#### Optics

Large round acrylic or polycarbonate refractor featuring two series of prisms controlling the lamp's horizontal and vertical luminous flux.

2 Asymmetrical

3 Asymmetrical

5 Symmetrical

> House shield available in option (HS)

### Voltage / HID

HID <sup>1</sup>
120
208
240
277
347
480

1. Multi-top ballast also available.

### Lamp/QL

Wattage	2 / 5
55 QL	■
85 QL	■

■ Available.

High frequency generator for induction lamp (4000K). Instant start. Operating range 50-60 Hz or DC. Lamp minimum starting temperature -40F (-40 °C).

### Optical System / QL

(Lamps not included)



#### SHA optics

Large round acrylic or polycarbonate refractor featuring two series of prisms controlling the lamp's horizontal and vertical luminous flux.

2 Asymmetrical

5 Symmetrical

> House shield available in option (HS)

### Voltage / QL

QL
120
208
240
277
347
480

### Options


**HS** House shield

**PH7** Button-type photoelectric cell


**CDA** Copper decorative accents (only with Z65B and Z65F)

### Mountings


Consult the eCatalog for details and the complete line of mountings.




M20A



M20H



M20G




M20M

### Poles and Pole Options

Consult the eCatalog for details and the complete line of poles.




APR4-LBC1



RS805



AM8



RA54

# Z65B-Z65F-Z60A Harmonia

## Pendant

### Assembly examples

