



Exemplifies Lumec's ability to blend engineering know-how and old-time charm. Nothing has been left to chance in the design of the Lumec **Hexagonal Lantern**. These luminaires are able to fill a space with a warm and reassuring light. Behind the antique-inspired look, the **Hexagonal Lantern** luminaire reminds us that the past and the present are eternally linked and when combined together in a luminaire, they offer exceptional style.

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering guide sample

Luminaire	Lamp	Optical System	Voltage	Options	Mounting & Configuration	Pole*	Finish**
L24-GLC	100 HPS	RR5	120	CPTC	CRC-2	CRC-2	GNTX

* Consult the eCatalog for details and the complete line of poles.


The specially formulated Lumital powder coat finish is available in a range of many standard colors.

** Consult Lumec's Color Chart for complete specifications.

Luminaires

Conform to the UL 1598 and CSA C22.2 No. 250.0-08 standards.


L24-RR



Weight: 37 lbs (16.8 kg)

EPA: 3.17 sq.ft


L28-SE-SF28



Weight: 54 lbs (24.5 kg)

EPA: 2.90 sq.ft


L60-SG-SF60



Weight: 40 lbs (18.1 kg)

EPA: 2.95 sq.ft


L61-RR-SF61



Weight: 49 lbs (22.2 kg)

EPA: 2.95 sq.ft

L60S-SR-SF60S



Weight: 34 lbs (15.4 kg)

EPA: 2.30 sq.ft

These lanterns are available with the following lens finishes

- PC-C** Clear polycarbonate
- PC-O** Opal polycarbonate
- PC-FC** Frosted clear polycarbonate
- GL-C** Clear tempered glass
- GLBG-C** Clear beveled tempered glass

L24-L28-L60-L61-L60S Hexagonal Lantern

Post Top

Lamp/HID

Wattage	L24			L28/L61			L60		
	RACE	RR	SE	RACE	RR	SE	RACE	RR	SE
50 MH, medium	RB	■	RB	■	■	■	■	■	■
70 MH, medium	RB	■	RB	■	■	■	■	■	■
100 MH, medium	RB	■	RB	■	■	■	■	■	■
150 MH, medium	RB	■	RB	■	■	■	■	■	■
250 MH, mogul	RB	RB	RB	RB	RB	RB	RB	RB	RB
250 PSMH, mogul ¹	RB	RB	RB	RB	RB	RB	RB	RB	RB
35 HPS, mogul	RB	■	RB	■	■	■	■	■	■
50 HPS, mogul	RB	■	RB	■	■	■	■	■	■
70 HPS, mogul	RB	■	RB	■	■	■	■	■	■
100 HPS, mogul	RB	■	RB	■	■	■	■	■	■
150 HPS, mogul	RB	■	RB	■	■	■	■	■	■
200 HPS, mogul ¹	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	RB ²
250 HPS, mogul ¹	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	RB ²

■ Available. N/A: Not available. RB: Remote Ballast Required. 1. N/A with a PC globe. 2. N/A with SGFM. 3. Remote Ballast with Glow top.

Wattage	L60S	
	RACE	RR
50 MH, medium	RB	■
70 MH, medium	RB	■
100 MH, medium	RB	■
150 MH, medium	RB	■
35 HPS, medium	RB	■
50 HPS, medium	RB	■
70 HPS, medium	RB	■
100 HPS, medium	RB	■
150 HPS, medium	RB	■

■ Available. RB: Remote Ballast Required.

Optical System / HID

(Lamps not included)




RR Optics

(not available in L60S)

Round borosilicate refractor

- RR5** Symmetrical
- RR3** Asymmetrical
- RR3MD** Asymmetrical with medium deflector



SE Optics

Hydro-formed cut-off reflector system set in faceted arc-image duplicating patterns

- SE5** Symmetrical
 - SE3** Asymmetrical
- > House shield available in option (HS)



RACE Optics

(not available in L60S)

Round acrylic (max. 100W) or borosilicate (150W and more) refractor with segmented upright recovery dome

- RACE5** Symmetrical
- RACE3** Asymmetrical
- RACE3D** Asymmetrical with deflector



SR Optics

(L60S only)

Small round borosilicate refractor

- SR5** Symmetrical
- SR5D** Symmetrical with deflector



SG Optics

(L60S only)

Segmented cut-off reflector system set in faceted arc-image duplicating patterns

- SGQ** Symmetrical
 - SG1** Symmetrical
 - SG2** Asymmetrical
 - SG3** Asymmetrical
 - SGFM** Forward throw
- > House shield available for SG2 and SG3

Voltage / HID

HID ¹
120
208
240
277
347
480

1. Multi-top ballast also available.

Options


- FN** Decorative finial (see to the right)
- FNC** Copper-color painted finial
- CPTC** Varnished copper cupola
- AL** Cupola painted the same color as the luminaire
- GT** Glow top (Available with L60 and RR or SG optical system only)
- HS** House shield (for SE and SG only)

L24-L28-L60-L61-L60S Hexagonal Lantern


Post Top

Mountings


Consult the eCatalog for details and the complete line of mountings.




CRA



CRD



CRC




CRF

Finials




FN1



FN5



FN2



FN6




FN3




FN8

Poles and Pole Options


Consult the eCatalog for details and the complete line of poles.




APR4




APR4-LBC3



RA61



RTA400



RTAF800

L24-L28-L60-L61-L60S Hexagonal Lantern

Post Top

Assembly examples

