



Combining state-of-the-art photometric performance and outstanding ease of maintenance, the Optima is designed to last. The **Optima** is the perfect choice for landscaped projects that compel that extra little bit of detail. This beautiful luminaire is made from top-quality materials, is easy to maintain, and adds a distinctive decorative aspect to any contemporary environment.

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering guide sample

Luminaire	Lamp	Optical System	Voltage	Options	Mounting & Configuration	Pole*	Finish**
OT10	100 HPS	SHA3M-ACDR	240	HS	CR-1A	R80F-12	GN8TX

* Consult the eCatalog for details and the complete line of poles.


The specially formulated Lumital powder coat finish is available in a range of many standard colors.

** Consult LumeC's Color Chart for complete specifications.

Luminaires


Conform to the UL 1598 and CSA C22.2 No. 250.0-08 standards.

OT10-SHA




Weight: 28 lbs (12.7 kg)
EPA: 1.74 sq. ft.

OT20-SCB



Weight: 47 lbs (21.3 kg)
EPA: 1.42 sq. ft.

XL10-SHA



Weight: 40 lbs (18.1 kg)
EPA: 1.91 sq. ft.

OT10-OT20-XL10 Optima

Post Top

Lamp/HID

Wattage	SCB3M SHA3M-PC SSA3M-PC	SHA3M-ACDR SA3M-ACDR
50 MH, medium	■	■
70 MH, medium	■	■
100 MH, medium	■	■
150 MH, medium	■	■
200 MH, mogul	■	N/A
175 PSMH, mogul	■	■
250 PSMH, mogul	■	N/A
35 HPS, medium	N/A	■
50 HPS, mogul	■	■
70 HPS, mogul	■	■
100 HPS, mogul	■	■
150 HPS, mogul	■	■
200 HPS, mogul	■	N/A
250 HPS, mogul	■	N/A

■ Available. N/A : Not available.

Optical System / HID

(Lamps not included)



SHA and SSA optics
Sealed optical chamber consisting of a reflector permanently assembled on top of an internal prismatic globe.

SHA3M Asymmetrical

SSA3M Asymmetrical

> House shield available in option (HS)

In the above optics, the sleeve and shutter permit exact positioning of the lamp.
SHA & SSA refractors available in: **ACDR**: Acrylique (175 W max.), **PC**: Polycarbonate.
Add suffix to optical system code.



SCB optics
Sealed optical chamber consisting of a reflector permanently assembled on top of a tempered-glass sapphire lens.

SCB3M Asymmetrical

> House shield available in option (HS)

In the above optics, the sleeve and shutter permit exact positioning of the lamp.

Voltage/HID

HID ¹
120
208
240
277
347
480


1. Multi-top ballast also available.

Options


- DF** Decorative cupola (DF10 with OT10 and DF20 with OT20)
- DA** Decorative arches
- DC** Decorative caps
- HS** House shield
- PH8** Photoelectric cell (Appropriate decorative cupola DF10 (OT10) and DF20 (OT20) required)

Mountings

Consult the eCatalog for details and the complete line of mountings.




CRC



CR




JR



M30

Poles and Pole Options

Consult the eCatalog for details and the complete line of poles.



RS61

RS856

R92

OT10-OT20-XL10 Optima

Post Top

Assembly examples

