

PHILIPS

Compatibility List Professional Q3 2026

TrueForce LED HID

Table of contents

TrueForce LED HPI - Universal	2
MASTER LED SON-T - InstantFit	3 - 4
MASTER LED SON - T - EM/Mains Voltage	5
MASTER LED SON-T Ultra Efficient - Mains	6
TrueForce Core LED SON-T - Mains Voltage	7
TrueForce LED HPL - EM/Mains	8
MASTER LED HPL - Mains	9
TrueForce CorePro LED HPL - Mains Voltage	10

Q3 2026

TrueForce LED HPI - Universal

9290023507	TForce LED HPI UN 95W E40 840 NB
9290023508	TForce LED HPI UN 95W E40 840 WB
9290023509	TForce LED HPI UN 140W E40 840 NB
9290023510	TForce LED HPI UN 140W E40 840 WB



Ballast - Igniter compatibility list

Key

	Compatible.
	Limited compatibility
	Not Compatible
N.A.	Combination not applicable

This document is for information purposes and must be treated as recommendation. Signify attempts to provide accurate result which are generated in lab conditions and might not completely reflect actual conditions.

The product is compatible with BHL/BSN ballasts, see above table.
The product is NOT compatible with electronic ballasts
The product is NOT compatible with CWA type of ballasts/transformers

BSN-series ballast type (or similar) combined with following igniter

Brand	Type	art.nr	mode	TForce LED HPI UN 95-250W Model Number/(Short) EOC code 9290023507/871869975367200 9290023508/871869975369600	TForce LED HPI UN 140-400W Model Number/(Short) EOC code 9290023509/871869975371900 9290023510/871869975373300
Without igniter	n.a.	n.a.	n.a.		
Philips	SN58	9136195799 9137001349 9137001348 9137100105 9136195199	semi-parallel		
	SKD578	9137006553 9137006554	semi-parallel		
Vossloh Schwabe	Z250s	140425	series		
	Z400s	140427	series		
	Z400MK	142897	series		
	PZI1000/1K	140617	parallel		
Tridonic	ZRM-2.5-ES/CT	87500086	series		
BAG	NI 400 LE 4K	10007322	series		
	NP603	10067389	parallel		
PARMAR	PAE40 0255	PAE400255	series		
	PXE07 0255		series		
ELT	AVS 400-D	3210232	series		
	AVS100-DP	3210442	semi-parallel		
Electrostart	ZX400-T	78.02.400.0-T	series		
Magnetek (May & Christe)	ZG4.5		series		

BSN-series ballast type (or similar) combined with following igniter

Brand	Type	art.nr	mode	TForce LED HPI UN 95-250W Model Number/(Short) EOC code 9290023507/871869975367200 9290023508/871869975369600	TForce LED HPI UN 140-400W Model Number/(Short) EOC code 9290023509/871869975371900 9290023510/871869975373300
Without igniter	n.a.	n.a.	n.a.		
Philips	SI51	9136195199	parallel		
Vossloh Schwabe	Z250s	140425	series		
	Z400s	140427	series		
	Z400MK	142897	series		
	PZI1000/1K	140617	parallel		
Tridonic	ZRM-2.5-ES/CT	87500086	series		
BAG	NI 400 LE 4K	10007322	series		
	NP603	10067389	parallel		
PARMAR	PAE400 255	PAE400255	series		
	PXE07 0255		series		
ELT	AVS 400-D	3210232	series		
Electrostart	ZX400-T	78.02.400.0-T	series		
Magnetek (May & Christe)	ZG4.5		series		

Note

- For enabling compatibility, the "Igniter comfort logic" function is equipped to simulate the low light level at start up of HID lamps, which in some cases can be observed as a short reduction of the light output of the lamp.
- In rare cases the igniter comfort logic cannot stop the igniter. This is visible as continuously flicker of the light. Signify advises to remove/disconnect the igniter.
- Instant ON/OFF – does not require to warm up or to cool down before restart.
- The compatibility of the lamp with the gear is measured in the laboratory at nominal voltage (230VAC). The performance in real applications can be different.
- Manufacturers of ballasts and igniters can change the technical design of their product without informing LED lamp suppliers. These changes can influence the performance of LED products. Signify cannot be held responsible for inaccuracies in the compatibility lists due to technical changes in ballasts or igniters.

Disclaimer:
Philips will not accept claims for any damage caused by implementing the recommendations in this document. More information:

TrueForce LED Industrial and Retail (Highbay – MH) | 6871562 | Philips lighting

Installer Hub | Philips lighting

Q3 2026

MASTER LED SON-T - InstantFit

9290034670	MAS LED SON-T IF 3.6Klm 23W 727 E27	
9290034671	MAS LED SON-T IF 4Klm 23W 740 E27	
9290034672	MAS LED SON-T IF 5.4Klm 34W 727 E27	
9290034673	MAS LED SON-T IF 6Klm 34W 740 E27	
9290034674	MAS LED SON-T IF 8.1Klm 50W 727 E40	
9290034675	MAS LED SON-T IF 9Klm 50W 740 E40	
9290034676	MAS LED SON-T IF 10.8Klm 65W 727 E40	
9290034677	MAS LED SON-T IF 12Klm 65W 740 E40	

Ballast - Igniter compatibility list

Key

	Compatible.
	Limited compatibility
	Not Compatible
N.A.	Combination not applicable

This document is for information purposes and must be treated as recommendation. Signify attempts to provide accurate result which are generated in lab conditions and might not completely reflect actual conditions.

EM ballast type	EM ballast Brand	MAS LED SON-T IF 3.6Klm 23W E27 Model Number/(Short) EOC wcode 9290034670/871951444887200 9290034671/871951444889600	MAS LED SON-T IF 5.4Klm 34W E27 Model Number/(Short) EOC wcode 9290034672/871951444891900 9290034673/871951444893300	MAS LED SON-T IF 8.1Klm 50W E40 Model Number/(Short) EOC wcode 9290034674/871951444895700 9290034675/871951444897100	MAS LED SON-T IF 10.8Klm 65W E40 Model Number/(Short) EOC wcode 9290034676/871951444899500 9290034677/871951444901500
BSN 50W	PHILIPS				
BSN 70W	PHILIPS				
BHL 80W	PHILIPS				
BHL 125W	PHILIPS				
BSN 100W	PHILIPS				
BSN 150W	PHILIPS				
NK70/50LUP	Helvar				
NG70ZT	OSRAM				
VS PKNaHJ 70.128	Vossloh Schwabe				
70W 1.0A MH/HPS HSA07223221	PARMAR				
100W 1.2A MH/HPS HSP10223221	PARMAR				
NaHJ 100.581	Vossloh Schwabe				
150W 1.8A MH/HPS HSA15223221	PARMAR				
NaHJ 150.995	Vossloh Schwabe				
NK 150 SEP	Helvar				
BSD 100L 406TS	PHILIPS				
BSD 150L 406TS	PHILIPS				

The product is compatible with BSN and BHL ballast (or similar models from other suppliers), see above table.
The product is NOT compatible with electronic ballasts
The product is NOT compatible with CWA type of ballasts/transformers

BSN-series ballast type (or similar) combined with following igniter

Brand	Type	art.nr	mode	MAS LED SON-T IF 3.6Klm 23W E27 Model Number/(Short) EOC wcode 9290034670/871951444887200 9290034671/871951444889600	MAS LED SON-T IF 5.4Klm 34W E27 Model Number/(Short) EOC wcode 9290034672/871951444891900 9290034673/871951444893300	MAS LED SON-T IF 8.1Klm 50W E40 Model Number/(Short) EOC wcode 9290034674/871951444895700 9290034675/871951444897100	MAS LED SON-T IF 10.8Klm 65W E40 Model Number/(Short) EOC wcode 9290034676/871951444899500 9290034677/871951444901500
Without igniter	n.a.	n.a.	n.a.				
Philips	SN58	9136195799 9137001349 9137001348 9137100105 9136195199	semi-parallel				
	SKD578	9137006553 9137006554	semi-parallel				
Vossloh Schwabe	Z250s	140425	series				
	Z400s	140427	series				
	Z400MK	142897	series				
	PZI1000/1K	140617	parallel				
Tridonic	ZRM-2.5-ES/CT	87500086	series				
BAG	NI 400 LE 4K	10007322	series				
	NP603	10067389	parallel				
PARMAR	PAE40 0255	PAE400255	series				
	PXE07 0255		series				
ELT	AVS 400-D	3210232	series				
Electrostart	ZX400-T	78.02.400.0-T	series				
Magnetek (May & Christe)	ZG4.5		series				

Q3 2026

MASTER LED SON-T - InstantFit

9290034670	MAS LED SON-T IF 3.6Klm 23W 727 E27	
9290034671	MAS LED SON-T IF 4Klm 23W 740 E27	
9290034672	MAS LED SON-T IF 5.4Klm 34W 727 E27	
9290034673	MAS LED SON-T IF 6Klm 34W 740 E27	
9290034674	MAS LED SON-T IF 8.1Klm 50W 727 E40	
9290034675	MAS LED SON-T IF 9Klm 50W 740 E40	
9290034676	MAS LED SON-T IF 10.8Klm 65W 727 E40	
9290034677	MAS LED SON-T IF 12Klm 65W 740 E40	

Ballast - Igniter compatibility list

Key

	Compatible.
	Limited compatibility
	Not Compatible
N.A.	Combination not applicable

This document is for information purposes and must be treated as recommendation. Signify attempts to provide accurate result which are generated in lab conditions and might not completely reflect actual conditions.

BSN-series ballast type (or similar) combined with following igniter

Brand	Type	art.nr	mode
Without igniter	n.a.	n.a.	n.a.
Philips	SI51	9136195199	parallel
Vossloh Schwabe	Z250s	140425	series
	Z400s	140427	series
	Z400MK	142897	series
	PZI1000/1K	140617	parallel
Tridonic	ZRM-2.5-ES/CT	87500086	series
BAG	NI 400 LE 4K	10007322	series
	NP603	10067389	parallel
PARMAR	PAE400255	PAE400255	series
	PXE07 0255		series
ELT	AVS 400-D	3210232	series
Electrostart	ZX400-T	78.02.400.0-T	series
Magnetek (May & Christe)	ZG 4.5		series

MAS LED SON-T IF 3.6Klm 23W E27	MAS LED SON-T IF 5.4Klm 34W E27	MAS LED SON-T IF 8.1Klm 50W E40	MAS LED SON-T IF 10.8Klm 65W E40
Model Number/(Short) EOC wcode 9290034670/871951444887200 9290034671/871951444889600	Model Number/(Short) EOC wcode 9290034672/871951444891900 9290034673/871951444893300	Model Number/(Short) EOC wcode 9290034674/871951444895700 9290034675/871951444897100	Model Number/(Short) EOC wcode 9290034676/871951444899500 9290034677/871951444901500

Note

- For enabling compatibility, the "Igniter comfort logic" function is equipped to simulate the low light level at start up of HID lamps, which in some cases can be observed as a short reduction of the light output of the lamp.
- In rare cases the igniter comfort logic cannot stop the igniter. This is visible as continuously flicker of the light. Signify advises to remove/disconnect the igniter.
- Instant ON/OFF – does not require to warm up or to cool down before restart.
- The compatibility of the lamp with the gear is measured in the laboratory at nominal voltage (230VAC). The performance in real applications can be different.
- Manufacturers of ballasts and igniters can change the technical design of their product without informing LED lamp suppliers. These changes can influence the performance of LED products. Signify cannot be held responsible for inaccuracies in the compatibility lists due to technical changes in ballasts or igniters.

Disclaimer:

Philips will not accept claims for any damage caused by implementing the recommendations in this document. More information:

TrueForce LED Public (Road – SON) | 7165342 | Philips lighting

Installer Hub | Philips lighting

MASTER LED SON - T - EM/Mains Voltage

9290034678	MAS LED SON-T EM 3.6Klm 23W 727 E27	
9290034679	MAS LED SON-T EM 4Klm 23W 740 E27	
9290034681	MAS LED SON-T EM 5.4Klm 34W 727 E27	
9290034682	MAS LED SON-T EM 6Klm 34W 740 E27	
9290034684	MAS LED SON-T EM 8.1Klm 50W 727 E40	
9290034685	MAS LED SON-T EM 9Klm 50W 740 E40	
9290034687	MAS LED SON-T EM 10.8Klm 65W 727 E40	
9290034688	MAS LED SON-T EM 12Klm 65W 740 E40	

Ballast - Igniter compatibility list

Key

	Compatible.
	Limited compatibility
	Not Compatible
N.A.	Combination not applicable

This document is for information purposes and must be treated as recommendation. Signify attempts to provide accurate result which are generated in lab conditions and might not completely reflect actual conditions.

EM ballast type	MAS LED SON-T EM 3.6Klm 23W E27 Model Number/(Short) EOC code 9290034678/871951444903900 9290034679/871951444905300	MAS LED SON-T EM 5.4Klm 34W E27 Model Number/(Short) EOC code 9290034681/871951444909100 9290034682/871951444911400	MAS LED SON-T EM 8.1Klm 50W E40 Model Number/(Short) EOC code 9290034684/871951444915200 9290034685/871951444917600	MAS LED SON-T EM 10.8Klm 65W E40 Model Number/(Short) EOC code 9290034687/871951444921300 9290034688/871951444923700
BSN 50W				
BSN 70W				
BHL 80W				
BHL 125W				
BSN 100W				
BSN 150W				
BSN 250W				
BHL 250W				
Direct Mains/Bypass Ballast				
BSD 100L 406TS				
BSD 150L 406TS				

The product is compatible with BSN and BHL ballast (or similar models from other suppliers), see above table.
The product is NOT compatible with electronic ballasts
The product is NOT compatible with CWA type of ballasts/transformers

Note

- The lamp is not compatible with any igniter. Ignitor should be removed.
- To get a decent PF, the power factor compensation capacitor should be removed.
- Instant ON/OFF – does not require to warm up or to cool down before restart.
- The compatibilty of the lamp with the gear is measured in the laboratory at nominal voltage (230VAC). The performance in real applications can be different
- Manufacturers of ballasts can change the technical design of their product without informing LED lamp suppliers. These changes can influence the performance of LED products. Signify cannot be held responsible for inaccuracies in the compatibility lists due to technical changes in ballasts.

Disclaimer:

Philips will not accept claims for any damage caused by implementing the recommendations in this document. More information:

TrueForce LED Public (Road – SON) | 7165342 | Philips lighting

Installer Hub | Philips lighting

MASTER LED SON-T Ultra Efficient - Mains

9290036771	MAS LED SON-T UE M 3.6Klm 19W 727 E27
9290036772	MAS LED SON-T UE M 4Klm 19W 740 E27
9290036773	MAS LED SON-T UE M 5.4Klm 28.5W 727 E27
9290036774	MAS LED SON-T UE M 6Klm 28.5W 740 E27
9290036775	MAS LED SON-T UE M 8Klm 42.8W 727 E40
9290036776	MAS LED SON-T UE M 9Klm 42.8W 740 E40



Ballast - Igniter compatibility list

Key

	Compatible.
	Limited compatibility
	Not Compatible
N.A.	Combination not applicable

This document is for information purposes and must be treated as recommendation. Signify attempts to provide accurate result which are generated in lab conditions and might not completely reflect actual conditions.

EM ballast type	MAS LED SON-T UE M 3.6Klm 19W E27	MAS LED SON-T UE M 5.4Klm 28.5W E27	MAS LED SON-T UE M 8Klm 42.8W E40
	Model Number/(Short) EOC code 9290036771/872016937419500 9290036772/872016937421800	Model Number/(Short) EOC code 9290036773/872016937423200 9290036774/872016937425600	Model Number/(Short) EOC code 9290036775/872016924037700 9290036776/872016924039100
Direct Mains/ Bypass Ballast			
EM ballast			

The product is NOT compatible with all types of ballasts/transformers

Note

- The lamp is not compatible with any Ballast Gear, ballast/igniter/power factor compensation capacitor should be removed.
- Instant ON/OFF – does not require to warm up or to cool down before restart.

Disclaimer:
Philips will not accept claims for any damage caused by implementing the recommendations in this document. More information:

MASTER LED SON-T Ultra Efficient - Mains
Installer Hub | Philips lighting

TrueForce Core LED SON-T - Mains Voltage

9290043411	TForce Core LED road 20W 722 E27 MV
9290043412	TForce Core LED road 26W 727 E27 MV
9290043413	TForce Core LED road 26W 730 E27 MV
9290043414	TForce Core LED road 26W 740 E27 MV
9290043415	TForce Core LED road 32W 722 E40 MV
9290037308	TForce Core LED road 17W 727 E27 MV
9290024848	TForce Core LED road 17W 730 E27 MV
9290024849	TForce Core LED road 17W 740 E27 MV
9290037310	TForce Core LED road 40W 727 E40 MV
9290024852	TForce Core LED road 40W 730 E40 MV
9290024853	TForce Core LED road 40W 740 E40 MV
9290037756	TForce Core LED road 45W 727 E40 MV
9290037788	TForce Core LED road 45W 730 E40 MV
9290037757	TForce Core LED road 49W 740 E40 MV



Ballast - Igniter compatibility list

Key

	Compatible.
	Limited compatibility
	Not Compatible
N.A.	Combination not applicable

This document is for information purposes and must be treated as recommendation. Signify attempts to provide accurate result which are generated in lab conditions and might not completely reflect actual conditions.

EM ballast type	TForce Core LED road 17W E27 Model Number/(Short) EOC code 9290037308/872016926771800 9290024848/871951431625600 9290024849/871951431627000	TForce Core LED road 26W E27 Model Number/(Short) EOC code 9290043412/872110312934500 9290043413/872110312936900 9290043414/872110312938300	TForce Core LED road 40W E40 Model Number/(Short) EOC code 9290037310/872016926775600 9290024852/871951431633100 9290024853/871951431635500	TForce Core LED road 45/49W E40 Model Number/(Short) EOC code 9290037756/872016929743200 9290037788/872016929747000 9290037757/872016929745600	TForce Core LED road 20W 722 E27 Model Number/(Short) EOC code 9290043411/872110312932100	TForce Core LED road 32W 722 E40 Model Number/(Short) EOC code 9290043415/872110312940600
Direct Mains/ Bypass Ballast						
EM ballast						

The product is NOT compatible with all types of ballasts/transformers

Note

- The lamp is not compatible with any Ballast Gear, ballast/igniter/power factor compensation capacitor should be removed.
- Instant ON/OFF – does not require to warm up or to cool down before restart.

Disclaimer:
Philips will not accept claims for any damage caused by implementing the recommendations in this document. More information:

Trueforce Core LED SON-T | 8852552 | Philips lighting

Installer Hub | Philips lighting

TrueForce LED HPL - EM/Mains

9290020061	TForce LED HPL ND 28-21W E27 830
9290020062	TForce LED HPL ND 30-21W E27 840
9290020063	TForce LED HPL ND 38-28W E27 830
9290020064	TForce LED HPL ND 40-28W E27 840
9290020065	TForce LED HPL ND 57-42W E27 830
9290020066	TForce LED HPL ND 60-42W E27 840
9290020067	TForce LED HPL ND 57-42W E40 830
9290020068	TForce LED HPL ND 60-42W E40 840



Ballast - Igniter compatibility list

Key

	Compatible.
	Limited compatibility
	Not Compatible
N.A.	Combination not applicable

This document is for information purposes and must be treated as recommendation. Signify attempts to provide accurate result which are generated in lab conditions and might not completely reflect actual conditions.

EM ballast type	TForce LED HPL ND 21W E27 Model Number/(Short) EOC code 9290020061/871869963814600 9290020062/871869963816000	TForce LED HPL ND 28W E27 Model Number/(Short) EOC code 9290020063/871869963818400 9290020064/871869963820700	TForce LED HPL ND 42W E27 Model Number/(Short) EOC code 9290020065/871869963822100 9290020066/871869963824500	TForce LED HPL ND 42W E40 Model Number/(Short) EOC code 9290020067/871869963826900 9290020068/871869963828300
BSN 50W				
BSN 70W				
BHL 80W				
BHL 125W				
BSN 100W				
BSN 150W				
BSN 250W				
BHL 250W				
Direct Mains/ Bypass Ballast				

The product is compatible with BSN and BHL ballast (or similar models from other suppliers), see above table.
The product is NOT compatible with electronic ballasts
The product is NOT compatible with CWA type of ballasts/transformers

Note

- The lamp is not compatible with any igniter. Ignitor should be removed.
- To get a decent PF, the power factor compensation capacitor should be removed.
- Instant ON/OFF – does not require to warm up or to cool down before restart.
- The compatibilty of the lamp with the gear is measured in the laboratory at nominal voltage (230VAC). The performance in real applications can be different
- Manufacturers of ballasts can change the technical design of their product without informing LED lamp suppliers. These changes can influence the performance of LED products. Signify cannot be held responsible for inaccuracies in the compatibility lists due to technical changes in ballasts.

Disclaimer:
Philips will not accept claims for any damage caused by implementing the recommendations in this document. More information:

TrueForce LED Public (Urban/Road – HPL/SON) | 5763385 | Philips lighting

Installer Hub | Philips lighting

MASTER LED HPL - Mains

929003530702	MAS LED HPL M 2.8Klm 19W 830E27 FR G
929003530802	MAS LED HPL M 3Klm 19W 840 E27 FR G
929003530902	MAS LED HPL M 3.8Klm 24W 830 E27 FR G
929003531002	MAS LED HPL M 4Klm 24W 840 E27 FR G
929003531102	MAS LED HPL M 5.6Klm 33.5W 830 E27 FR G
929003531202	MAS LED HPL M 6Klm 33.5W 840 E27 FR G
929003531302	MAS LED HPL M 5.6Klm 33.5W 830 E40 FR G
929003531402	MAS LED HPL M 6Klm 33.5W 840 E40 FR G



Ballast - Igniter compatibility list

Key

	Compatible.
	Limited compatibility
	Not Compatible
N.A.	Combination not applicable

This document is for information purposes and must be treated as recommendation. Signify attempts to provide accurate result which are generated in lab conditions and might not completely reflect actual conditions.

EM ballast type	MAS LED HPL M 2.8Klm 19W E27 Model Number/(Short) EOC code 9290035307/871951445193300 9290035308/871951445195700	MAS LED HPL M 3.8Klm 24W E27 Model Number/(Short) EOC code 9290035309/871951445197100 9290035310/871951445199500	MAS LED HPL M 5.6Klm 33.5W E27 Model Number/(Short) EOC code 9290035311/871951445201500 9290035312/871951445203900	MAS LED HPL M 5.6Klm 33.5W E40 Model Number/(Short) EOC code 9290035313/871951445205300 9290035314/871951445207700
Direct Mains/ Bypass Ballast				
EM ballast				

The product is NOT compatible with all types of ballasts/transformers

Note

- The lamp is not compatible with any Ballast Gear, ballast/igniter/power factor compensation capacitor should be removed.
- Instant ON/OFF – does not require to warm up or to cool down before restart.

Disclaimer:
Philips will not accept claims for any damage caused by implementing the recommendations in this document. More information:

CorePro LED HPI - Mains

Installer Hub | Philips lighting

Q3 2026

TrueForce CorePro LED HPL - Mains Voltage

9290043650	CorePro LED HPL/SON M 1.8Klm13W827E27FR
9290043651	CorePro LED HPL/SON M 2Klm13W830E27FR
9290043652	CorePro LED HPL/SON M 2Klm13W840E27FR
9290043653	CorePro LED HPL/SON M2.6Klm18.3W827E27FR
9290043654	CorePro LED HPL/SON M3Klm18.3W830E27FR
9290043655	CorePro LED HPL/SON M3Klm18.3W840E27FR
9290043656	CorePro LED HPL/SON M 3.6Klm23W 827E27FR
9290043657	CorePro LED HPL/SON M 4Klm 23W 830E27FR
9290043658	CorePro LED HPL/SON M 4Klm 23W840E27FR
9290043659	CorePro LED HPL/SON M5.3Klm28.5W827E27FR
9290043660	CorePro LED HPL/SON M5.5Klm29.5W830E27FR
9290043661	CorePro LED HPL/SON M 6Klm 31W 840 E27FR
9290043662	CorePro LED HPL/SON M5.3Klm28.5W827E40FR
9290043663	CorePro LED HPL/SON M5.5Klm29.5W830E40FR
9290043664	CorePro LED HPL/SON M 6Klm 31W 840 E40FR



Ballast - Igniter compatibility list

Key

	Compatible.
	Limited compatibility
	Not Compatible
N.A.	Combination not applicable

This document is for information purposes and must be treated as recommendation. Signify attempts to provide accurate result which are generated in lab conditions and might not completely reflect actual conditions.

EM ballast type	CorePro LED HPL/SON 13W E27	CorePro LED HPL/SON 18.3W E27	CorePro LED HPL/SON 23W E27	CorePro LED HPL/SON 28.5/29.5/31W E27	CorePro LED HPL/SON 28.5/29.5/31W E40
	Model Number/(Short) EOC code 9290043650/872110314373000 9290043651/872110314375400 9290043650/872110314377800	Model Number/(Short) EOC code 9290043653/872110314379200 9290043654/872110314381500 9290043655/872110314383900	Model Number/(Short) EOC code 9290043656/872110314385300 9290043657/872110314387700 9290043658/872110314389100	Model Number/(Short) EOC code 9290043659/872110314391400 9290043660/872110314393800 9290043661/872110314395200	Model Number/(Short) EOC code 9290043662/872110314397600 9290043663/872110314399000 9290043664/872110314401000
Direct Mains/ Bypass Ballast					
EM ballast					

The product is NOT compatible with all types of ballasts/transformers

Note

- The lamp is not compatible with any Ballast Gear, ballast/igniter/power factor compensation capacitor should be removed.
- Instant ON/OFF – does not require to warm up or to cool down before restart.

Disclaimer:
Philips will not accept claims for any damage caused by implementing the recommendations in this document. More information:

Trueforce CorePro LED HPL | 7903997 | Philips lighting

Installer Hub | Philips lighting

© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com