



Designed to exceed the aesthetic expectations of city planners, lighting designers, and other outdoor lighting professionals, the **Renaissance** stands as a tribute to history. The **Renaissance** mixes refinement together with ambition. The design reflects and evokes late 19th and early 20th century styling and is perfectly suited for most urban and rural areas. The state-of-the-art technology inside provides exceptional photometric performance, a long lifespan, and ease of maintenance.

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering guide sample


Luminaire	Lamp	Globe/Lens	Optical System	Voltage	Adaptor	Options	Mounting & Configuration	Pole*	Finish**
RN20	250HPS	ACDR	THA3	240	SMA	CR1	PR6-1A	R92-25	GN6TX

* Consult the eCatalog for details and the complete line of poles.
 The specially formulated Lumital powder coat finish is available in a range of many standard colors.
 ** Consult Lume's Color Chart for complete specifications.

Luminaires


Conform to the UL 1598 and CSA C22.2 No. 250.0-08 standards.

RN20-LE3R-ACDR




Weight AC: 34 lbs (15 kg)
Weight GL: 49 lbs (22 kg)
EPA: 1.90 sq. ft.

RN30-THA3-ACDR




Weight AC: 36 lbs (17 kg)
Weight GL: 52 lbs (23 kg)
EPA: 1.90 sq. ft.

RN20-THA3-GL-SMA



Weight AC: 45 lbs (20 kg)
Weight GL: 60 lbs (27 kg)
EPA: 2.63 sq. ft.

RNS20-ACDR



Weight AC: 32 lbs (14.5 kg)
Weight GL: 42 lbs (19.1 kg)
EPA: 1.35 sq. ft.

RN20-RN30-RNS20 Renaissance

Pendant

Lamp/HID


Wattage	RN20 / RN30			RNS20 / RNS30	
	THA3-GL THB3-GL	THA3-ACDR THB3-ACDR	THB3-ACDR	THC3-ACDR TSC3-ACDR	THC3-GL TSC3-GL
50 MH, medium	■	■	■	■	■
70 MH, medium	■	■	■	■	■
100 MH, medium	■	■	■	■	■
150 MH, medium	■	■	■	■	■
175 MH, mogul	■	■	■	■	■
200 MH, mogul	■	■	■	RB	RB
250 MH, mogul	■	■	N/A	N/A	N/A
400 MH, mogul	■	N/A	N/A	N/A	N/A
50 HPS, mogul	■	■	■	■	■
70 HPS, mogul	■	■	■	■	■
100 HPS, mogul	■	■	■	■	■
150 HPS, mogul	■	■	■	■	■
200 HPS, mogul	■	■	■	N/A	RB
250 HPS, mogul	■	■	N/A	N/A	RB
400 HPS, mogul	■	N/A	N/A	N/A	N/A


■ Available. N/A: Not available. RB: Remote Ballast Required.

Optical System / HID

(Lamps not included)

 **THA optics (RN20/RN30)** **THA3** Asymmetrical
Sealed optical chamber consisting of a reflector permanently assembled of top of an internal prismatic globe. Horizontal lamp. > House shield available in option (HS)

 **THB optics (RN20/RN30)** **THB3** Asymmetrical
Sealed optical chamber consisting of a reflector permanently assembled of top of an internal prismatic globe. Vertical lamp. > House shield available in option (HS)

 **THC/TSC optics (RNS20/RNS30)** **THC3** Asymmetrical
TSC3 Asymmetrical
Optical system with an identical structure as the THB with a vertical reflector. Made for lower mounting heights. > House shield available in option (HS)

In the above optics, the sleeve and shutter permit exact positioning of the lamp.

THA & THB refractors available in:

ACDR: Acrylic (max 250 W: THA, 200 W: THB) - **GL:** Borosilicate glass

Add suffix to optical system code.

Voltage/HID

HID ¹
120
208
240
277
347
480


1. Multi-top ballast also available.

Options

- FS** Fusing
- HS** House shield
- PH7** Button-type photoelectric cell
- PH8** Quarter-turn photoelectric cell (Complete with decorative cover and finial. Available with SMA option only)
- CR1** Decorative crown #1
- DC1** 4 decorative hooks
- DE1** Decorative deflector


Poles and Pole Options

Consult the eCatalog for details and the complete line of poles.



Mountings

Consult the eCatalog for details and the complete line of mountings.




Adaptors



MA1
The luminaire is suspended by means of a mounting adaptor with a 1-1/4" (32mm) npt threaded hole accepting a threaded tube from the mounting. (retrofit adaptor for existing mounting)



MA2
1-1/2" (38mm) npt threaded hole accepting a threaded tube from the mounting. (retrofit adaptor for existing mounting)




SMA
The luminaire is suspended by means of a decorative side-mounting cast-aluminum adaptor. This adaptor accepts tubes from 1-5/8" to 2-3/8" (41 to 60 mm) and is adjustable to more or less than 50. The adaptor features a cast-aluminum decorative cover and finial.

RN20-RN30-RNS20 Renaissance

Pendant

Assembly examples



22 ft / 6.71 m
 20 ft / 6.10 m
 18 ft / 5.49 m
 16 ft / 4.88 m
 14 ft / 4.27 m
 12 ft / 3.66 m
 10 ft / 3.05 m
 8 ft / 2.44 m
 6 ft / 1.83 m
 4 ft / 1.22 m
 2 ft / 0.61 m

Luminaire:
RN30-THA3-SMA
 Mounting: **CJL8-1A**
 Pole: **RTA92-BA**

Luminaire:
RN20-THA3
 Mounting: **NM-1A**
 Pole: **RA56-FH**

Luminaire:
RN20-THA3-SMA
 Mounting: **PR8-1A**
 Pole: **SSM8-PS**

Luminaire:
RNS20-THC3-YM
 Pole: **RTA906/907**

