



Combining state-of-the-art photometric performance with outstanding ease-of-maintenance the decorative **Transit** luminaires are designed to last in even the most demanding environments. The versatility and character of the **Transit** luminaire is clear. Combining stunning good looks with outstanding photometric performance, the **Transit** incorporates the cutting edge photometrics and ease of maintenance that have made Lumec luminaires the perfect choice for effective area lighting.

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering guide sample

Luminaire	Lamp	Optical System	Voltage	Options	Mounting & Configuration	Pole*	Finish**
TR10	100HPS	SHA3M-ACDR	240	HS	CR-1A	SM6-12	GN6TX

* Consult the eCatalog for details and the complete line of poles.


The specially formulated Lumital powder coat finish is available in a range of many standard colors.

** Consult Lumec's Color Chart for complete specifications.

Luminaires


Conform to the UL 1598 and CSA C22.2 No. 250.0-08 standards.

TR10-SHA-PH8




Weight: 40 lbs (18.1 kg)
EPA: 1.52 sq. ft.

TR20-SSA




EPA: 1.46 sq. ft.

TR20-SHA-SN




Weight: 46 lbs (20.9 kg)
EPA: 2.38 sq. ft.

TR20-SHA-GRD-TN



Weight: 51 lbs (23.1 kg)
EPA: 2.70 sq. ft.

TR20-SCB-UN



Weight: 53 lbs (24.0 kg)
EPA: 4.20 sq. ft.

TR10-TR20 Transit

Post Top and Pendant

Lamp/HID

Wattage	TR10			TR20		
	SCB3M SHA3M-PC SSA3M-PC	SHA3M-ACDR SA3M-ACDR	SG	SCB3M SHA3M-PC SSA3M-PC	SHA3M-ACDR SSA3M-ACDR	SG
50MH, medium	■	■	RB	■	■	■
70MH, medium	■	■	RB	■	■	■
100MH, medium	■	■	RB	■	■	■
150MH, medium	■	■	RB	■	■	■
200MH, mogul	■	N/A	RB	■	N/A	■
175PSMH, mogul	■	■	N/A	■	■	■
250PSMH, mogul	■	N/A	RB	■	N/A	■
35HPS, medium	■	■	RB	■	■	■
50HPS, mogul	■	■	RB	■	■	■
70HPS, mogul	■	■	RB	■	■	■
100HPS, mogul	■	■	RB	■	■	■
150HPS, mogul	■	■	RB	■	■	■
200HPS, mogul ¹	■	N/A	RB	■	N/A	■
250HPS, mogul ¹	■	N/A	RB	■	N/A	■
400HPS, mogul ¹	N/A	N/A	N/A	N/A	N/A	RB

■ Available. N/A : Not available. 1. N/A with SGFM.

Optical System / HID

(Lamps not included)



SHA and SSA optics
Sealed optical chamber
consisting of a reflector
permanently assembled
on top of an internal
prismatic globe.

SHA3M Asymmetrical

SSA3M Asymmetrical

> House shield available in option (HS)



SCB optics
Sealed optical chamber
consisting of a reflector
permanently assembled
on top of a tempered-glass
sag lens.

SCB3M Asymmetrical

> House shield available in option (HS)

In the above optics, the sleeve and shutter permit exact positioning of the lamp.

Voltage

HID ¹
120
208
240
277
347
480


1. Multi-top ballast also available.

Options

- HS** House shield
- GRD** Decorative grid (TR20 only. Not available with SCB optics)
- PH** Photoelectric cell (TR10 only)

Poles and Pole Options

Consult the eCatalog for details and the complete line of poles.




APR4 & LBC2

SM6


SM8

Mountings


Consult the eCatalog for details and the complete line of mountings.




CR




TN



JR



SN



UN

TR10-TR20 Transit

Post Top and Pendant

Assembly examples

