

Wall Light Classic



Classic rectangular look, futuristic performance with these weatherproof mains voltage outdoor wall lights. Bathe your front garden, back garden, balcony, or porch with a whopping 1,000 lumens of beautiful dynamic color and tunable white light. Works with your existing Wi-Fi and WIZ lamps and luminaires.

PRODUCT HIGHLIGHTS

- Full color
- Mains Voltage
- Weatherproof




Instant setup for all your smart lighting

Access all smart features instantly, simply by connecting your new lights to your existing Wi-Fi. You can control lights when you're away from home and set schedules to turn them on and off automatically. All without needing to install additional hardware. Keep the controller within Wi-Fi range, and all linked lights will be fully controllable even out of Wi-Fi range.




Matter Certified

This product is Matter certified. You can set it up and control it with your preferred smart home platform and make it work seamlessly with other Matter Certified devices.



Always feel safe and secure with automated outdoor lights

Schedule your outdoor lights to turn on every day before you get home, so that you can clearly see your environment and feel safe. Set your lights to turn off automatically in the morning, or when they are not necessary, and save energy.




Create your perfect outdoor light Scene

Mix different color and white light modes to create the perfect light ambience for your perfect garden moments. Save your scene and select it anytime with app, voice or control accessory.



Beautify your garden with millions of colors & dynamic modes

Choose from millions of light colors, from energizing cool white to soft warm white and create the best ambience for your outdoor activities. Or simply apply a preset dynamic light mode, like Ocean, Forest or Party to create an amazing atmosphere and lift the mood.



Control your outdoor lights the way you like it

WiZ gives you many options to control your smart lights. Simply adjust lights with your smartphone or your voice from wherever you are. Works with Google Home, Alexa and Siri Shortcuts.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Outdoor

DESIGN AND FINISHING

Color: Black

Material: Metal Plastic

DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)

Lumen maintenance factor: 70%

Nominal lifetime: 25,000

Number of switch cycles: 50,000

EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: No

Dimmable with remote control: Yes

LED integrated: Yes

LED lamp(s) included: No

Remote control included: No

LIGHT CHARACTERISTICS

Color consistency: 7 SDCM

Color rendering index (CRI): 80

Warm-up time to 60% light: <2

MISCELLANEOUS

Especially designed for: Garden & Patio

OTHER CHARACTERISTICS

Lamp current: 88 mA

Efficacy: 63 lm/W

POWER CONSUMPTION

Power factor: 0.7

Voltage: 100-120 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.78 kg

Height: 24.1 cm

Length: 23 cm

Width: 17 cm

SERVICE

Warranty: 2 year(s)

Subscription: Not applicable

TECHNICAL SPECIFICATIONS

Lumen output bulb included: 1,000

Total lumen output fixture: 600

Light color: 2700-5000 (RGB)

Fixture dimmable: Wireless Dim - Do not use with dimmer

Number of bulbs: 1

Wattage bulb included: 9.5

Maximum wattage replacement bulb: 9.5

IP code: UL03 | Wet Location

Class of protection: UL earthed

Light source replaceable: No

WHAT'S SUPPORTED

Compatible with Effects: Yes

Max. number of accessories: 9999

WiFi: Wireless G

Defined support period: Minimum of 60 months after introduction date

Communication protocol: Bluetooth WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677605308

Net weight: 0.78 kg

Gross weight: 1.16 kg

Height: 29.6 cm

Length: 19.7 cm

Width: 25.2 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.