Maxos LED Performer – efficient and precise line lighting

Maxos LED Performer

Customers want to save energy and reduce cost compared to what they are used to with conventional lighting. At the same time, excellent lighting conditions are needed: in industrial environments, to guarantee safety and productivity; and in retail environments, to make the merchandise stand out and attract shoppers. Maxos LED Performer is an extremely flexible solution that delivers low energy consumption and excellent beam shaping at an attractive investment level.

Benefits

- Extremely fast payback
- Breakthrough optical system for precise beam shaping
- Flexible in terms of retrofits, spots, changes, accessories

Features

- Low energy consumption compared to fluorescent
- Excellent beam shaping for less spill light and exact light distribution in horizontal and vertical planes
- Proven Philips LED engines (Fortimo)
- Can be mounted, new or retrofit, onto a Maxos rail

Application

- Supermarkets
- Warehouses
- Production facilities

Maxos LED Performer

Dimensional drawing



Product details

IPDP_4MX900i_0001-Detail photo

IPDP_4MX900i_0003-Detail photo



IPDP_4MX900i_0011-Detail photo

Maxos LED Performer

Product details

General Information	
CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	≥80
Operating and Electrical	
Line Frequency	50 to 60 Hz
Temperature	
Ambient temperature range	-20 to +40 °C
Approval and Application	
Protection class IEC	Safety class I
Mech. impact protection code	IK02
Ingress protection code	IP40
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Application Conditions	
Suitable for random switching	Not applicable

General Information

Order Code	Full Product Name	Lamp family code	Embedded control	Product family code
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	LED50S	Constant light output	4MX900
910500460293	4MX900 491 LED50S/840 PSD-CLO DA20 WH	-	-	4MX900
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	-	-	4MX900
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	-	-	4MX900
910500460296	4MX900 491 LED50S/840 PSD DA20 WH C-2R	-	-	4MX900
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	-	-	4MX900
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	-	-	4MX900
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	-	-	4MX900
910500460301	4MX900 491 LED75S/840 PSD-CLO DA20 WH	-	-	4MX900
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	-	-	4MX900
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	-	-	4MX900
910500460304	4MX900 491 LED75S/840 PSD DA20 WH C-2R	-	-	4MX900
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	-	-	4MX900
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	-	-	4MX900
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	-	-	4MX900
910500460308	4MX900 581 LED40S/840 PSD DA20 WH	-	-	4MX900
910500460309	4MX900 581 LED40S/840 PSD MB WH	-	-	4MX900
910500460310	4MX900 581 LED40S/840 PSD NB WH	-	-	4MX900
910500460311	4MX900 581 LED40S/840 PSD WB WH	-	-	4MX900
910500460312	4MX900 581 LED50S/840 PSD DA20 WH	-	-	4MX900
910500460313	4MX900 581 LED50S/840 PSD-CLO DA20 WH	-	-	4MX900
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	-	-	4MX900
910500460315	4MX900 581 LED50S/840 PSD-CLO NB WH	-	-	4MX900
910500460316	4MX900 581 LED50S/840 PSD DA20 WH C-2R	-	-	4MX900
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	-	-	4MX900
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	-	-	4MX900
910500460320	4MX900 581 LED75S/840 PSD-CLO DA20 WH	-	-	4MX900
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	-	-	4MX900
910500460322	4MX900 581 LED75S/840 PSD DA20 WH C-2R	-	-	4MX900
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	-	-	4MX900
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	-	-	4MX900
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	-	-	4MX900
910500460358	4MX933 491 LED50S/840 PSU DA20 WH ELB3	-	-	4MX933
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	-	-	4MX933
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	-	-	4MX933

Order Code	Full Product Name	Lamp family code	Embedded control	Product family code
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	-	-	4MX933
910500460362	4MX933 491 LED50S/840 PSD DA20WHELB3C-2R	-	-	4MX933
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	-	-	4MX933
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	-	-	4MX933
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	-	-	4MX933
910500460370	4MX933 491 LED75S/840 PSD DA20WHELB3C-2R	-	-	4MX933
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	-	-	4MX933
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	-	-	4MX933
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	-	-	4MX933
910500460374	4MX933 581 LED50S/840 PSU DA20 WH ELB3	-	-	4MX933
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	-	-	4MX933
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	-	-	4MX933
910500460378	4MX933 581 LED50S/840 PSD DA20WHELB3C-2R	-	-	4MX933
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	-	-	4MX933
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	-	-	4MX933
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	-	-	4MX933
910500460386	4MX933 581 LED75S/840 PSD DA20WHELB3C-2R	-	-	4MX933
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	-	-	4MX933
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	-	-	4MX933
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	-	-	4MX933
910629173126	4MX900 581 LED50S/840 PSD MB WH	LED50S	-	4MX900
910629177026	4MX900 581 LED50S/840 PSD WB WH	LED50S	-	4MX900
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	LED75S	Constant light output	4MX900
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	-	-	4MX933
910629132426	4MX900 LED40S/840 PSD WB WH L1200	LED40S	-	4MX900
910629132526	4MX900 LED40S/840 PSD MB WH L1200	LED40S	-	4MX900
910629132626	4MX900 LED40S/840 PSD NB WH L1200	LED40S	-	4MX900
910629132726	4MX900 LED40S/840 PSD DA20 WH L1200	LED40S	-	4MX900
910629137226	4MX900 LED60S/840 PSD WB WH L1800	LED60S	-	4MX900
910629137326	4MX900 LED60S/840 PSD MB WH L1800	LED60S	-	4MX900
910629137426	4MX900 LED60S/840 PSD NB WH L1800	LED60S	-	4MX900
910629137526	4MX900 LED60S/840 PSD DA20 WH L1800	LED60S	-	4MX900
910629138826	4MX900 LED90S/840 PSD WB WH L1800	LED90S	-	4MX900
910629138926	4MX900 LED90S/840 PSD MB WH L1800	LED90S	-	4MX900
910629139026	4MX900 LED90S/840 PSD NB WH L1800	LED90S	-	4MX900
910629139126	4MX900 LED90S/840 PSD DA20 WH L1800	LED90S	-	4MX900
910629140426	4MX900 581 LED40S/840 PSU WB WH	LED40S	-	4MX900
910629140526	4MX900 581 LED40S/840 PSU MB WH	LED40S	-	4MX900
910629142026	4MX900 491 LED40S/840 PSU WB WH	LED40S	-	4MX900
910629142126	4MX900 491 LED40S/840 PSU MB WH	LED40S	-	4MX900
910629143226	4MX900 LED40S/840 PSU WB WH L1200	LED40S	-	4MX900
910629144426	4MX900 491 LED40S/840 PSD WB WH	LED40S	-	4MX900
910629144526	4MX900 491 LED40S/840 PSD MB WH	LED40S	-	4MX900

Order Code	Full Product Name	Lamp family code	Embedded control	Product family code
910629144626	4MX900 491 LED40S/840 PSD NB WH	LED40S	-	4MX900
910629144826	4MX900 491 LED50S/840 PSD WB WH	LED50S	-	4MX900
910629144926	4MX900 491 LED50S/840 PSD MB WH	LED50S	-	4MX900
910629145026	4MX900 491 LED50S/840 PSD NB WH	LED50S	-	4MX900
910629145126	4MX900 491 LED50S/840 PSD DA20 WH	LED50S	-	4MX900
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	LED40S	-	4MX900
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	LED60S	-	4MX900
910629145626	4MX900 581 LED40S/840 PSU A30 WH	LED40S	-	4MX900
910629145726	4MX900 581 LED50S/840 PSU A30 WH	LED50S	-	4MX900
910629145826	4MX900 491 LED40S/840 PSU A30 WH	LED40S	-	4MX900
910629145926	4MX900 491 LED50S/840 PSU A30 WH	LED50S	-	4MX900
910629146026	4MX900 581 LED50S/840 PSU WB WH	LED50S	-	4MX900
910629146126	4MX900 581 LED50S/840 PSU MB WH	LED50S	-	4MX900
910629146426	4MX900 491 LED50S/840 PSU WB WH	LED50S	-	4MX900
910629146526	4MX900 491 LED50S/840 PSU MB WH	LED50S	-	4MX900
910629146626	4MX900 491 LED50S/840 PSU NB WH	LED50S	-	4MX900
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	LED90S	-	4MX900
910629148326	4MX900 581 LED75S/840 PSU A30 WH	LED75S	-	4MX900
910629148526	4MX900 491 LED75S/840 PSU A30 WH	LED75S	-	4MX900
910629170126	4MX900 491 LED50S/840 PSU DA30 WH	LED50S	-	4MX900
910629170326	4MX900 491 LED75S/840 PSU WB WH	LED75S	-	4MX900
910629170426	4MX900 491 LED75S/840 PSU MB WH	LED75S	-	4MX900
910629170826	4MX900 581 LED75S/840 PSU WB WH	LED75S	-	4MX900
910629170926	4MX900 581 LED75S/840 PSU MB WH	LED75S	-	4MX900
910629171026	4MX900 581 LED75S/840 PSU NB WH	LED75S	-	4MX900
910629171326	4MX900 491 LED75S/840 PSD WB WH	LED75S	-	4MX900
910629171426	4MX900 491 LED75S/840 PSD MB WH	LED75S	-	4MX900
910629171526	4MX900 491 LED75S/840 PSD NB WH	LED75S	-	4MX900
910629171726	4MX900 491 LED75S/840 PSD DA20 WH	LED75S	-	4MX900
910629171826	4MX900 491 LED75S/840 PSD A30 WH	LED75S	-	4MX900
910629171926	4MX900 581 LED75S/840 PSD WB WH	LED75S	-	4MX900
910629172026	4MX900 581 LED75S/840 PSD MB WH	LED75S	-	4MX900
910629172126	4MX900 581 LED75S/840 PSD NB WH	LED75S	-	4MX900
910629172326	4MX900 581 LED75S/840 PSD DA20 WH	LED75S	-	4MX900
910629172426	4MX900 581 LED75S/840 PSD A30 WH	LED75S	-	4MX900
910629173226	4MX900 581 LED50S/840 PSD A30 WH	LED50S	-	4MX900
910629131626	4MX900 LED40S/840 PSD WB SI L1200	LED40S	-	4MX900
910629131926	4MX900 LED40S/840 PSD DA20 SI L1200	LED40S	-	4MX900
910629136426	4MX900 LED60S/840 PSD WB SI L1800	LED60S	-	4MX900
910629136726	4MX900 LED60S/840 PSD DA20 SI L1800	LED60S	-	4MX900
910629138026	4MX900 LED90S/840 PSD WB SI L1800	LED90S	-	4MX900
910629138126	4MX900 LED90S/840 PSD MB SI L1800	LED90S	-	4MX900
910629141226	4MX900 491 LED40S/840 PSU WB SI	LED40S	-	4MX900
910629141326	4MX900 491 LED40S/840 PSU MB SI	LED40S	-	4MX900
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	LED90S	-	4MX900
910629172926	4MX900 LED40S/840 PSU WB SI L1200	LED40S	-	4MX900
910629177526	4MX900 581 LED50S/840 PSU A30 SI	LED50S	-	4MX900

Light Technical

Maxos LED Performer

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	155 lm/W	5,000 lm	-	Wide beam
910500460293	4MX900 491 LED50S/840 PSD-CLO DA20 WH	155 lm/W	5,000 lm	-	Double asymmetric optic 20°
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	155 lm/W	5,000 lm	-	Medium beam
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	155 lm/W	5,000 lm	-	Narrow beam
910500460296	4MX900 491 LED50S/840 PSD DA20 WH C-2R	155 lm/W	5,000 lm	-	Double asymmetric optic 20°
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	155 lm/W	5,000 lm	-	Medium beam
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	155 lm/W	5,000 lm	-	Narrow beam
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	155 lm/W	5,000 lm	-	Wide beam
910500460301	4MX900 491 LED75S/840 PSD-CLO DA20 WH	149 lm/W	7,500 lm	-	Double asymmetric optic 20°
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	149 lm/W	7,500 lm	-	Narrow beam
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	149 lm/W	7,500 lm	-	Wide beam
910500460304	4MX900 491 LED75S/840 PSD DA20 WH C-2R	149 lm/W	7,500 lm	-	Double asymmetric optic 20°
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	149 lm/W	7,500 lm	-	Medium beam
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	149 lm/W	7,500 lm	-	Narrow beam
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	149 lm/W	7,500 lm	-	Wide beam
910500460308	4MX900 581 LED40S/840 PSD DA20 WH	159 lm/W	4,000 lm	-	Double asymmetric optic 20°
910500460309	4MX900 581 LED40S/840 PSD MB WH	159 lm/W	4,000 lm	-	Medium beam
910500460310	4MX900 581 LED40S/840 PSD NB WH	159 lm/W	4,000 lm	-	Narrow beam
910500460311	4MX900 581 LED40S/840 PSD WB WH	159 lm/W	4,000 lm	-	Wide beam
910500460312	4MX900 581 LED50S/840 PSD DA20 WH	155 lm/W	5,000 lm	-	Double asymmetric optic 20°
910500460313	4MX900 581 LED50S/840 PSD-CLO DA20 WH	155 lm/W	5,000 lm	-	Double asymmetric optic 20°
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	155 lm/W	5,000 lm	-	Medium beam
910500460315	4MX900 581 LED50S/840 PSD-CLO NB WH	155 lm/W	5,000 lm	-	Narrow beam
910500460316	4MX900 581 LED50S/840 PSD DA20 WH C-2R	155 lm/W	5,000 lm	-	Double asymmetric optic 20°
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	155 lm/W	5,000 lm	-	Medium beam
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	155 lm/W	5,000 lm	-	Narrow beam
910500460320	4MX900 581 LED75S/840 PSD-CLO DA20 WH	149 lm/W	7,500 lm	-	Double asymmetric optic 20°
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	149 lm/W	7,500 lm	-	Narrow beam
910500460322	4MX900 581 LED75S/840 PSD DA20 WH C-2R	149 lm/W	7,500 lm	-	Double asymmetric optic 20°
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	149 lm/W	7,500 lm	-	Medium beam
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	149 lm/W	7,500 lm	-	Narrow beam
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	149 lm/W	7,500 lm	-	Wide beam

Maxos LED Performer

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
910500460358	4MX933 491 LED50S/840 PSU DA20 WH ELB3	155 lm/W	5,000 lm	-	Double asymmetric optic 20°
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	155 lm/W	5,000 lm	-	Medium beam
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	155 lm/W	5,000 lm	-	Narrow beam
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	155 lm/W	5,000 lm	-	Wide beam
910500460362	4MX933 491 LED50S/840 PSD DA20WHELB3C-2R	155 lm/W	5,000 lm	-	Double asymmetric optic 20°
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	155 lm/W	5,000 lm	-	Medium beam
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	155 lm/W	5,000 lm	-	Narrow beam
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	155 lm/W	5,000 lm	-	Wide beam
910500460370	4MX933 491 LED75S/840 PSD DA20WHELB3C-2R	149 lm/W	7,500 lm	-	Double asymmetric optic 20°
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	149 lm/W	7,500 lm	-	Medium beam
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	149 lm/W	7,500 lm	-	Narrow beam
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	149 lm/W	7,500 lm	-	Wide beam
910500460374	4MX933 581 LED50S/840 PSU DA20 WH ELB3	155 lm/W	5,000 lm	-	Double asymmetric optic 20°
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	155 lm/W	5,000 lm	-	Medium beam
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	155 lm/W	5,000 lm	-	Wide beam
910500460378	4MX933 581 LED50S/840 PSD DA20WHELB3C-2R	155 lm/W	5,000 lm	-	Double asymmetric optic 20°
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	155 lm/W	5,000 lm	-	Medium beam
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	155 lm/W	5,000 lm	-	Narrow beam
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	155 lm/W	5,000 lm	-	Wide beam
910500460386	4MX933 581 LED75S/840 PSD DA20WHELB3C-2R	149 lm/W	7,500 lm	-	Double asymmetric optic 20°
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	149 lm/W	7,500 lm	-	Medium beam
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	149 lm/W	7,500 lm	-	Narrow beam
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	149 lm/W	7,500 lm	-	Wide beam
910629173126	4MX900 581 LED50S/840 PSD MB WH	155 lm/W	5,000 lm	-	Medium beam
910629177026	4MX900 581 LED50S/840 PSD WB WH	155 lm/W	5,000 lm	-	Wide beam
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	149 lm/W	7,500 lm	1	Medium beam
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	155 lm/W	5,000 lm	-	Narrow beam
910629132426	4MX900 LED40S/840 PSD WB WH L1200	154 lm/W	4,000 lm	1	Wide beam
910629132526	4MX900 LED40S/840 PSD MB WH L1200	154 lm/W	4,000 lm	1	Medium beam
910629132626	4MX900 LED40S/840 PSD NB WH L1200	154 lm/W	4,000 lm	1	Narrow beam
910629132726	4MX900 LED40S/840 PSD DA20 WH L1200	154 lm/W	4,000 lm	1	Double asymmetric optic 20°
910629137226	4MX900 LED60S/840 PSD WB WH L1800	161 lm/W	6,000 lm	1	Wide beam

Maxos LED Performer

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
910629137326	4MX900 LED60S/840 PSD MB WH L1800	161 lm/W	6,000 lm	1	Medium beam
910629137426	4MX900 LED60S/840 PSD NB WH L1800	161 lm/W	6,000 lm	1	Narrow beam
910629137526	4MX900 LED60S/840 PSD DA20 WH L1800	161 lm/W	6,000 lm	1	Double asymmetric optic 20°
910629138826	4MX900 LED90S/840 PSD WB WH L1800	150 lm/W	9,000 lm	1	Wide beam
910629138926	4MX900 LED90S/840 PSD MB WH L1800	150 lm/W	9,000 lm	1	Medium beam
910629139026	4MX900 LED90S/840 PSD NB WH L1800	150 lm/W	9,000 lm	1	Narrow beam
910629139126	4MX900 LED90S/840 PSD DA20 WH L1800	150 lm/W	9,000 lm	1	Double asymmetric optic 20°
910629140426	4MX900 581 LED40S/840 PSU WB WH	159 lm/W	4,000 lm	1	Wide beam
910629140526	4MX900 581 LED40S/840 PSU MB WH	159 lm/W	4,000 lm	1	Medium beam
910629142026	4MX900 491 LED40S/840 PSU WB WH	159 lm/W	4,000 lm	1	Wide beam
910629142126	4MX900 491 LED40S/840 PSU MB WH	159 lm/W	4,000 lm	1	Medium beam
910629143226	4MX900 LED40S/840 PSU WB WH L1200	154 lm/W	4,000 lm	1	Wide beam
910629144426	4MX900 491 LED40S/840 PSD WB WH	159 lm/W	4,000 lm	1	Wide beam
910629144526	4MX900 491 LED40S/840 PSD MB WH	159 lm/W	4,000 lm	1	Medium beam
910629144626	4MX900 491 LED40S/840 PSD NB WH	159 lm/W	4,000 lm	1	Narrow beam
910629144826	4MX900 491 LED50S/840 PSD WB WH	155 lm/W	5,000 lm	1	Wide beam
910629144926	4MX900 491 LED50S/840 PSD MB WH	155 lm/W	5,000 lm	1	Medium beam
910629145026	4MX900 491 LED50S/840 PSD NB WH	155 lm/W	5,000 lm	1	Narrow beam
910629145126	4MX900 491 LED50S/840 PSD DA20 WH	155 lm/W	5,000 lm	1	Double asymmetric optic 20°
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	154 lm/W	4,000 lm	1	Asymmetrical mirror axis angle 30°
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	161 lm/W	6,000 lm	1	Asymmetrical mirror axis angle 30°
910629145626	4MX900 581 LED40S/840 PSU A30 WH	159 lm/W	4,000 lm	1	Asymmetrical mirror axis angle 30°
910629145726	4MX900 581 LED50S/840 PSU A30 WH	155 lm/W	5,000 lm	1	Asymmetrical mirror axis angle 30°
910629145826	4MX900 491 LED40S/840 PSU A30 WH	159 lm/W	4,000 lm	1	Asymmetrical mirror axis angle 30°
910629145926	4MX900 491 LED50S/840 PSU A30 WH	155 lm/W	5,000 lm	1	Asymmetrical mirror axis angle 30°
910629146026	4MX900 581 LED50S/840 PSU WB WH	155 lm/W	5,000 lm	1	Wide beam
910629146126	4MX900 581 LED50S/840 PSU MB WH	155 lm/W	5,000 lm	1	Medium beam
910629146426	4MX900 491 LED50S/840 PSU WB WH	155 lm/W	5,000 lm	1	Wide beam
910629146526	4MX900 491 LED50S/840 PSU MB WH	155 lm/W	5,000 lm	1	Medium beam
910629146626	4MX900 491 LED50S/840 PSU NB WH	155 lm/W	5,000 lm	1	Narrow beam
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	150 lm/W	9,000 lm	1	Asymmetrical mirror axis angle 30°
910629148326	4MX900 581 LED75S/840 PSU A30 WH	149 lm/W	7,500 lm	1	Asymmetrical mirror axis angle 30°

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
910629148526	4MX900 491 LED75S/840 PSU A30 WH	149 lm/W	7,500 lm	1	Asymmetrical mirror axis angle 30°
910629170126	4MX900 491 LED50S/840 PSU DA30 WH	155 lm/W	5,000 lm	1	Double asymmetric optic 30°
910629170326	4MX900 491 LED75S/840 PSU WB WH	149 lm/W	7,500 lm	1	Wide beam
910629170426	4MX900 491 LED75S/840 PSU MB WH	149 lm/W	7,500 lm	1	Medium beam
910629170826	4MX900 581 LED75S/840 PSU WB WH	149 lm/W	7,500 lm	1	Wide beam
910629170926	4MX900 581 LED75S/840 PSU MB WH	149 lm/W	7,500 lm	1	Medium beam
910629171026	4MX900 581 LED75S/840 PSU NB WH	149 lm/W	7,500 lm	1	Narrow beam
910629171326	4MX900 491 LED75S/840 PSD WB WH	149 lm/W	7,500 lm	1	Wide beam
910629171426	4MX900 491 LED75S/840 PSD MB WH	149 lm/W	7,500 lm	1	Medium beam
910629171526	4MX900 491 LED75S/840 PSD NB WH	149 lm/W	7,500 lm	1	Narrow beam
910629171726	4MX900 491 LED75S/840 PSD DA20 WH	149 lm/W	7,500 lm	1	Double asymmetric optic 20°
910629171826	4MX900 491 LED75S/840 PSD A30 WH	149 lm/W	7,500 lm	1	Asymmetrical mirror axis angle 30°
910629171926	4MX900 581 LED75S/840 PSD WB WH	149 lm/W	7,500 lm	1	Wide beam
910629172026	4MX900 581 LED75S/840 PSD MB WH	149 lm/W	7,500 lm	1	Medium beam
910629172126	4MX900 581 LED75S/840 PSD NB WH	149 lm/W	7,500 lm	1	Narrow beam
910629172326	4MX900 581 LED75S/840 PSD DA20 WH	149 lm/W	7,500 lm	1	Double asymmetric optic 20°
910629172426	4MX900 581 LED75S/840 PSD A30 WH	149 lm/W	7,500 lm	1	Asymmetrical mirror axis angle 30°
910629173226	4MX900 581 LED50S/840 PSD A30 WH	155 lm/W	5,000 lm	1	Asymmetrical mirror axis angle 30°
910629131626	4MX900 LED40S/840 PSD WB SI L1200	154 lm/W	4,000 lm	1	Wide beam
910629131926	4MX900 LED40S/840 PSD DA20 SI L1200	154 lm/W	4,000 lm	1	Double asymmetric optic 20°
910629136426	4MX900 LED60S/840 PSD WB SI L1800	161 lm/W	6,000 lm	1	Wide beam
910629136726	4MX900 LED60S/840 PSD DA20 SI L1800	161 lm/W	6,000 lm	1	Double asymmetric optic 20°
910629138026	4MX900 LED90S/840 PSD WB SI L1800	150 lm/W	9,000 lm	1	Wide beam
910629138126	4MX900 LED90S/840 PSD MB SI L1800	150 lm/W	9,000 lm	1	Medium beam
910629141226	4MX900 491 LED40S/840 PSU WB SI	159 lm/W	4,000 lm	1	Wide beam
910629141326	4MX900 491 LED40S/840 PSU MB SI	159 lm/W	4,000 lm	1	Medium beam
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	150 lm/W	9,000 lm	1	Asymmetrical mirror axis angle 30°
910629172926	4MX900 LED40S/840 PSU WB SI L1200	154 lm/W	4,000 lm	1	Wide beam
910629177526	4MX900 581 LED50S/840 PSU A30 SI	155 lm/W	5,000 lm	1	Asymmetrical mirror axis angle 30°

Operating and Electrical

Maxos LED Performer

Order Code	Full Product Name	Input Voltage	Power Consumption
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	220 to 240 V	32.2 W
910500460293	4MX900 491 LED50S/840 PSD-CLO DA20 WH	220 to 240 V	32.2 W
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	220 to 240 V	32.2 W
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	220 to 240 V	32.2 W
910500460296	4MX900 491 LED50S/840 PSD DA20 WH C-2R	220 to 240 V	32.2 W
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	220 to 240 V	32.2 W
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	220 to 240 V	32.2 W
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	220 to 240 V	32.2 W
910500460301	4MX900 491 LED75S/840 PSD-CLO DA20 WH	220 to 240 V	50.2 W
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	220 to 240 V	50.2 W
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	220 to 240 V	50.2 W
910500460304	4MX900 491 LED75S/840 PSD DA20 WH C-2R	220 to 240 V	50.2 W
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	220 to 240 V	50.2 W
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	220 to 240 V	50.2 W
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	220 to 240 V	50.2 W
910500460308	4MX900 581 LED40S/840 PSD DA20 WH	220 to 240 V	25.2 W
910500460309	4MX900 581 LED40S/840 PSD MB WH	220 to 240 V	25.2 W
910500460310	4MX900 581 LED40S/840 PSD NB WH	220 to 240 V	25.2 W
910500460311	4MX900 581 LED40S/840 PSD WB WH	220 to 240 V	25.2 W
910500460312	4MX900 581 LED50S/840 PSD DA20 WH	220 to 240 V	32.2 W
910500460313	4MX900 581 LED50S/840 PSD-CLO DA20 WH	220 to 240 V	32.2 W
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	220 to 240 V	32.2 W
910500460315	4MX900 581 LED50S/840 PSD-CLO NB WH	220 to 240 V	32.2 W
910500460316	4MX900 581 LED50S/840 PSD DA20 WH C-2R	220 to 240 V	32.2 W
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	220 to 240 V	32.2 W
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	220 to 240 V	32.2 W
910500460320	4MX900 581 LED75S/840 PSD-CLO DA20 WH	220 to 240 V	50.2 W
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	220 to 240 V	50.2 W
910500460322	4MX900 581 LED75S/840 PSD DA20 WH C-2R	220 to 240 V	50.2 W
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	220 to 240 V	50.2 W
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	220 to 240 V	50.2 W
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	220 to 240 V	50.2 W
910500460358	4MX933 491 LED50S/840 PSU DA20 WH ELB3	220 to 240 V	32.2 W
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	220 to 240 V	32.2 W
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	220 to 240 V	32.2 W
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	220 to 240 V	32.2 W
910500460362	4MX933 491 LED50S/840 PSD DA20WHELB3C-2R	220 to 240 V	32.2 W
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	220 to 240 V	32.2 W
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	220 to 240 V	32.2 W
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	220 to 240 V	32.2 W
910500460370	4MX933 491 LED75S/840 PSD DA20WHELB3C-2R	220 to 240 V	50.2 W
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	220 to 240 V	50.2 W
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	220 to 240 V	50.2 W
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	220 to 240 V	50.2 W
910500460374	4MX933 581 LED50S/840 PSU DA20 WH ELB3	220 to 240 V	32.2 W
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	220 to 240 V	32.2 W
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	220 to 240 V	32.2 W
910500460378	4MX933 581 LED50S/840 PSD DA20WHELB3C-2R	220 to 240 V	32.2 W
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	220 to 240 V	32.2 W
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	220 to 240 V	32.2 W

Maxos LED Performer

Order Code	Full Product Name	Input Voltage	Power Consumption
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	220 to 240 V	32.2 W
910500460386	4MX933 581 LED75S/840 PSD DA20WHELB3C-2R	220 to 240 V	50.2 W
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	220 to 240 V	50.2 W
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	220 to 240 V	50.2 W
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	220 to 240 V	50.2 W
910629173126	4MX900 581 LED50S/840 PSD MB WH	220 to 240 V	32.2 W
910629177026	4MX900 581 LED50S/840 PSD WB WH	220-240 V	32.2 W
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	220 to 240 V	50.2 W
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	220 to 240 V	32.2 W
910629132426	4MX900 LED40S/840 PSD WB WH L1200	220 to 240 V	25.9 W
910629132526	4MX900 LED40S/840 PSD MB WH L1200	220 to 240 V	25.9 W
910629132626	4MX900 LED40S/840 PSD NB WH L1200	220 to 240 V	25.9 W
910629132726	4MX900 LED40S/840 PSD DA20 WH L1200	220 to 240 V	25.9 W
910629137226	4MX900 LED60S/840 PSD WB WH L1800	220 to 240 V	37.3 W
910629137326	4MX900 LED60S/840 PSD MB WH L1800	220 to 240 V	37.3 W
910629137426	4MX900 LED60S/840 PSD NB WH L1800	220 to 240 V	37.3 W
910629137526	4MX900 LED60S/840 PSD DA20 WH L1800	220 to 240 V	37.3 W
910629138826	4MX900 LED90S/840 PSD WB WH L1800	220 to 240 V	60.1 W
910629138926	4MX900 LED90S/840 PSD MB WH L1800	220 to 240 V	60.1 W
910629139026	4MX900 LED90S/840 PSD NB WH L1800	220 to 240 V	60.1 W
910629139126	4MX900 LED90S/840 PSD DA20 WH L1800	220 to 240 V	60.1 W
910629140426	4MX900 581 LED40S/840 PSU WB WH	220 to 240 V	25.2 W
910629140526	4MX900 581 LED40S/840 PSU MB WH	220 to 240 V	25.2 W
910629142026	4MX900 491 LED40S/840 PSU WB WH	220 to 240 V	25.2 W
910629142126	4MX900 491 LED40S/840 PSU MB WH	220 to 240 V	25.2 W
910629143226	4MX900 LED40S/840 PSU WB WH L1200	220 to 240 V	25.9 W
910629144426	4MX900 491 LED40S/840 PSD WB WH	220 to 240 V	25.2 W
910629144526	4MX900 491 LED40S/840 PSD MB WH	220 to 240 V	25.2 W
910629144626	4MX900 491 LED40S/840 PSD NB WH	220 to 240 V	25.2 W
910629144826	4MX900 491 LED50S/840 PSD WB WH	220 to 240 V	32.2 W
910629144926	4MX900 491 LED50S/840 PSD MB WH	220 to 240 V	32.2 W
910629145026	4MX900 491 LED50S/840 PSD NB WH	220 to 240 V	32.2 W
910629145126	4MX900 491 LED50S/840 PSD DA20 WH	220 to 240 V	32.2 W
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	220 to 240 V	25.9 W
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	220 to 240 V	37.3 W
910629145626	4MX900 581 LED40S/840 PSU A30 WH	220 to 240 V	25.2 W
910629145726	4MX900 581 LED50S/840 PSU A30 WH	220 to 240 V	32.2 W
910629145826	4MX900 491 LED40S/840 PSU A30 WH	220 to 240 V	25.2 W
910629145926	4MX900 491 LED50S/840 PSU A30 WH	220 to 240 V	32.2 W
910629146026	4MX900 581 LED50S/840 PSU WB WH	220 to 240 V	32.2 W
910629146126	4MX900 581 LED50S/840 PSU MB WH	220 to 240 V	32.2 W
910629146426	4MX900 491 LED50S/840 PSU WB WH	220 to 240 V	32.2 W
910629146526	4MX900 491 LED50S/840 PSU MB WH	220 to 240 V	32.2 W
910629146626	4MX900 491 LED50S/840 PSU NB WH	220 to 240 V	32.2 W
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	220 to 240 V	60.1 W
910629148326	4MX900 581 LED75S/840 PSU A30 WH	220 to 240 V	50.2 W
910629148526	4MX900 491 LED75S/840 PSU A30 WH	220 to 240 V	50.2 W
910629170126	4MX900 491 LED50S/840 PSU DA30 WH	220 to 240 V	32.2 W
910629170326	4MX900 491 LED75S/840 PSU WB WH	220 to 240 V	50.2 W
910629170426	4MX900 491 LED75S/840 PSU MB WH	220 to 240 V	50.2 W

Order Code	Full Product Name	Input Voltage	Power Consumption
910629170826	4MX900 581 LED75S/840 PSU WB WH	220 to 240 V	50.2 W
910629170926	4MX900 581 LED75S/840 PSU MB WH	220 to 240 V	50.2 W
910629171026	4MX900 581 LED75S/840 PSU NB WH	220 to 240 V	50.2 W
910629171326	4MX900 491 LED75S/840 PSD WB WH	220 to 240 V	50.2 W
910629171426	4MX900 491 LED75S/840 PSD MB WH	220 to 240 V	50.2 W
910629171526	4MX900 491 LED75S/840 PSD NB WH	220 to 240 V	50.2 W
910629171726	4MX900 491 LED75S/840 PSD DA20 WH	220 to 240 V	50.2 W
910629171826	4MX900 491 LED75S/840 PSD A30 WH	220 to 240 V	50.2 W
910629171926	4MX900 581 LED75S/840 PSD WB WH	220 to 240 V	50.2 W
910629172026	4MX900 581 LED75S/840 PSD MB WH	220 to 240 V	50.2 W
910629172126	4MX900 581 LED75S/840 PSD NB WH	220 to 240 V	50.2 W
910629172326	4MX900 581 LED75S/840 PSD DA20 WH	220 to 240 V	50.2 W
910629172426	4MX900 581 LED75S/840 PSD A30 WH	220 to 240 V	50.2 W

Order Code	Full Product Name	Input Voltage	Power Consumption
910629173226	4MX900 581 LED50S/840 PSD A30 WH	220 to 240 V	32.2 W
910629131626	4MX900 LED40S/840 PSD WB SI L1200	220 to 240 V	25.9 W
910629131926	4MX900 LED40S/840 PSD DA20 SI L1200	220 to 240 V	25.9 W
910629136426	4MX900 LED60S/840 PSD WB SI L1800	220 to 240 V	37.3 W
910629136726	4MX900 LED60S/840 PSD DA20 SI L1800	220 to 240 V	37.3 W
910629138026	4MX900 LED90S/840 PSD WB SI L1800	220 to 240 V	60.1 W
910629138126	4MX900 LED90S/840 PSD MB SI L1800	220 to 240 V	60.1 W
910629141226	4MX900 491 LED40S/840 PSU WB SI	220 to 240 V	25.2 W
910629141326	4MX900 491 LED40S/840 PSU MB SI	220 to 240 V	25.2 W
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	220 to 240 V	60.1 W
910629172926	4MX900 LED40S/840 PSU WB SI L1200	220 to 240 V	25.9 W
910629177526	4MX900 581 LED50S/840 PSU A30 SI	220 to 240 V	32.2 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	Yes
910500460293	4MX900 491 LED50S/840 PSD-CLO DA20 WH	Yes
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	Yes
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	Yes
910500460296	4MX900 491 LED50S/840 PSD DA20 WH C-2R	Yes
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	Yes
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	Yes
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	Yes
910500460301	4MX900 491 LED75S/840 PSD-CLO DA20 WH	Yes
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	Yes
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	Yes
910500460304	4MX900 491 LED75S/840 PSD DA20 WH C-2R	Yes
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	Yes
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	Yes
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	Yes
910500460308	4MX900 581 LED40S/840 PSD DA20 WH	Yes
910500460309	4MX900 581 LED40S/840 PSD MB WH	Yes
910500460310	4MX900 581 LED40S/840 PSD NB WH	Yes
910500460311	4MX900 581 LED40S/840 PSD WB WH	Yes
910500460312	4MX900 581 LED50S/840 PSD DA20 WH	Yes
910500460313	4MX900 581 LED50S/840 PSD-CLO DA20 WH	Yes

Order Code	Full Product Name	Dimmable
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	Yes
910500460315	4MX900 581 LED50S/840 PSD-CLO NB WH	Yes
910500460316	4MX900 581 LED50S/840 PSD DA20 WH C-2R	Yes
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	Yes
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	Yes
910500460320	4MX900 581 LED75S/840 PSD-CLO DA20 WH	Yes
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	Yes
910500460322	4MX900 581 LED75S/840 PSD DA20 WH C-2R	Yes
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	Yes
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	Yes
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	Yes
910500460358	4MX933 491 LED50S/840 PSU DA20 WH ELB3	No
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	No
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	No
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	No
910500460362	4MX933 491 LED50S/840 PSD DA20WHELB3C-2R	Yes
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	Yes
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	Yes
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	Yes
910500460370	4MX933 491 LED75S/840 PSD DA20WHELB3C-2R	Yes
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	Yes

Order Code	Full Product Name	Dimmable
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	Yes
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	Yes
910500460374	4MX933 581 LED50S/840 PSU DA20 WH ELB3	No
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	No
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	No
910500460378	4MX933 581 LED50S/840 PSD DA20WHELB3C-2R	Yes
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	Yes
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	Yes
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	Yes
910500460386	4MX933 581 LED75S/840 PSD DA20WHELB3C-2R	Yes
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	Yes
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	Yes
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	Yes
910629173126	4MX900 581 LED50S/840 PSD MB WH	Yes
910629177026	4MX900 581 LED50S/840 PSD WB WH	Yes
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	Yes
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	No
910629132426	4MX900 LED40S/840 PSD WB WH L1200	Yes
910629132526	4MX900 LED40S/840 PSD MB WH L1200	Yes
910629132626	4MX900 LED40S/840 PSD NB WH L1200	Yes
910629132726	4MX900 LED40S/840 PSD DA20 WH L1200	Yes
910629137226	4MX900 LED60S/840 PSD WB WH L1800	Yes
910629137326	4MX900 LED60S/840 PSD MB WH L1800	Yes
910629137426	4MX900 LED60S/840 PSD NB WH L1800	Yes
910629137526	4MX900 LED60S/840 PSD DA20 WH L1800	Yes
910629138826	4MX900 LED90S/840 PSD WB WH L1800	Yes
910629138926	4MX900 LED90S/840 PSD MB WH L1800	Yes
910629139026	4MX900 LED90S/840 PSD NB WH L1800	Yes
910629139126	4MX900 LED90S/840 PSD DA20 WH L1800	Yes
910629140426	4MX900 581 LED40S/840 PSU WB WH	No
910629140526	4MX900 581 LED40S/840 PSU MB WH	No
910629142026	4MX900 491 LED40S/840 PSU WB WH	No
910629142126	4MX900 491 LED40S/840 PSU MB WH	No
910629143226	4MX900 LED40S/840 PSU WB WH L1200	No
910629144426	4MX900 491 LED40S/840 PSD WB WH	Yes
910629144526	4MX900 491 LED40S/840 PSD MB WH	Yes
910629144626	4MX900 491 LED40S/840 PSD NB WH	Yes
910629144826	4MX900 491 LED50S/840 PSD WB WH	Yes
910629144926	4MX900 491 LED50S/840 PSD MB WH	Yes
910629145026	4MX900 491 LED50S/840 PSD NB WH	Yes
910629145126	4MX900 491 LED50S/840 PSD DA20 WH	Yes
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	Yes

Order Code	Full Product Name	Dimmable
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	Yes
910629145626	4MX900 581 LED40S/840 PSU A30 WH	No
910629145726	4MX900 581 LED50S/840 PSU A30 WH	No
910629145826	4MX900 491 LED40S/840 PSU A30 WH	No
910629145926	4MX900 491 LED50S/840 PSU A30 WH	No
910629146026	4MX900 581 LED50S/840 PSU WB WH	No
910629146126	4MX900 581 LED50S/840 PSU MB WH	No
910629146426	4MX900 491 LED50S/840 PSU WB WH	No
910629146526	4MX900 491 LED50S/840 PSU MB WH	No
910629146626	4MX900 491 LED50S/840 PSU NB WH	No
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	Yes
910629148326	4MX900 581 LED75S/840 PSU A30 WH	No
910629148526	4MX900 491 LED75S/840 PSU A30 WH	No
910629170126	4MX900 491 LED50S/840 PSU DA30 WH	No
910629170326	4MX900 491 LED75S/840 PSU WB WH	No
910629170426	4MX900 491 LED75S/840 PSU MB WH	No
910629170826	4MX900 581 LED75S/840 PSU WB WH	No
910629170926	4MX900 581 LED75S/840 PSU MB WH	No
910629171026	4MX900 581 LED75S/840 PSU NB WH	No
910629171326	4MX900 491 LED75S/840 PSD WB WH	Yes
910629171426	4MX900 491 LED75S/840 PSD MB WH	Yes
910629171526	4MX900 491 LED75S/840 PSD NB WH	Yes
910629171726	4MX900 491 LED75S/840 PSD DA20 WH	Yes
910629171826	4MX900 491 LED75S/840 PSD A30 WH	Yes
910629171926	4MX900 581 LED75S/840 PSD WB WH	Yes
910629172026	4MX900 581 LED75S/840 PSD MB WH	Yes
910629172126	4MX900 581 LED75S/840 PSD NB WH	Yes
910629172326	4MX900 581 LED75S/840 PSD DA20 WH	Yes
910629172426	4MX900 581 LED75S/840 PSD A30 WH	Yes
910629173226	4MX900 581 LED50S/840 PSD A30 WH	Yes
910629131626	4MX900 LED40S/840 PSD WB SI L1200	Yes
910629131926	4MX900 LED40S/840 PSD DA20 SI L1200	Yes
910629136426	4MX900 LED60S/840 PSD WB SI L1800	Yes
910629136726	4MX900 LED60S/840 PSD DA20 SI L1800	Yes
910629138026	4MX900 LED90S/840 PSD WB SI L1800	Yes
910629138126	4MX900 LED90S/840 PSD MB SI L1800	Yes
910629141226	4MX900 491 LED40S/840 PSU WB SI	No
910629141326	4MX900 491 LED40S/840 PSU MB SI	No
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	Yes
910629172926	4MX900 LED40S/840 PSU WB SI L1200	No
910629177526	4MX900 581 LED50S/840 PSU A30 SI	No

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	White
910500460293	4MX900 491 LED50S/840 PSD-CLO DA20 WH	White
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	White
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	White
910500460296	4MX900 491 LED50S/840 PSD DA20 WH C-2R	White
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	White

Order Code	Full Product Name	Housing Color
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	White
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	White
910500460301	4MX900 491 LED75S/840 PSD-CLO DA20 WH	White
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	White
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	White
910500460304	4MX900 491 LED75S/840 PSD DA20 WH C-2R	White

Maxos LED Performer

Order Code	Full Product Name	Housing Color
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	White
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	White
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	White
910500460308	4MX900 581 LED40S/840 PSD DA20 WH	White
910500460309	4MX900 581 LED40S/840 PSD MB WH	White
910500460310	4MX900 581 LED40S/840 PSD NB WH	White
910500460311	4MX900 581 LED40S/840 PSD WB WH	White
910500460312	4MX900 581 LED50S/840 PSD DA20 WH	White
910500460313	4MX900 581 LED50S/840 PSD-CLO DA20 WH	White
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	White
910500460315	4MX900 581 LED50S/840 PSD-CLO NB WH	White
910500460316	4MX900 581 LED50S/840 PSD DA20 WH C-2R	White
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	White
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	White
910500460320	4MX900 581 LED75S/840 PSD-CLO DA20 WH	White
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	White
910500460322	4MX900 581 LED75S/840 PSD DA20 WH C-2R	White
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	White
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	White
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	White
910500460358	4MX933 491 LED50S/840 PSU DA20 WH ELB3	White
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	White
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	White
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	White
910500460362	4MX933 491 LED50S/840 PSD DA20WHELB3C-2R	White
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	White
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	White
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	White
910500460370	4MX933 491 LED75S/840 PSD DA20WHELB3C-2R	White
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	White
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	White
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	White
910500460374	4MX933 581 LED50S/840 PSU DA20 WH ELB3	White
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	White
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	White
910500460378	4MX933 581 LED50S/840 PSD DA20WHELB3C-2R	White
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	White
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	White
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	White
910500460386	4MX933 581 LED75S/840 PSD DA20WHELB3C-2R	White
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	White
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	White
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	White
910629173126	4MX900 581 LED50S/840 PSD MB WH	White
910629177026	4MX900 581 LED50S/840 PSD WB WH	White
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	White
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	White
910629132426	4MX900 LED40S/840 PSD WB WH L1200	White
910629132526	4MX900 LED40S/840 PSD MB WH L1200	White
910629132626	4MX900 LED40S/840 PSD NB WH L1200	White
910629132726	4MX900 LED40S/840 PSD DA20 WH L1200	White
910629137226	4MX900 LED60S/840 PSD WB WH L1800	White

Order Code	Full Product Name	Housing Color
910629137326	4MX900 LED60S/840 PSD MB WH L1800	White
910629137426	4MX900 LED60S/840 PSD NB WH L1800	White
910629137526	4MX900 LED60S/840 PSD DA20 WH L1800	White
910629138826	4MX900 LED90S/840 PSD WB WH L1800	White
910629138926	4MX900 LED90S/840 PSD MB WH L1800	White
910629139026	4MX900 LED90S/840 PSD NB WH L1800	White
910629139126	4MX900 LED90S/840 PSD DA20 WH L1800	White
910629140426	4MX900 581 LED40S/840 PSU WB WH	White
910629140526	4MX900 581 LED40S/840 PSU MB WH	White
910629142026	4MX900 491 LED40S/840 PSU WB WH	White
910629142126	4MX900 491 LED40S/840 PSU MB WH	White
910629143226	4MX900 LED40S/840 PSU WB WH L1200	White
910629144426	4MX900 491 LED40S/840 PSD WB WH	White
910629144526	4MX900 491 LED40S/840 PSD MB WH	White
910629144626	4MX900 491 LED40S/840 PSD NB WH	White
910629144826	4MX900 491 LED50S/840 PSD WB WH	White
910629144926	4MX900 491 LED50S/840 PSD MB WH	White
910629145026	4MX900 491 LED50S/840 PSD NB WH	White
910629145126	4MX900 491 LED50S/840 PSD DA20 WH	White
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	White
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	White
910629145626	4MX900 581 LED40S/840 PSU A30 WH	White
910629145726	4MX900 581 LED50S/840 PSU A30 WH	White
910629145826	4MX900 491 LED40S/840 PSU A30 WH	White
910629145926	4MX900 491 LED50S/840 PSU A30 WH	White
910629146026	4MX900 581 LED50S/840 PSU WB WH	White
910629146126	4MX900 581 LED50S/840 PSU MB WH	White
910629146426	4MX900 491 LED50S/840 PSU WB WH	White
910629146526	4MX900 491 LED50S/840 PSU MB WH	White
910629146626	4MX900 491 LED50S/840 PSU NB WH	White
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	White
910629148326	4MX900 581 LED75S/840 PSU A30 WH	White
910629148526	4MX900 491 LED75S/840 PSU A30 WH	White
910629170126	4MX900 491 LED50S/840 PSU DA30 WH	White
910629170326	4MX900 491 LED75S/840 PSU WB WH	White
910629170426	4MX900 491 LED75S/840 PSU MB WH	White
910629170826	4MX900 581 LED75S/840 PSU WB WH	White
910629170926	4MX900 581 LED75S/840 PSU MB WH	White
910629171026	4MX900 581 LED75S/840 PSU NB WH	White
910629171326	4MX900 491 LED75S/840 PSD WB WH	White
910629171426	4MX900 491 LED75S/840 PSD MB WH	White
910629171526	4MX900 491 LED75S/840 PSD NB WH	White
910629171726	4MX900 491 LED75S/840 PSD DA20 WH	White
910629171826	4MX900 491 LED75S/840 PSD A30 WH	White
910629171926	4MX900 581 LED75S/840 PSD WB WH	White
910629172026	4MX900 581 LED75S/840 PSD MB WH	White
910629172126	4MX900 581 LED75S/840 PSD NB WH	White
910629172326	4MX900 581 LED75S/840 PSD DA20 WH	White
910629172426	4MX900 581 LED75S/840 PSD A30 WH	White
910629173226	4MX900 581 LED50S/840 PSD A30 WH	White
910629131626	4MX900 LED40S/840 PSD WB SI L1200	Silver
910629131926	4MX900 LED40S/840 PSD DA20 SI L1200	Silver

Order Code	Full Product Name	Housing Color
910629136426	4MX900 LED60S/840 PSD WB SI L1800	Silver
910629136726	4MX900 LED60S/840 PSD DA20 SI L1800	Silver
910629138026	4MX900 LED90S/840 PSD WB SI L1800	Silver
910629138126	4MX900 LED90S/840 PSD MB SI L1800	Silver
910629141226	4MX900 491 LED40S/840 PSU WB SI	Silver

Order Code	Full Product Name	Housing Color
910629141326	4MX900 491 LED40S/840 PSU MB SI	Silver
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	Silver
910629172926	4MX900 LED40S/840 PSU WB SI L1200	Silver
910629177526	4MX900 581 LED50S/840 PSU A30 SI	Silver

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	(0.38, 0.38) SDCM <3.5
910500460293	4MX900 491 LED50S/840 PSD-CLO DA20 WH	(0.38, 0.38) SDCM <3.5
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	(0.38, 0.38) SDCM <3.5
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	(0.38, 0.38) SDCM <3.5
910500460296	4MX900 491 LED50S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460301	4MX900 491 LED75S/840 PSD-CLO DA20 WH	(0.38, 0.38) SDCM <3.5
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	(0.38, 0.38) SDCM <3.5
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	(0.38, 0.38) SDCM <3.5
910500460304	4MX900 491 LED75S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460308	4MX900 581 LED40S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910500460309	4MX900 581 LED40S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910500460310	4MX900 581 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910500460311	4MX900 581 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910500460312	4MX900 581 LED50S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910500460313	4MX900 581 LED50S/840 PSD-CLO DA20 WH	(0.38, 0.38) SDCM <3.5
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	(0.38, 0.38) SDCM <3.5
910500460315	4MX900 581 LED50S/840 PSD-CLO NB WH	(0.38, 0.38) SDCM <3.5
910500460316	4MX900 581 LED50S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460320	4MX900 581 LED75S/840 PSD-CLO DA20 WH	(0.38, 0.38) SDCM <3.5
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	(0.38, 0.38) SDCM <3.5
910500460322	4MX900 581 LED75S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460358	4MX933 491 LED50S/840 PSU DA20 WH ELB3	(0.38, 0.38) SDCM <3.5
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460362	4MX933 491 LED50S/840 PSD DA20WHELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5

Order Code	Full Product Name	Initial chromaticity
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460370	4MX933 491 LED75S/840 PSD DA20WHELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460374	4MX933 581 LED50S/840 PSU DA20 WH ELB3	(0.38, 0.38) SDCM <3.5
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460378	4MX933 581 LED50S/840 PSD DA20WHELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460386	4MX933 581 LED75S/840 PSD DA20WHELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910629173126	4MX900 581 LED50S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910629177026	4MX900 581 LED50S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	(0.38, 0.38) SDCM <3.5
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	(0.38, 0.38) SDCM <3.5
910629132426	4MX900 LED40S/840 PSD WB WH L1200	(0.38, 0.38) SDCM <3.5
910629132526	4MX900 LED40S/840 PSD MB WH L1200	(0.38, 0.38) SDCM <3.5
910629132626	4MX900 LED40S/840 PSD NB WH L1200	(0.38, 0.38) SDCM <3.5
910629132726	4MX900 LED40S/840 PSD DA20 WH L1200	(0.38, 0.38) SDCM <3.5
910629137226	4MX900 LED60S/840 PSD WB WH L1800	(0.38, 0.38) SDCM <3.5
910629137326	4MX900 LED60S/840 PSD MB WH L1800	(0.38, 0.38) SDCM <3.5
910629137426	4MX900 LED60S/840 PSD NB WH L1800	(0.38, 0.38) SDCM <3.5
910629137526	4MX900 LED60S/840 PSD DA20 WH L1800	(0.38, 0.38) SDCM <3.5

Order Code	Full Product Name	Initial chromaticity
910629138826	4MX900 LED90S/840 PSD WB WH L1800	(0.38, 0.38) SDCM <3.5
910629138926	4MX900 LED90S/840 PSD MB WH L1800	(0.38, 0.38) SDCM <3.5
910629139026	4MX900 LED90S/840 PSD NB WH L1800	(0.38, 0.38) SDCM <3.5
910629139126	4MX900 LED90S/840 PSD DA20 WH L1800	(0.38, 0.38) SDCM <3.5
910629140426	4MX900 581 LED40S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
910629140526	4MX900 581 LED40S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
910629142026	4MX900 491 LED40S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
910629142126	4MX900 491 LED40S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
910629143226	4MX900 LED40S/840 PSU WB WH L1200	(0.38, 0.38) SDCM <3.5
910629144426	4MX900 491 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629144526	4MX900 491 LED40S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910629144626	4MX900 491 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629144826	4MX900 491 LED50S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629144926	4MX900 491 LED50S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910629145026	4MX900 491 LED50S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629145126	4MX900 491 LED50S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	(0.38, 0.38) SDCM <3.5
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	(0.38, 0.38) SDCM <3.5
910629145626	4MX900 581 LED40S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
910629145726	4MX900 581 LED50S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
910629145826	4MX900 491 LED40S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
910629145926	4MX900 491 LED50S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
910629146026	4MX900 581 LED50S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
910629146126	4MX900 581 LED50S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
910629146426	4MX900 491 LED50S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
910629146526	4MX900 491 LED50S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
910629146626	4MX900 491 LED50S/840 PSU NB WH	(0.38, 0.38) SDCM <3.5
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	(0.38, 0.38) SDCM <3.5
910629148326	4MX900 581 LED75S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5

Order Code	Full Product Name	Initial chromaticity
910629148526	4MX900 491 LED75S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
910629170126	4MX900 491 LED50S/840 PSU DA30 WH	(0.38, 0.38) SDCM <3.5
910629170326	4MX900 491 LED75S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
910629170426	4MX900 491 LED75S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
910629170826	4MX900 581 LED75S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
910629170926	4MX900 581 LED75S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
910629171026	4MX900 581 LED75S/840 PSU NB WH	(0.38, 0.38) SDCM <3.5
910629171326	4MX900 491 LED75S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629171426	4MX900 491 LED75S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910629171526	4MX900 491 LED75S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629171726	4MX900 491 LED75S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910629171826	4MX900 491 LED75S/840 PSD A30 WH	(0.38, 0.38) SDCM <3.5
910629171926	4MX900 581 LED75S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629172026	4MX900 581 LED75S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910629172126	4MX900 581 LED75S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629172326	4MX900 581 LED75S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910629172426	4MX900 581 LED75S/840 PSD A30 WH	(0.38, 0.38) SDCM <3.5
910629173226	4MX900 581 LED50S/840 PSD A30 WH	(0.38, 0.38) SDCM <3.5
910629131626	4MX900 LED40S/840 PSD WB SI L1200	(0.38, 0.38) SDCM <3.5
910629131926	4MX900 LED40S/840 PSD DA20 SI L1200	(0.38, 0.38) SDCM <3.5
910629136426	4MX900 LED60S/840 PSD WB SI L1800	(0.38, 0.38) SDCM <3.5
910629136726	4MX900 LED60S/840 PSD DA20 SI L1800	(0.38, 0.38) SDCM <3.5
910629138026	4MX900 LED90S/840 PSD WB SI L1800	(0.38, 0.38) SDCM <3.5
910629138126	4MX900 LED90S/840 PSD MB SI L1800	(0.38, 0.38) SDCM <3.5
910629141226	4MX900 491 LED40S/840 PSU WB SI	(0.38, 0.38) SDCM <3.5
910629141326	4MX900 491 LED40S/840 PSU MB SI	(0.38, 0.38) SDCM <3
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	(0.38, 0.38) SDCM <3.5
910629172926	4MX900 LED40S/840 PSU WB SI L1200	(0.38, 0.38) SDCM <3.5
910629177526	4MX900 581 LED50S/840 PSU A30 SI	(0.38, 0.38) SDCM <3.5

Application Conditions

Order Code	Full Product Name	Maximum dim level
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	1%
910500460293	4MX900 491 LED50S/840 PSD-CLO DA20 WH	1%
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	1%
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	1%
910500460296	4MX900 491 LED50S/840 PSD DA20 WH C-2R	1%
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	1%
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	1%
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	1%
910500460301	4MX900 491 LED75S/840 PSD-CLO DA20 WH	1%
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	1%
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	1%
910500460304	4MX900 491 LED75S/840 PSD DA20 WH C-2R	1%
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	1%
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	1%
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	1%
910500460308	4MX900 581 LED40S/840 PSD DA20 WH	1%
910500460309	4MX900 581 LED40S/840 PSD MB WH	1%
910500460310	4MX900 581 LED40S/840 PSD NB WH	1%

Order Code	Full Product Name	Maximum dim level
910500460311	4MX900 581 LED40S/840 PSD WB WH	1%
910500460312	4MX900 581 LED50S/840 PSD DA20 WH	1%
910500460313	4MX900 581 LED50S/840 PSD-CLO DA20 WH	1%
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	1%
910500460315	4MX900 581 LED50S/840 PSD-CLO NB WH	1%
910500460316	4MX900 581 LED50S/840 PSD DA20 WH C-2R	1%
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	1%
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	1%
910500460320	4MX900 581 LED75S/840 PSD-CLO DA20 WH	1%
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	1%
910500460322	4MX900 581 LED75S/840 PSD DA20 WH C-2R	1%
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	1%
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	1%
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	1%
910500460358	4MX933 491 LED50S/840 PSU DA20 WH ELB3	Not applicable
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	Not applicable
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	Not applicable
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	Not applicable

Maxos LED Performer

Order Code	Full Product Name	Maximum dim level
910500460362	4MX933 491 LED50S/840 PSD DA20WHELB3C-2R	1%
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	1%
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	1%
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	1%
910500460370	4MX933 491 LED75S/840 PSD DA20WHELB3C-2R	1%
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	1%
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	1%
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	1%
910500460374	4MX933 581 LED50S/840 PSU DA20 WH ELB3	Not applicable
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	Not applicable
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	Not applicable
910500460378	4MX933 581 LED50S/840 PSD DA20WHELB3C-2R	1%
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	1%
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	1%
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	1%
910500460386	4MX933 581 LED75S/840 PSD DA20WHELB3C-2R	1%
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	1%
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	1%
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	1%
910629173126	4MX900 581 LED50S/840 PSD MB WH	1%
910629177026	4MX900 581 LED50S/840 PSD WB WH	1%
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	1%
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	Not applicable
910629132426	4MX900 LED40S/840 PSD WB WH L1200	1%
910629132526	4MX900 LED40S/840 PSD MB WH L1200	1%
910629132626	4MX900 LED40S/840 PSD NB WH L1200	1%
910629132726	4MX900 LED40S/840 PSD DA20 WH L1200	1%
910629137226	4MX900 LED60S/840 PSD WB WH L1800	1%
910629137326	4MX900 LED60S/840 PSD MB WH L1800	1%
910629137426	4MX900 LED60S/840 PSD NB WH L1800	1%
910629137526	4MX900 LED60S/840 PSD DA20 WH L1800	1%
910629138826	4MX900 LED90S/840 PSD WB WH L1800	1%
910629138926	4MX900 LED90S/840 PSD MB WH L1800	1%
910629139026	4MX900 LED90S/840 PSD NB WH L1800	1%
910629139126	4MX900 LED90S/840 PSD DA20 WH L1800	1%
910629140426	4MX900 581 LED40S/840 PSU WB WH	Not applicable
910629140526	4MX900 581 LED40S/840 PSU MB WH	Not applicable
910629142026	4MX900 491 LED40S/840 PSU WB WH	Not applicable
910629142126	4MX900 491 LED40S/840 PSU MB WH	Not applicable
910629143226	4MX900 LED40S/840 PSU WB WH L1200	Not applicable
910629144426	4MX900 491 LED40S/840 PSD WB WH	1%
910629144526	4MX900 491 LED40S/840 PSD MB WH	1%
910629144626	4MX900 491 LED40S/840 PSD NB WH	1%
910629144826	4MX900 491 LED50S/840 PSD WB WH	1%
910629144926	4MX900 491 LED50S/840 PSD MB WH	1%

Order Code	Full Product Name	Maximum dim level
910629145026	4MX900 491 LED50S/840 PSD NB WH	1%
910629145126	4MX900 491 LED50S/840 PSD DA20 WH	1%
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	1%
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	1%
910629145626	4MX900 581 LED40S/840 PSU A30 WH	Not applicable
910629145726	4MX900 581 LED50S/840 PSU A30 WH	Not applicable
910629145826	4MX900 491 LED40S/840 PSU A30 WH	Not applicable
910629145926	4MX900 491 LED50S/840 PSU A30 WH	Not applicable
910629146026	4MX900 581 LED50S/840 PSU WB WH	Not applicable
910629146126	4MX900 581 LED50S/840 PSU MB WH	Not applicable
910629146426	4MX900 491 LED50S/840 PSU WB WH	Not applicable
910629146526	4MX900 491 LED50S/840 PSU MB WH	Not applicable
910629146626	4MX900 491 LED50S/840 PSU NB WH	Not applicable
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	1%
910629148326	4MX900 581 LED75S/840 PSU A30 WH	Not applicable
910629148526	4MX900 491 LED75S/840 PSU A30 WH	Not applicable
910629170126	4MX900 491 LED50S/840 PSU DA30 WH	Not applicable
910629170326	4MX900 491 LED75S/840 PSU WB WH	Not applicable
910629170426	4MX900 491 LED75S/840 PSU MB WH	Not applicable
910629170826	4MX900 581 LED75S/840 PSU WB WH	Not applicable
910629170926	4MX900 581 LED75S/840 PSU MB WH	Not applicable
910629171026	4MX900 581 LED75S/840 PSU NB WH	Not applicable
910629171326	4MX900 491 LED75S/840 PSD WB WH	1%
910629171426	4MX900 491 LED75S/840 PSD MB WH	1%
910629171526	4MX900 491 LED75S/840 PSD NB WH	1%
910629171726	4MX900 491 LED75S/840 PSD DA20 WH	1%
910629171826	4MX900 491 LED75S/840 PSD A30 WH	1%
910629171926	4MX900 581 LED75S/840 PSD WB WH	1%
910629172026	4MX900 581 LED75S/840 PSD MB WH	1%
910629172126	4MX900 581 LED75S/840 PSD NB WH	1%
910629172326	4MX900 581 LED75S/840 PSD DA20 WH	1%
910629172426	4MX900 581 LED75S/840 PSD A30 WH	1%
910629173226	4MX900 581 LED50S/840 PSD A30 WH	1%
910629131626	4MX900 LED40S/840 PSD WB SI L1200	1%
910629131926	4MX900 LED40S/840 PSD DA20 SI L1200	1%
910629136426	4MX900 LED60S/840 PSD WB SI L1800	1%
910629136726	4MX900 LED60S/840 PSD DA20 SI L1800	1%
910629138026	4MX900 LED90S/840 PSD WB SI L1800	1%
910629138126	4MX900 LED90S/840 PSD MB SI L1800	1%
910629141226	4MX900 491 LED40S/840 PSU WB SI	Not applicable
910629141326	4MX900 491 LED40S/840 PSU MB SI	Not applicable
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	1%
910629172926	4MX900 LED40S/840 PSU WB SI L1200	Not applicable
910629177526	4MX900 581 LED50S/840 PSU A30 SI	Not applicable

Polar Wide Diagrams



IFPS_4MX900 491 1xLED40S/830 PSD A30-Polar Normal (separate)



IFPS_4MX900 491 1xLED40S/830 PSD DA20-Polar Normal (separate)



IFPS_4MX900 491 1xLED40S/830 PSD MB-Polar Normal (separate)



IFPS_4MX900 491 1xLED40S/830 PSD WB-Polar Normal (separate)



IFPS_4MX900 491 1xLED40S/830 PSU MB-Polar Normal (separate)



IFPS_4MX900 491 1xLED40S/830 PSU NB-Polar Normal (separate)



IFPS_4MX900 491 1xLED40S/830 PSU WB-Polar Normal (separate)



IFPS_4MX900 491 1xLED40S/840 PSD A30-Polar Normal (separate)



IFPS_4MX900 491 1xLED40S/840 PSD DA20-Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 491 1xLED40S/840 PSD WB-Polar Normal (separate)



IFPS_4MX900 491 1xLED40S/840 PSU A30-Polar Normal (separate)



IFPS_4MX900 491 1xLED40S/840 PSU DA30-Polar Normal (separate)



IFPS_4MX900 491 1xLED40S/840 PSU MB-Polar Normal (separate)



IFPS_4MX900 491 1xLED40S/840 PSU WB-Polar Normal (separate)



IFPS_4MX900 491 1xLED50S/830 PSD A30-Polar Normal (separate)



IFPS_4MX900 491 1xLED50S/830 PSD DA20-Polar Normal (separate)



IFPS_4MX900 491 1xLED50S/830 PSD MB-Polar Normal (separate)



IFPS_4MX900 491 1xLED50S/830 PSD WB-Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 491 1xLED50S/830 PSU DA30- Polar Normal (separate)



IFPS_4MX900 491 1xLED50S/830 PSU NB- Polar Normal (separate)



IFPS_4MX900 491 1xLED50S/830 PSU WB- Polar Normal (separate)



IFPS_4MX900 491 1xLED50S/840 PSD DA20- Polar Normal (separate)



IFPS_4MX900 491 1xLED50S/840 PSD WB- Polar Normal (separate)



IFPS_4MX900 491 1xLED50S/840 PSU A30- Polar Normal (separate)



IFPS_4MX900 491 1xLED50S/840 PSU DA30- Polar Normal (separate)



IFPS_4MX900 491 1xLED50S/840 PSU NB- Polar Normal (separate)



IFPS_4MX900 491 1xLED71S/830 PSD A30- Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 491 1xLED71S/830 PSD MB-Polar Normal (separate)



IFPS_4MX900 491 1xLED71S/830 PSD NB-Polar Normal (separate)



IFPS_4MX900 491 1xLED71S/830 PSD WB-Polar Normal (separate)



IFPS_4MX900 491 1xLED71S/830 PSU A30-Polar Normal (separate)



IFPS_4MX900 491 1xLED75S/840 PSD A30-Polar Normal (separate)



IFPS_4MX900 491 1xLED75S/840 PSD DA20-Polar Normal (separate)



IFPS_4MX900 491 1xLED75S/840 PSD WB-Polar Normal (separate)



IFPS_4MX900 491 1xLED75S/840 PSU DA30-Polar Normal (separate)



IFPS_4MX900 491 1xLED75S/840 PSU WB-Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 581 1xLED40S/830 PSD DA20-Polar Normal (separate)



IFPS_4MX900 581 1xLED40S/830 PSD MB-Polar Normal (separate)



IFPS_4MX900 581 1xLED40S/830 PSD NB-Polar Normal (separate)



IFPS_4MX900 581 1xLED40S/830 PSU MB-Polar Normal (separate)



IFPS_4MX900 581 1xLED40S/830 PSU WB-Polar Normal (separate)



IFPS_4MX900 581 1xLED40S/840 PSD A30-Polar Normal (separate)



IFPS_4MX900 581 1xLED40S/840 PSD MB-Polar Normal (separate)



IFPS_4MX900 581 1xLED40S/840 PSD NB-Polar Normal (separate)



IFPS_4MX900 581 1xLED40S/840 PSD WB-Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 581 1xLED40S/840 PSU A30-Polar Normal (separate)



IFPS_4MX900 581 1xLED40S/840 PSU WB-Polar Normal (separate)



IFPS_4MX900 581 1xLED50S/830 PSD DA20-Polar Normal (separate)



IFPS_4MX900 581 1xLED50S/830 PSD MB-Polar Normal (separate)



IFPS_4MX900 581 1xLED50S/830 PSU NB-Polar Normal (separate)



IFPS_4MX900 581 1xLED50S/830 PSU WB-Polar Normal (separate)



IFPS_4MX900 581 1xLED50S/840 PSD A30-Polar Normal (separate)



IFPS_4MX900 581 1xLED50S/840 PSD DA20-Polar Normal (separate)



IFPS_4MX900 581 1xLED50S/840 PSU MB-Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 581 1xLED71S/830 PSD MB-Polar Normal (separate)



IFPS_4MX900 581 1xLED71S/830 PSD NB-Polar Normal (separate)



IFPS_4MX900 581 1xLED71S/830 PSU NB-Polar Normal (separate)



IFPS_4MX900 581 1xLED75S/840 PSD A30-Polar Normal (separate)



IFPS_4MX900 581 1xLED75S/840 PSD DA20-Polar Normal (separate)



IFPS_4MX900 581 1xLED75S/840 PSD MB-Polar Normal (separate)



IFPS_4MX900 581 1xLED75S/840 PSD NB-Polar Normal (separate)



IFPS_4MX900 581 1xLED75S/840 PSU A30-Polar Normal (separate)



IFPS_4MX900 L1200 1xLED32S/840 PSU WB-Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 L1200 1xLED40S/830 PSU WB-Polar Normal (separate)



IFPS_4MX900 L1200 1xLED40S/840 PSU WB-Polar Normal (separate)



IFPS_4MX900 L1200 1xLED57S/830 PSD MB-Polar Normal (separate)



IFPS_4MX900 L1200 1xLED57S/830 PSD NB-Polar Normal (separate)



IFPS_4MX900 L1200 1xLED57S/830 PSD WB-Polar Normal (separate)



IFPS_4MX900 L1200 1xLED57S/830 PSU WB-Polar Normal (separate)



IFPS_4MX900 L1200 1xLED60S/840 PSD DA20-Polar Normal (separate)



IFPS_4MX900 L1200 1xLED60S/840 PSD NB-Polar Normal (separate)



IFPS_4MX900 L1200 1xLED60S/840 PSD WB-Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 L1800 1xLED48S/830 PSD NB-Polar Normal (separate)



IFPS_4MX900 L1800 1xLED48S/840 PSD DA20-Polar Normal (separate)



IFPS_4MX900 L1800 1xLED48S/840 PSD NB-Polar Normal (separate)



IFPS_4MX900 L1800 1xLED48S/840 PSD WB-Polar Normal (separate)



IFPS_4MX900 L1800 1xLED60S/830 PSD A30-Polar Normal (separate)



IFPS_4MX900 L1800 1xLED60S/830 PSD MB-Polar Normal (separate)



IFPS_4MX900 L1800 1xLED60S/830 PSD NB-Polar Normal (separate)



IFPS_4MX900 L1800 1xLED60S/840 PSD DA20-Polar Normal (separate)



IFPS_4MX900 L1800 1xLED60S/840 PSD MB-Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 L1800 1xLED60S/840 PSD NB-Polar Normal (separate)



IFPS_4MX900 L1800 1xLED85S/830 PSD A30-Polar Normal (separate)



IFPS_4MX900 L1800 1xLED85S/830 PSD MB-Polar Normal (separate)



IFPS_4MX900 L1800 1xLED85S/830 PSD WB-Polar Normal (separate)



IFPS_4MX900 L1800 1xLED90S/840 PSD DA20-Polar Normal (separate)



IFPS_4MX900 L1800 1xLED90S/840 PSD NB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED40S/830 PSD A30-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED40S/830 PSD DA20-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED40S/830 PSD MB-Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 G3 491 1xLED40S/830 PSD NB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED40S/830 PSU A30-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED40S/830 PSU NB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED40S/830 PSU WB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED40S/840 PSD A30-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED40S/840 PSD DA20-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED40S/840 PSD NB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED40S/840 PSD WB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED40S/840 PSU MB-Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 G3 491 1xLED50S/830 PSD A30-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/830 PSD DA20-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/830 PSD NB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/830 PSD WB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/830 PSU DA30-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/830 PSU NB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/830 PSU WB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/840 PSD DA20-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/840 PSD MB-Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 G3 491 1xLED50S/840 PSD NB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/840 PSD WB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/840 PSU A30-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/840 PSU DA30-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/840 PSU MB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/840 PSU NB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/840 PSU WB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED71S/830 PSD A30-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED71S/830 PSD DA20-Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 G3 491 1xLED71S/830 PSU A30-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED71S/830 PSU DA30-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED75S/840 PSD A30-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED75S/840 PSD MB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED75S/840 PSD WB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED75S/840 PSU A30-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED75S/840 PSU DA30-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED75S/840 PSU MB-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED75S/840 PSU NB-Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 G3 581 1xLED40S/830 PSD A30-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED40S/830 PSD MB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED40S/830 PSD NB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED40S/830 PSU NB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED40S/840 PSD A30-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED40S/840 PSD MB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED40S/840 PSD NB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED40S/840 PSD WB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED40S/840 PSU A30-Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 G3 581 1xLED40S/840 PSU MB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED40S/840 PSU NB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED40S/840 PSU WB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED50S/830 PSD DA20-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED50S/830 PSU A30-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED50S/830 PSU MB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED50S/840 PSD MB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED50S/840 PSU MB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED71S/830 PSD A30-Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 G3 581 1xLED71S/830 PSD DA20-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED71S/830 PSD NB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED71S/830 PSD WB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED71S/830 PSU MB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED71S/830 PSU NB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED75S/840 PSD A30-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED75S/840 PSD DA20-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED75S/840 PSD NB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED75S/840 PSD WB-Polar Normal (separate)

Polar Wide Diagrams



IFPS_4MX900 G3 581 1xLED75S/840 PSU A30-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED75S/840 PSU MB-Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED75S/840 PSU WB-Polar Normal (separate)



IFPS_4MX900 G3 L1200 1xLED40S/830 PSD NB-Polar Normal (separate)



IFPS_4MX900 G3 L1200 1xLED40S/840 PSU WB-Polar Normal (separate)



IFPS_4MX900 G3 L1200 1xLED60S/840 PSU WB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED60S/830 PSD NB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED60S/830 PSD WB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED60S/840 PSD MB-Polar Normal (separate)

Maxos LED Performer

Polar Wide Diagrams



IFPS_4MX900 G3 L1800 1xLED60S/840 PSD
NB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED60S/840 PSD
WB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED85S/830 PSD
WB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED90S/840 PSD
NB-Polar Normal (separate)

© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.