# Maxos LED Performer – iluminação eficiente com precisão de linha

## Maxos LED Performer

Os clientes pretendem poupar energia e reduzir custos em comparação com o que estão habituados na iluminação convencional. Ao mesmo tempo, são necessárias excelentes condições de iluminação: em ambientes industriais, para garantir a segurança e a produtividade; e em ambientes de revenda, para realçar os produtos e atrair a atenção dos clientes. O Maxos LED Performer representa uma solução extremamente flexível que proporciona um consumo de energia reduzido e uma excelente distribuição lumínica com um nível de investimento atractivo.

### Benefícios

- Retorno extremamente rápido do investimento
- Sistema óptico inovador para um feixe de luz preciso
- Flexível em termos de versões adaptáveis, focos, alterações, acessórios

### Características

- Baixo consumo de energia em comparação com a iluminação fluorescente
- Excelente distribuição lumínica para uma menor dispersão da luz e com precisão nos planos horizontal e vertical
- Moódulos LED da Philips (Fortimo) de qualidade comprovada
- Possibilidade de montagem, em instalações novas ou adaptadas, numa calha Maxos
- Também disponível na versão de painel flexível 4MX800 ou na versão de eficiência elevada 4MX850

### Aplicação

- Supermercados
- Armazéns de mercadorias
- Instalações de produção

# Maxos LED Performer

## Versions

IPPR1 4MX900i 0001.JPG

## Desenho dimensional










## Detalhes do produto

IPDP_4MX900i_0001-Detail photo

IPDP_4MX900i_0003-Detail photo



## Detalhes do produto

IPDP_4MX900i_0011-Detail photo

# Maxos LED Performer

| Informações gerais | |
|---|---|
| **Marca CE** | Sim |
| **Driver incluído** | Sim |
| **Marca ENEC** | Marca ENEC |
| **Marca de inflamabilidade** | - |
| **Teste de resistência do cabo** | Temperatura 650 °C, duração 30 s |
| **Fonte de luz substituível** | Não |
| **Número de unidades de equipamento** | 1 unidade |
| **Código da família de produtos** | 4MX900 |
| **Caraterísticas técnicas da luz** | |
| **Ângulo de feixe da fonte de luz** | 120 ° |
| **Temperatura de cor correlacionada** | 4000 K |
| **Color rendering index (CRI)** | ≥80 |
| **Funcionamento e caraterísticas elétricas** | |
| **Tensão de entrada** | 220 a 240 V |
| **Frequência de linha** | 50 to 60 Hz |
| **Temperatura** | |
| **Amplo intervalo de temperatura ambiente** | -20 a +40 °C |
| **Aprovação e aplicação** | |
| **Classe de proteção IEC** | Classe de segurança I |
| **Código de proteção mecânica contra impactos** | IK02 |
| **Código de proteção de entrada** | IP40 |
| **Desempenho inicial (em conformidade com a IEC)** | |
| **Cromaticidade inicial** | (0.38, 0.38) SDCM <3.5 |
| **Tolerância do fluxo luminoso** | +/-10% |
| **Condições de aplicação** | |
| **Adequado para uma comutação aleatória** | Não aplicável |

## Informações gerais

| Order Code | Full Product Name | Código da família das lâmpadas |
|---|---|---|
| 97678499 | 4MX900 581 LED40S/840 PSD WB WH | - |
| 66444399 | 4MX900 LED60S/840 PSD WB WH L1800 | LED60S |
| 66445099 | 4MX900 LED60S/840 PSD MB WH L1800 | LED60S |
| 66446799 | 4MX900 LED60S/840 PSD NB WH L1800 | LED60S |
| 66447499 | 4MX900 LED60S/840 PSD DA20 WH L1800 | LED60S |
| 66460399 | 4MX900 LED90S/840 PSD WB WH L1800 | LED90S |
| 66461099 | 4MX900 LED90S/840 PSD MB WH L1800 | LED90S |
| 66462799 | 4MX900 LED90S/840 PSD NB WH L1800 | LED90S |
| 66463499 | 4MX900 LED90S/840 PSD DA20 WH L1800 | LED90S |
| 66476499 | 4MX900 581 LED40S/840 PSU WB WH | LED40S |
| 66477199 | 4MX900 581 LED40S/840 PSU MB WH | LED40S |
| 66492499 | 4MX900 491 LED40S/840 PSU WB WH | LED40S |
| 66493199 | 4MX900 491 LED40S/840 PSU MB WH | LED40S |
| 66624999 | 4MX900 491 LED40S/840 PSD WB WH | LED40S |
| 66625699 | 4MX900 491 LED40S/840 PSD MB WH | LED40S |
| 66628799 | 4MX900 491 LED50S/840 PSD WB WH | LED50S |
| 66637999 | 4MX900 581 LED50S/840 PSU A30 WH | LED50S |
| 66640999 | 4MX900 581 LED50S/840 PSU WB WH | LED50S |
| 66644799 | 4MX900 491 LED50S/840 PSU WB WH | LED50S |
| 66790199 | 4MX900 491 LED75S/840 PSU WB WH | LED75S |
| 66791899 | 4MX900 491 LED75S/840 PSU MB WH | LED75S |
| 66800799 | 4MX900 491 LED75S/840 PSD WB WH | LED75S |
| 66807699 | 4MX900 581 LED75S/840 PSD MB WH | LED75S |
| 66808399 | 4MX900 581 LED75S/840 PSD NB WH | LED75S |
| 66883099 | 4MX900 581 LED50S/840 PSD A30 WH | LED50S |
| 66436899 | 4MX900 LED60S/840 PSD WB SI L1800 | LED60S |
| 66439999 | 4MX900 LED60S/840 PSD DA20 SI L1800 | LED60S |
| 66452899 | 4MX900 LED90S/840 PSD WB SI L1800 | LED90S |
| 66453599 | 4MX900 LED90S/840 PSD MB SI L1800 | LED90S |
| 66484999 | 4MX900 491 LED40S/840 PSU WB SI | LED40S |

## Caraterísticas técnicas da luz

| Order Code | Full Product Name | Eficiência luminosa (nominal) (Nom.) | Fluxo Luminoso | Número de fontes de luz | Tipo de ótica |
|---|---|---|---|---|---|
| 97678499 | 4MX900 581 LED40S/840 PSD WB WH | 159 lm/W | 4.000 lm | - | Feixe largo |
| 66444399 | 4MX900 LED60S/840 PSD WB WH L1800 | 161 lm/W | 6.000 lm | 1 | Feixe largo |

| Order Code | Full Product Name | Eficiência luminosa (nominal) (Nom.) | Fluxo Luminoso | Número de fontes de luz | Tipo de ótica |
|---|---|---|---|---|---|
| 66445099 | 4MX900 LED60S/840 PSD MB WH L1800 | 161 lm/W | 6.000 lm | 1 | Feixe médio |
| 66446799 | 4MX900 LED60S/840 PSD NB WH L1800 | 161 lm/W | 6.000 lm | 1 | Feixe estreito |

# Maxos LED Performer

| Order Code | Full Product Name | Eficiência luminosa (nominal) (Nom.) | Fluxo Luminoso | Número de fontes de luz | Tipo de ótica |
|---|---|---|---|---|---|
| 66447499 | 4MX900 LED60S/840 PSD DA20 WH L1800 | 161 lm/W | 6.000 lm | 1 | Ótica assimétrica dupla 20° |
| 66460399 | 4MX900 LED90S/840 PSD WB WH L1800 | 150 lm/W | 9.000 lm | 1 | Feixe largo |
| 66461099 | 4MX900 LED90S/840 PSD MB WH L1800 | 150 lm/W | 9.000 lm | 1 | Feixe médio |
| 66462799 | 4MX900 LED90S/840 PSD NB WH L1800 | 150 lm/W | 9.000 lm | 1 | Feixe estreito |
| 66463499 | 4MX900 LED90S/840 PSD DA20 WH L1800 | 150 lm/W | 9.000 lm | 1 | Ótica assimétrica dupla 20° |
| 66476499 | 4MX900 581 LED40S/840 PSU WB WH | 159 lm/W | 4.000 lm | 1 | Feixe largo |
| 66477199 | 4MX900 581 LED40S/840 PSU MB WH | 159 lm/W | 4.000 lm | 1 | Feixe médio |
| 66492499 | 4MX900 491 LED40S/840 PSU WB WH | 159 lm/W | 4.000 lm | 1 | Feixe largo |
| 66493199 | 4MX900 491 LED40S/840 PSU MB WH | 159 lm/W | 4.000 lm | 1 | Feixe médio |
| 66624999 | 4MX900 491 LED40S/840 PSD WB WH | 159 lm/W | 4.000 lm | 1 | Feixe largo |
| 66625699 | 4MX900 491 LED40S/840 PSD MB WH | 159 lm/W | 4.000 lm | 1 | Feixe médio |
| 66628799 | 4MX900 491 LED50S/840 PSD WB WH | 155 lm/W | 5.000 lm | 1 | Feixe largo |
| 66637999 | 4MX900 581 LED50S/840 PSU A30 WH | 155 lm/W | 5.000 lm | 1 | Espelho assimétrico, ângulo do eixo de 30° |
| 66640999 | 4MX900 581 LED50S/840 PSU WB WH | 155 lm/W | 5.000 lm | 1 | Feixe largo |
| 66644799 | 4MX900 491 LED50S/840 PSU WB WH | 155 lm/W | 5.000 lm | 1 | Feixe largo |
| 66790199 | 4MX900 491 LED75S/840 PSU WB WH | 149 lm/W | 7.500 lm | 1 | Feixe largo |
| 66791899 | 4MX900 491 LED75S/840 PSU MB WH | 149 lm/W | 7.500 lm | 1 | Feixe médio |
| 66800799 | 4MX900 491 LED75S/840 PSD WB WH | 149 lm/W | 7.500 lm | 1 | Feixe largo |
| 66807699 | 4MX900 581 LED75S/840 PSD MB WH | 149 lm/W | 7.500 lm | 1 | Feixe médio |
| 66808399 | 4MX900 581 LED75S/840 PSD NB WH | 149 lm/W | 7.500 lm | 1 | Feixe estreito |
| 66883099 | 4MX900 581 LED50S/840 PSD A30 WH | 155 lm/W | 5.000 lm | 1 | Espelho assimétrico, ângulo do eixo de 30° |
| 66436899 | 4MX900 LED60S/840 PSD WB SI L1800 | 161 lm/W | 6.000 lm | 1 | Feixe largo |
| 66439999 | 4MX900 LED60S/840 PSD DA20 SI L1800 | 161 lm/W | 6.000 lm | 1 | Ótica assimétrica dupla 20° |
| 66452899 | 4MX900 LED90S/840 PSD WB SI L1800 | 150 lm/W | 9.000 lm | 1 | Feixe largo |
| 66453599 | 4MX900 LED90S/840 PSD MB SI L1800 | 150 lm/W | 9.000 lm | 1 | Feixe médio |
| 66484999 | 4MX900 491 LED40S/840 PSU WB SI | 159 lm/W | 4.000 lm | 1 | Feixe largo |

## Funcionamento e caraterísticas elétricas

| Order Code | Full Product Name | Consumo de Energia |
|---|---|---|
| 97678499 | 4MX900 581 LED40S/840 PSD WB WH | 25,2 W |
| 66444399 | 4MX900 LED60S/840 PSD WB WH L1800 | 37,3 W |
| 66445099 | 4MX900 LED60S/840 PSD MB WH L1800 | 37,3 W |
| 66446799 | 4MX900 LED60S/840 PSD NB WH L1800 | 37,3 W |
| 66447499 | 4MX900 LED60S/840 PSD DA20 WH L1800 | 37,3 W |

| Order Code | Full Product Name | Consumo de Energia |
|---|---|---|
| 66460399 | 4MX900 LED90S/840 PSD WB WH L1800 | 60,1 W |
| 66461099 | 4MX900 LED90S/840 PSD MB WH L1800 | 60,1 W |
| 66462799 | 4MX900 LED90S/840 PSD NB WH L1800 | 60,1 W |
| 66463499 | 4MX900 LED90S/840 PSD DA20 WH L1800 | 60,1 W |
| 66476499 | 4MX900 581 LED40S/840 PSU WB WH | 25,2 W |

| Order Code | Full Product Name | Consumo de Energia |
|---|---|---|
| 66477199 | 4MX900 581 LED40S/840 PSU MB WH | 25,2 W |
| 66492499 | 4MX900 491 LED40S/840 PSU WB WH | 25,2 W |
| 66493199 | 4MX900 491 LED40S/840 PSU MB WH | 25,2 W |
| 66624999 | 4MX900 491 LED40S/840 PSD WB WH | 25,2 W |
| 66625699 | 4MX900 491 LED40S/840 PSD MB WH | 25,2 W |
| 66628799 | 4MX900 491 LED50S/840 PSD WB WH | 32,2 W |
| 66637999 | 4MX900 581 LED50S/840 PSU A30 WH | 32,2 W |
| 66640999 | 4MX900 581 LED50S/840 PSU WB WH | 32,2 W |
| 66644799 | 4MX900 491 LED50S/840 PSU WB WH | 32,2 W |
| 66790199 | 4MX900 491 LED75S/840 PSU WB WH | 50,2 W |

| Order Code | Full Product Name | Consumo de Energia |
|---|---|---|
| 66791899 | 4MX900 491 LED75S/840 PSU MB WH | 50,2 W |
| 66800799 | 4MX900 491 LED75S/840 PSD WB WH | 50,2 W |
| 66807699 | 4MX900 581 LED75S/840 PSD MB WH | 50,2 W |
| 66808399 | 4MX900 581 LED75S/840 PSD NB WH | 50,2 W |
| 66883099 | 4MX900 581 LED50S/840 PSD A30 WH | 32,2 W |
| 66436899 | 4MX900 LED60S/840 PSD WB SI L1800 | 37,3 W |
| 66439999 | 4MX900 LED60S/840 PSD DA20 SI L1800 | 37,3 W |
| 66452899 | 4MX900 LED90S/840 PSD WB SI L1800 | 60,1 W |
| 66453599 | 4MX900 LED90S/840 PSD MB SI L1800 | 60,1 W |
| 66484999 | 4MX900 491 LED40S/840 PSU WB SI | 25,2 W |

## Controlos e regulação

| Order Code | Full Product Name | Regulável |
|---|---|---|
| 97678499 | 4MX900 581 LED40S/840 PSD WB WH | Sim |
| 66444399 | 4MX900 LED60S/840 PSD WB WH L1800 | Sim |
| 66445099 | 4MX900 LED60S/840 PSD MB WH L1800 | Sim |
| 66446799 | 4MX900 LED60S/840 PSD NB WH L1800 | Sim |
| 66447499 | 4MX900 LED60S/840 PSD DA20 WH L1800 | Sim |
| 66460399 | 4MX900 LED90S/840 PSD WB WH L1800 | Sim |
| 66461099 | 4MX900 LED90S/840 PSD MB WH L1800 | Sim |
| 66462799 | 4MX900 LED90S/840 PSD NB WH L1800 | Sim |
| 66463499 | 4MX900 LED90S/840 PSD DA20 WH L1800 | Sim |
| 66476499 | 4MX900 581 LED40S/840 PSU WB WH | Não |
| 66477199 | 4MX900 581 LED40S/840 PSU MB WH | Não |
| 66492499 | 4MX900 491 LED40S/840 PSU WB WH | Não |
| 66493199 | 4MX900 491 LED40S/840 PSU MB WH | Não |
| 66624999 | 4MX900 491 LED40S/840 PSD WB WH | Sim |
| 66625699 | 4MX900 491 LED40S/840 PSD MB WH | Sim |

| Order Code | Full Product Name | Regulável |
|---|---|---|
| 66628799 | 4MX900 491 LED50S/840 PSD WB WH | Sim |
| 66637999 | 4MX900 581 LED50S/840 PSU A30 WH | Não |
| 66640999 | 4MX900 581 LED50S/840 PSU WB WH | Não |
| 66644799 | 4MX900 491 LED50S/840 PSU WB WH | Não |
| 66790199 | 4MX900 491 LED75S/840 PSU WB WH | Não |
| 66791899 | 4MX900 491 LED75S/840 PSU MB WH | Não |
| 66800799 | 4MX900 491 LED75S/840 PSD WB WH | Sim |
| 66807699 | 4MX900 581 LED75S/840 PSD MB WH | Sim |
| 66808399 | 4MX900 581 LED75S/840 PSD NB WH | Sim |
| 66883099 | 4MX900 581 LED50S/840 PSD A30 WH | Sim |
| 66436899 | 4MX900 LED60S/840 PSD WB SI L1800 | Sim |
| 66439999 | 4MX900 LED60S/840 PSD DA20 SI L1800 | Sim |
| 66452899 | 4MX900 LED90S/840 PSD WB SI L1800 | Sim |
| 66453599 | 4MX900 LED90S/840 PSD MB SI L1800 | Sim |
| 66484999 | 4MX900 491 LED40S/840 PSU WB SI | Não |

## Características mecânicas e compartimento

| Order Code | Full Product Name | Cor do compartimento |
|---|---|---|
| 97678499 | 4MX900 581 LED40S/840 PSD WB WH | Branco |
| 66444399 | 4MX900 LED60S/840 PSD WB WH L1800 | Branco |
| 66445099 | 4MX900 LED60S/840 PSD MB WH L1800 | Branco |
| 66446799 | 4MX900 LED60S/840 PSD NB WH L1800 | Branco |
| 66447499 | 4MX900 LED60S/840 PSD DA20 WH L1800 | Branco |
| 66460399 | 4MX900 LED90S/840 PSD WB WH L1800 | Branco |
| 66461099 | 4MX900 LED90S/840 PSD MB WH L1800 | Branco |
| 66462799 | 4MX900 LED90S/840 PSD NB WH L1800 | Branco |
| 66463499 | 4MX900 LED90S/840 PSD DA20 WH L1800 | Branco |
| 66476499 | 4MX900 581 LED40S/840 PSU WB WH | Branco |
| 66477199 | 4MX900 581 LED40S/840 PSU MB WH | Branco |
| 66492499 | 4MX900 491 LED40S/840 PSU WB WH | Branco |
| 66493199 | 4MX900 491 LED40S/840 PSU MB WH | Branco |
| 66624999 | 4MX900 491 LED40S/840 PSD WB WH | Branco |
| 66625699 | 4MX900 491 LED40S/840 PSD MB WH | Branco |

| Order Code | Full Product Name | Cor do compartimento |
|---|---|---|
| 66628799 | 4MX900 491 LED50S/840 PSD WB WH | Branco |
| 66637999 | 4MX900 581 LED50S/840 PSU A30 WH | Branco |
| 66640999 | 4MX900 581 LED50S/840 PSU WB WH | Branco |
| 66644799 | 4MX900 491 LED50S/840 PSU WB WH | Branco |
| 66790199 | 4MX900 491 LED75S/840 PSU WB WH | Branco |
| 66791899 | 4MX900 491 LED75S/840 PSU MB WH | Branco |
| 66800799 | 4MX900 491 LED75S/840 PSD WB WH | Branco |
| 66807699 | 4MX900 581 LED75S/840 PSD MB WH | Branco |
| 66808399 | 4MX900 581 LED75S/840 PSD NB WH | Branco |
| 66883099 | 4MX900 581 LED50S/840 PSD A30 WH | Branco |
| 66436899 | 4MX900 LED60S/840 PSD WB SI L1800 | Prata |
| 66439999 | 4MX900 LED60S/840 PSD DA20 SI L1800 | Prata |
| 66452899 | 4MX900 LED90S/840 PSD WB SI L1800 | Prata |
| 66453599 | 4MX900 LED90S/840 PSD MB SI L1800 | Prata |
| 66484999 | 4MX900 491 LED40S/840 PSU WB SI | Prata |

## Condições de aplicação

| Order Code | Full Product Name | Nível de regulação máximo |
|---|---|---|
| 97678499 | 4MX900 581 LED40S/840 PSD WB WH | 1% |
| 66444399 | 4MX900 LED60S/840 PSD WB WH L1800 | 1% |
| 66445099 | 4MX900 LED60S/840 PSD MB WH L1800 | 1% |
| 66446799 | 4MX900 LED60S/840 PSD NB WH L1800 | 1% |
| 66447499 | 4MX900 LED60S/840 PSD DA20 WH L1800 | 1% |
| 66460399 | 4MX900 LED90S/840 PSD WB WH L1800 | 1% |
| 66461099 | 4MX900 LED90S/840 PSD MB WH L1800 | 1% |
| 66462799 | 4MX900 LED90S/840 PSD NB WH L1800 | 1% |
| 66463499 | 4MX900 LED90S/840 PSD DA20 WH L1800 | 1% |
| 66476499 | 4MX900 581 LED40S/840 PSU WB WH | Não aplicável |
| 66477199 | 4MX900 581 LED40S/840 PSU MB WH | Não aplicável |
| 66492499 | 4MX900 491 LED40S/840 PSU WB WH | Não aplicável |
| 66493199 | 4MX900 491 LED40S/840 PSU MB WH | Não aplicável |
| 66624999 | 4MX900 491 LED40S/840 PSD WB WH | 1% |
| 66625699 | 4MX900 491 LED40S/840 PSD MB WH | 1% |

| Order Code | Full Product Name | Nível de regulação máximo |
|---|---|---|
| 66628799 | 4MX900 491 LED50S/840 PSD WB WH | 1% |
| 66637999 | 4MX900 581 LED50S/840 PSU A30 WH | Não aplicável |
| 66640999 | 4MX900 581 LED50S/840 PSU WB WH | Não aplicável |
| 66644799 | 4MX900 491 LED50S/840 PSU WB WH | Não aplicável |
| 66790199 | 4MX900 491 LED75S/840 PSU WB WH | Não aplicável |
| 66791899 | 4MX900 491 LED75S/840 PSU MB WH | Não aplicável |
| 66800799 | 4MX900 491 LED75S/840 PSD WB WH | 1% |
| 66807699 | 4MX900 581 LED75S/840 PSD MB WH | 1% |
| 66808399 | 4MX900 581 LED75S/840 PSD NB WH | 1% |
| 66883099 | 4MX900 581 LED50S/840 PSD A30 WH | 1% |
| 66436899 | 4MX900 LED60S/840 PSD WB SI L1800 | 1% |
| 66439999 | 4MX900 LED60S/840 PSD DA20 SI L1800 | 1% |
| 66452899 | 4MX900 LED90S/840 PSD WB SI L1800 | 1% |
| 66453599 | 4MX900 LED90S/840 PSD MB SI L1800 | 1% |
| 66484999 | 4MX900 491 LED40S/840 PSU WB SI | Não aplicável |

## Polar Wide Diagrams




**IFPS_4MX900 491 1xLED40S/830 PSD MB-Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSD WB-Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSU MB-Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSU WB-Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSD WB-Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSU MB-Polar Normal (separate)**

## Polar Wide Diagrams




**IFPS_4MX900 491 1xLED40S/840 PSU WB-Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSD MB-Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSD WB-Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSU WB-Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/840 PSD WB-Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD MB-Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD WB-Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSD WB-Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSU WB-Polar Normal (separate)**

## Polar Wide Diagrams




**IFPS_4MX900 581 1xLED40S/830 PSD MB-Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSD NB-Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSU MB-Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSU WB-Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSD A30-Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSD MB-Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSD NB-Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSU A30-Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSU WB-Polar Normal (separate)**

## Polar Wide Diagrams




**IFPS_4MX900 581 1xLED50S/830 PSD MB-Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/830 PSU WB-Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/840 PSD A30-Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/840 PSU MB-Polar Normal (separate)**




**IFPS_4MX900 581 1xLED71S/830 PSD MB-Polar Normal (separate)**




**IFPS_4MX900 581 1xLED71S/830 PSD NB-Polar Normal (separate)**




**IFPS_4MX900 581 1xLED75S/840 PSD A30-Polar Normal (separate)**




**IFPS_4MX900 581 1xLED75S/840 PSD MB-Polar Normal (separate)**




**IFPS_4MX900 581 1xLED75S/840 PSD NB-Polar Normal (separate)**

## Polar Wide Diagrams




**IFPS_4MX900 581 1xLED75S/840 PSU A30-Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/830 PSD NB-Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/840 PSD DA20-Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/840 PSD NB-Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/840 PSD WB-Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/830 PSD MB-Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/830 PSD NB-Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/840 PSD DA20-Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/840 PSD MB-Polar Normal (separate)**

## Polar Wide Diagrams




IFPS_4MX900 L1800 1xLED60S/840 PSD NB-Polar Normal (separate)




IFPS_4MX900 L1800 1xLED85S/830 PSD MB-Polar Normal (separate)




IFPS_4MX900 L1800 1xLED85S/830 PSD WB-Polar Normal (separate)




IFPS_4MX900 L1800 1xLED90S/840 PSD DA20-Polar Normal (separate)




IFPS_4MX900 L1800 1xLED90S/840 PSD NB-Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/830 PSD MB-Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/830 PSU WB-Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/840 PSD WB-Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/840 PSU MB-Polar Normal (separate)

## Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED50S/830 PSD WB-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSU WB-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSD WB-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSU MB-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSU WB-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSD WB-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSU MB-Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/830 PSD A30-Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/830 PSD MB-Polar Normal (separate)**

## Polar Wide Diagrams




**IFPS_4MX900 G3 581 1xLED40S/830 PSD NB-Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSD A30-Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSD MB-Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSD NB-Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSD WB-Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU A30-Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU MB-Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU WB-Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED50S/830 PSU A30-Polar Normal (separate)**

## Polar Wide Diagrams




IFPS_4MX900 G3 581 1xLED50S/840 PSD MB-Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED71S/830 PSD A30-Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED71S/830 PSD NB-Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED75S/840 PSD A30-Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED75S/840 PSD NB-Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED75S/840 PSU A30-Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED75S/840 PSU WB-Polar Normal (separate)




IFPS_4MX900 G3 L1800 1xLED60S/830 PSD NB-Polar Normal (separate)




IFPS_4MX900 G3 L1800 1xLED60S/830 PSD WB-Polar Normal (separate)

# Maxos LED Performer

## Polar Wide Diagrams




**IFPS_4MX900 G3 L1800 1xLED60S/840 PSD**
**MB-Polar Normal (separate)**




**IFPS_4MX900 G3 L1800 1xLED60S/840 PSD**
**NB-Polar Normal (separate)**




**IFPS_4MX900 G3 L1800 1xLED60S/840 PSD**
**WB-Polar Normal (separate)**




**IFPS_4MX900 G3 L1800 1xLED85S/830 PSD**
**WB-Polar Normal (separate)**




**IFPS_4MX900 G3 L1800 1xLED90S/840 PSD**
**NB-Polar Normal (separate)**

© 2023 Signify Holding Todos os direitos reservados. A Signify não fornece quaisquer representações ou garantia relativamente à exatidão ou integridade das informações aqui incluídas e não será responsável por qualquer ação com base nas mesmas. As informações apresentadas neste documento não se destinam a qualquer oferta comercial e não constituem parte de qualquer proposta ou contrato, salvo acordo em contrário com a Signify. Todas as marcas comerciais registadas são propriedade da Signify Holding ou dos respetivos proprietários.