

Philips hue Personal  
Wireless Lighting  
Recessed spot light

**PHOENIX**  
white  
LED

31155/31/PH



# Light that matches your moments

## Connected to you

The Philips Hue Phoenix 4" downlight provides you with dimmable warm to cool white light to match your daily moments. Connect via the Hue bridge (not included) to your home WiFi network for effortless control via your smart device.

### Connect light to your life

- 4 light recipes for your daily activities

### Advanced ambience creation

- Advanced ambience creation with warm to cool white light
- LightDuo for double the Hue experience
- Effortless and smooth dimming without rewiring your home
- 3D texture for sparkling light effect

### Wireless connectivity

- Full control from your smart device with extended features
- Get light notifications to keep you connected
- Set lights to turn on and off when you're away from home
- Always up to date
- Connect up to 50 Hue bulbs and lamps

**PHILIPS**

Recessed spot light  
PHOENIX white, LED

# Highlights

## 4 light recipes



Get the best light for whatever you do. Philips Hue has captured the optimal light for your daily activities in 4 light recipes. "Energize" bathes you in cool and vibrant light for that extra boost. "Concentrate" enables you to focus and get your work done with finely tuned bright white light. "Read" gives the optimal warm white light that does not strain your eyes - perfect for that good read. "Relax" helps you to unwind with a soft glow of warm white light.

## All shades of white light




Set the right ambience for any moment with a range of beautiful, natural white LED light. Use the app on your smart device to set any shade of white light, from cool energizing daylight (6700K) to relaxing warm white light (2200K).

## Double the Hue experience


This Philips Hue light has two integrated independent light sources, so you can mix warm and cool white light to match your moment and set functional lighting for your activity at the same time.

## Smooth wireless dimming




Adjust the brightness of your Philips Hue lights easy and seamlessly via your smart device. No need to rewire your home or install a wall dimmer.

## 3D texture for sparkling light



Hue Phoenix has a 3D texture that enhances its looks and gives a pleasant diffusion of light. The surface of the lamp is covered with a hexagonal pattern that captures and reflects light, which creates a sparkling effect. The effect changes depending on your viewing angle, making Hue Phoenix a dynamic and eye-catching piece of decoration in your home, even when the lights are off.

## Control from your smart device




Connect this Philips Hue lamp with the Hue bridge and discover the full range of lighting possibilities. Control the Hue lamp wirelessly from any iOS or Android device via the Philips

3115531PH


Hue app or any third party app developed for Hue. Set timers, notifications, alarms, geofencing for soft security, and sync to your entertainment system for the full Hue experience.

## Timers & light notifications



Set your Philips Hue lights to notify you of incoming calls, messages, social media updates, appointments, the weather and other relevant communications received through your smart device. Through the IFTTT platform, you can set different behaviors for your lighting. Hue's ambient light notifications are a pleasant way to keep you informed and connected.

## Safety and security at home



Make it look like you are at home even when you are away. Set scheduled alarms or use timers to turn your lights on and off at fixed or random times. With online access, you can also control your home lighting directly via the app on your smart device. Enable geofencing in the app and your lights will automatically turn on or off when you enter or leave the house. Convenient and peace of mind - wherever you are.

# Specifications

## Design and finishing

- Material: synthetics, metal
- Color: white

## Product dimensions & weight

- Length: 14 cm
- Width: 8.4 cm
- Recessed distance: 10 cm
- Cut out length: 12.5 cm

## Technical specifications

- Mains power: Range 220 V - 240 V, 50-60 Hz
- Bulb technology: LED, Safety Extra Low Voltage
- Number of bulbs: 1
- Wattage bulb included: 5 W
- Maximum wattage replacement bulb: 5.5 W
- Light color: warm white
- Lamp lifetime up to: 20,000 hrs
- Fixture dimmable
- LED

- Built in LED
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated
- Light source equivalent to traditional bulb of: 31 W

## Service

- Warranty: 2 year(s)

## Packaging dimensions & weight

- Height: 14.8 cm
- Length: 14.3 cm
- Width: 9.3 cm

## Miscellaneous

- Especially designed for: Living- & Bedroom, Functional
- Style: Contemporary
- Type: Recessed spot light



Issue date 2015-02-18

Version: 1.0.1

12 NC: 9150 050 49301  
EAN: 87 18696 12662 2

© 2015 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)