Switch Start Metal Halide Standard

Switch Start Metal Halide Standard

High performance, Long life and Superior light quality. A compact, energy efficient metal halide lamp that provides crisp, sparkling light wih long life and high efficiency.

Features

- Long life up to 20,000 hours for 360 and 400 watt lamps.
- Up to 100 lumens per watt.

Application

- Ideal for industrial and retail high/low bays, and parking lots.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Switch Start Metal Halide Standard

Versions

LPPR D-MH-R BT56 CL

Dimensional drawing



Product	D	C (max)
MH1500/U 1/6PK	7 inch	15.4 inch

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.