

# MASTER LEDspot LV AR111

# MAS LEDspotLV D 11-50W 927 AR111 24D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV AR111 is an ideal retrofit solution for spot and general lighting applications in the hospitality and retail industry. It is particularly suitable for general lighting where the light is on all the time, such as creative accent lighting applications in shops, restaurants, hotels, and especially for galleries, exhibitions and museums. The robustly designed MASTER LEDspot LV AR111 offers various beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. MASTER LEDspot LV AR111 delivers huge energy savings and minimizes maintenance cost without any reduction in brightness.

# Product data

#### • General Information

 Cap-Base
 GX53 [ GX53]

 Nominal Lifetime (Nom)
 40000 h

 Switching Cycle
 50000X

 Technical Type
 11-50W

#### • Light Technical

Color Code 927 Beam Angle (Nom) 24° Light Distribution 24D [ Medium beam] Luminous Flux 620 Im (Nom) Luminous Flux 620 lm (Rated) (Nom) 2900 cd Luminous Intensity (Nom) Color Designation Warm White (WW) Rated Beam Angle Correlated Color 2700 K Temperature (Nom) Luminous Efficacy 56.36 lm/W (rated) (Nom) Color Consistency 6 steps

Color Rendering 90 Index (Nom) LImf At End Of 70 % Nominal Lifetime (Nom)

#### Operating and Electrical

Power (Rated) 11 W (Nom) Lamp Current (Nom) 1300 mA 50 W Wattage Equivalent Starting Time (Max) 0.5 s instant full light Warm Up Time To 60% Light (Nom) Power Factor (Nom) 0.7 Voltage (Nom) 12 V

#### • Temperature

T-Case Maximum 70 °C (Nom)

#### Controls and Dimming

Dimmable Yes



# **MASTER LEDspot LV AR111**

#### • Approval and Application

Suitable For Accent Lighting Energy Efficiency Label (EEL) Α

• Product Data

871869651488700 Full product code

Order product name MAS LEDspotLV D 11-50W 927


AR111 24D 8718696514887

EAN/UPC - Product 929001169802 Order code Numerator - Quan-

tity Per Pack Numerator - Packs 6


per outer box . Material Nr. (12NC) 929001169802 Net Weight (Piece) 0.360 kg

# Dimensional drawing



### LED D 11-50W 927 AR111 24D

MAS LEDspotLV D 11-50W 927 AR111 24D 111 mm 62.27 mm





© 2015 Koninklijke Philips N.V. (Royal Philips) All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.