

MASTER LEDspot LV AR111

MAS LEDspotLV D 20-100W 830 AR111 40D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV AR111 is an ideal retrofit solution for spot and general lighting applications in the hospitality and retail industry. It is particularly suitable for general lighting where the light is on all the time, such as creative accent lighting applications in shops, restaurants, hotels, and especially for galleries, exhibitions and museums. The robustly designed MASTER LEDspot LV AR111 offers various beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. MASTER LEDspot LV AR111 delivers huge energy savings and minimizes maintenance cost without any reduction in brightness.

Product data

• General Information

 Cap-Base
 GX53 [GX53]

 Nominal Lifetime (Nom)
 25000 h

 Switching Cycle
 50000X

 Technical Type
 20-100W

• Light Technical

Color Code 830 [CCT of 3000K] Beam Angle (Nom) 40 40D [Medium beam] Light Distribution Luminous Flux 1350 lm (Nom) Luminous Flux 1350 lm (Rated) (Nom) 2350 cd Luminous Intensity (Nom) Color Designation White (WH) Rated Beam Angle Correlated Color 3000 K Temperature (Nom) Luminous Efficacy 67.50 lm/W (rated) (Nom) Color Consistency 6 steps

Color Rendering Index (Nom) LImf At End Of Nominal Lifetime (Nom)

80 70 %

• Operating and Electrical

Power (Rated) 20 W (Nom) Lamp Current (Nom) 2400 mA 100 W Wattage Equivalent Starting Time (Max) 0.5 s instant full light Warm Up Time To 60% Light (Nom) Power Factor (Nom) 0.7 Voltage (Nom) 12 V

• Temperature

T-Case Maximum 80 °C (Nom)

Controls and Dimming

Dimmable Yes



MASTER LEDspot LV AR111

• Approval and Application

Suitable For Accent Yes

Lighting

• Product Data

Full product code 871869651528000

Order product name MAS LEDspotLV D 20-100W 830

AR111 40D


EAN/UPC - Product 8718696515280 Order code 929001171208

Numerator - Quantity Per Pack

Numerator - Packs per outer box

Material Nr. (12NC) 929001171208 Net Weight (Piece) 0.360 kg


Dimensional drawing



LED D 20-100W 830 AR111 40D

 Product
 D
 C

 MAS LEDspotLV D 20-100W 830 AR111 40D
 111 mm
 62.27 mm





© 2016 Koninklijke Philips N.V. (Royal Philips) All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.