Philips TrueLine suspended: True line of light

TrueLine, suspended

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine surface is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in surface and recess-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 140 lm/W and the option to upgrade to wireless connectivity and control.

Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

TrueLine, suspended

Features

- Highly-uniform lighting with excellent glare control (UGR<19, L65<3000cd/m2)
- Best-in-class efficacy up to 140 lm/W
- 3000K, 4000K, and Tunable White versions, all CRI>90
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options, including all accessories

Application

- Offices
- Education
- Retail

Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Versions

TrueLine-SP534P

SP530P with U4 BK sensor

TrueLine-SP530 L570 WH

TrueLine-SP530 L2810 BK

TrueLine Suspended black housing

TrueLine-Suspended-line-LF

TrueLine, suspended

Dimensional drawing



Dimensional drawing



TrueLine, suspended

Product details

TrueLine_Suspended-line-side-view

TrueLine_Suspended-line-top-view

TrueLine Suspended black housing

TrueLine_Suspended-top-view

TrueLine_Suspended-U3

TrueLine_Suspended-U0

TrueLine Suspended-SP530P-LF-power-cable-03

TrueLine-SP-line-U3

TrueLine, suspended

Product details

TrueLine Suspended black housing

SP530P U4 BK DPP

TrueLine_SM_SP-line-connectio-side-view-2

General Information	
CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Light Technical	
Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>90
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Operating and Electrical	
Line Frequency	50 to 60 Hz
Temperature	
Ambient temperature range	+10 to +40 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mech. impact protection code	IK02
Ingress protection code	IP20
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%
Application Conditions	
Maximum dim level	1%
Suitable for random switching	No

General Information

Order Code	Full Product Name	Number of gear units	Product family code
910505103203	SP532P LED47S/940 PSD LE1 PI5SM2L1410ALU	1 unit	SP532P
910505103206	SP534P LED34S/940 PSD LE1 PI5SM2L1130ALU	1 unit	SP534P
910505103210	SP532P LED29S/940 PSD LE1 PI5SM2L1410ALU	1 unit	SP532P
910505103213	SP534P LED43S/940 PSD LE1 PI5SM2L1410ALU	1 unit	SP534P
910505103246	SP530P LED17S/940 PSD LE2PI5 SM2 L570 BK	1 unit	SP530P
910505103248	SP532P LED24S/930 PSD LE2 PI5 SM2L570 BK	1 unit	SP532P
910505103161	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP533P
910505103162	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	1 unit	SP532P
910505103163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP530P
910505103164	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP532P
910505103165	SP530P LED25S/940 POE SW2 L1130 ALU	1 unit	SP530P
910505103166	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP531P
910505103167	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP530P
910505103168	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP532P
910505103169	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP532P
910505103170	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP532P
910505103171	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP530P
910505103172	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	1 unit	SP533P
910505103173	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	1 unit	SP532P
910505103174	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	1 unit	SP532P
910505103175	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	1 unit	SP532P
910505103176	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	1 unit	SP533P
910505103177	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP534P
910505103180	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP533P
910505103181	SP532P LED21S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP532P
910505103182	SP533P LED33S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP533P
910505103183	SP532P LED29S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP532P
910505103185	SP532P LED66S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP532P
910505103186	SP533P LED54S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP533P
910505103187	SP532P LED49S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP532P
910505103188	SP532P LED66S/940 PSD PI5 SM2 L1410 WH	1 unit	SP532P
910505103189	SP532P LED47S/940 PSD PI5 SM2 L1410 WH	1 unit	SP532P
910505103191	SP530P LED31S/940 POE U3 SW2 L1450 ALU	1 unit	SP530P
910505103192	SP530P LED40S/940 POE U3 SW2 L1170 ALU	1 unit	SP530P
910505103193	SP530P LED40S/940 POE U0 SW2 L1170 ALU	1 unit	SP530P
910505103194	SP530P LED43S/940 POE U0 SW2 L1450 ALU	1 unit	SP530P
910505103196	SP530P LED40S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP530P
910505103184	SP534P LED50S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP534P
910505103281	SP532P LED66S/TW9 SIA PI3 U4 L1450 BK	2 units	SP532P
910505103245	SP531P LED7S/940 PSD LE2 PI5 SM2 L570 WH	1 unit	SP531P
910505103249	SP533P LED12S/930 PSD LE2 PI5 SM2L570 WH	1 unit	SP533P
910505103256	SP530P LED30S/930 PSD LF1 PI5 L2250 BK	1 unit	SP530P
910505103282	SP530P LED50S/TW9 SIA SM2 U4 L2290 ALU	2 units	SP530P
910505103283	SP530P LED86S/TW9 SIA SM2 U4 L2850 ALU	2 units	SP532P
910505103257	SP531P LED30S/930 SRD U4LF1PI3 L2290 ALU	1 unit	SP531P
910505103260	SP532P LED72S/940 PSD PI5 SM2 L2250 ALU	1 unit	SP532P
910505103261	SP533P LED48S/940 PSD PI5 SM2 L2250 ALU	1 unit	SP533P
910505103263	SP533P LED82S/940 PSD PI5 SM2 L2250 ALU	1 unit	SP533P
910505103269	SP530P LED38S/930 PSD LF1 PI5 L2810 ALU	1 unit	SP530P
910505103273	SP532P LED58S/930 PSD LF1 PI5 L2810 ALU	1 unit	SP532P
910505103274	SP533P LED66S/930 PSD LF1 PI5 L2810 ALU	1 unit	SP533P

Order Code	Full Product Name	Number of gear units	Product family code
910505103258	SP530P LED50S/940 SRD U4 PI5 SM2L2290 BK	1 unit	SP530P
910505103262	SP532P LED98S/940 SRD U4 PI5 SM2L2290 BK	1 unit	SP532P
910505103270	SP530P LED62S/940 SRD U4 PI5 SM2L2850 BK	1 unit	SP530P
910505103244	SP530P LED7S/940 PSD LE2 PI5 SM2L570 ALU	1 unit	SP530P
910505103247	SP532P LED10S/930 PSD LE2 PI5 L570 ALU	1 unit	SP532P
910505103259	SP530P LED50S/930 PSD PI5 SM2 L2250 WH	1 unit	SP530P
910505103271	SP531P LED62S/930 PSD PI5 SM2L2810 WH	1 unit	SP531P
910505103272	SP532P LED94S/940 PSD PI5 SM2L2810 WH	1 unit	SP532P
910505103197	SP532P LED47S/940 PSD PI5 SM2 L1410 BK	1 unit	SP532P
910505103198	SP531P LED15S/940 PSD PI5 SM2 L1130 BK	1 unit	SP531P
910505103199	SP530P LED34S/940 PSD PI5 SM2 L1130 BK	1 unit	SP530P
910505103201	SP532P LED29S/930 PSD LF2 PI5 SM2L1410BK	1 unit	SP532P
910505103202	SP532P LED29S/940 PSD LF2 PI5 SM2L1410BK	1 unit	SP532P
910505103207	SP532P LED36S/940 PSD LF2 PI5SMTTL1130BK	1 unit	SP532P
910505103204	SP532P LED29S/940 PSD LF1 PI5SW2L1410ALU	1 unit	SP532P
910505103205	SP532P LED36S/940 PSD LF2 PI5SMTTL1130AL	1 unit	SP532P
910505103208	SP532P LED29S/940 PSD LF2 PI5 SM2L1410AL	1 unit	SP532P
910505103209	SP534P LED43S/940 PSD LF1 PI5SW2L1410ALU	1 unit	SP534P
910505103211	SP532P LED47S/940 PSD LF1 PI5SW2L1410ALU	1 unit	SP532P
910505103212	SP532P LED36S/940 PSD LF1 PI5SW2L1130ALU	1 unit	SP532P
910505103279	SP532P LED36S/TW9 DIA LF1 PI5 L1130 ALU	1 unit	SP532P
910505103280	SP533P LED33S/TW9 DIA LF1 PI5 L1410 ALU	2 units	SP533P
910505103214	SP532P LED47S/940 SRD U4 PI3 SM2L1450ALU	1 unit	SP532P
910505103215	SP530P LED40S/940 SRD U4 PI3 SM2L1170ALU	1 unit	SP530P
910505103216	SP532P LED66S/940 SRD U4 PI3 SM2L1450ALU	1 unit	SP532P

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910505103203	SP532P LED47S/940 PSD LE1 PI5SM2L1410ALU	4000 K	138 lm/W	4,700 lm	Wide beam
910505103206	SP534P LED34S/940 PSD LE1 PI5SM2L1130ALU	4000 K	131 lm/W	3,400 lm	Asymmetrical mirror
910505103210	SP532P LED29S/940 PSD LE1 PI5SM2L1410ALU	4000 K	138 lm/W	2,900 lm	Wide beam
910505103213	SP534P LED43S/940 PSD LE1 PI5SM2L1410ALU	4000 K	132 lm/W	4,300 lm	Asymmetrical mirror
910505103246	SP530P LED17S/940 PSD LE2PI5 SM2 L570 BK	4000 K	139 lm/W	1,700 lm	Wide beam
910505103248	SP532P LED24S/930 PSD LE2 PI5 SM2L570 BK	3000 K	132 lm/W	2,450 lm	Wide beam
910505103161	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	4000 K	115 lm/W	4,100 lm	Wide beam
910505103162	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	4000 K	138 lm/W	2,900 lm	Wide beam
910505103163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	4000 K	139 lm/W	5,000 lm	Wide beam
910505103164	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	4000 K	138 lm/W	4,700 lm	Wide beam

TrueLine, suspended

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910505103165	SP530P LED25S/940 POE SW2 L1130 ALU	4000 K	149 lm/W	2,500 lm	Wide beam
910505103166	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	4000 K	104 lm/W	1,500 lm	Wide beam
910505103167	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	4000 K	141 lm/W	4,300 lm	Wide beam
910505103168	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	4000 K	135 lm/W	7,700 lm	Wide beam
910505103169	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	4000 K	136 lm/W	3,600 lm	Wide beam
910505103170	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	4000 K	133 lm/W	5,800 lm	Wide beam
910505103171	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	4000 K	139 lm/W	3,400 lm	Wide beam
910505103172	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	3000 K	112 lm/W	3,300 lm	Wide beam
910505103173	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	3000 K	129 lm/W	4,950 lm	Wide beam
910505103174	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	3000 K	128 lm/W	7,700 lm	Wide beam
910505103175	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	4000 K	136 lm/W	3,600 lm	Wide beam
910505103176	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	3000 K	112 lm/W	3,300 lm	Wide beam
910505103177	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	4000 K	129 lm/W	4,000 lm	Asymmetrical mirror

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910505103180	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	4000 K	116 lm/W	2,400 lm	Wide beam
910505103181	SP532P LED21S/940 PSD PI5 SM2 L1130 ALU	4000 K	132 lm/W	2,100 lm	Wide beam
910505103182	SP533P LED33S/940 PSD PI5 SM2 L1410 ALU	4000 K	118 lm/W	3,300 lm	Wide beam
910505103183	SP532P LED29S/940 PSD PI5 SM2 L1410 ALU	4000 K	138 lm/W	2,900 lm	Wide beam
910505103185	SP532P LED66S/940 PSD PI5 SM2 L1410 ALU	4000 K	138 lm/W	6,600 lm	Wide beam
910505103186	SP533P LED54S/940 PSD PI5 SM2 L1410 ALU	4000 K	116 lm/W	5,400 lm	Wide beam
910505103187	SP532P LED49S/940 PSD PI5 SM2 L1130 ALU	4000 K	136 lm/W	4,950 lm	Wide beam
910505103188	SP532P LED66S/940 PSD PI5 SM2 L1410 WH	4000 K	138 lm/W	6,600 lm	Wide beam
910505103189	SP532P LED47S/940 PSD PI5 SM2 L1410 WH	4000 K	138 lm/W	4,700 lm	Wide beam
910505103191	SP530P LED31S/940 POE U3 SW2 L1450 ALU	4000 K	148 lm/W	3,100 lm	Wide beam
910505103192	SP530P LED40S/940 POE U3 SW2 L1170 ALU	4000 K	143 lm/W	4,000 lm	Wide beam
910505103193	SP530P LED40S/940 POE U0 SW2 L1170 ALU	4000 K	143 lm/W	4,000 lm	Wide beam
910505103194	SP530P LED43S/940 POE U0 SW2 L1450 ALU	4000 K	143 lm/W	4,300 lm	Wide beam

TrueLine, suspended

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910505103196	SP530P LED40S/940 PSD PI5 SM2 L1130 ALU	4000 K	140 lm/W	4,000 lm	Wide beam
910505103184	SP534P LED50S/940 PSD PI5 SM2 L1410 ALU	4000 K	130 lm/W	5,000 lm	Asymmetrical mirror
910505103281	SP532P LED66S/TW9 SIA PI3 U4 L1450 BK	Tunable white 2700-6500 K	116 lm/W	6,600 lm	Wide beam
910505103245	SP531P LED7S/940 PSD LE2 PI5 SM2 L570 WH	4000 K	104 lm/W	750 lm	Wide beam
910505103249	SP533P LED12S/930 PSD LE2 PI5 SM2L570 WH	3000 K	109 lm/W	1,200 lm	Wide beam
910505103256	SP530P LED30S/930 PSD LF1 PI5 L2250 BK	3000 K	130 lm/W	3,000 lm	Wide beam
910505103282	SP530P LED50S/TW9 SIA SM2 U4 L2290 ALU	Tunable white 2700-6500 K	125 lm/W	5,000 lm	Wide beam
910505103283	SP530P LED86S/TW9 SIA SM2 U4 L2850 ALU	Tunable white 2700-6500 K	121 lm/W	8,600 lm	Wide beam
910505103257	SP531P LED30S/930 SRD U4LF1PI3 L2290 ALU	3000 K	103 lm/W	3,000 lm	Wide beam
910505103260	SP532P LED72S/940 PSD PI5 SM2 L2250 ALU	4000 K	138 lm/W	7,200 lm	Wide beam
910505103261	SP533P LED48S/940 PSD PI5 SM2 L2250 ALU	4000 K	122 lm/W	4,800 lm	Wide beam
910505103263	SP533P LED82S/940 PSD PI5 SM2 L2250 ALU	4000 K	119 lm/W	8,200 lm	Wide beam
910505103269	SP530P LED38S/930 PSD LF1 PI5 L2810 ALU	3000 K	136 lm/W	3,800 lm	Wide beam
910505103273	SP532P LED58S/930 PSD LF1 PI5 L2810 ALU	3000 K	132 lm/W	5,800 lm	Wide beam
910505103274	SP533P LED66S/930 PSD LF1 PI5 L2810 ALU	3000 K	114 lm/W	6,600 lm	Wide beam
910505103258	SP530P LED50S/940 SRD U4 PI5 SM2L2290 BK	4000 K	139 lm/W	5,000 lm	Wide beam
910505103262	SP532P LED98S/940 SRD U4 PI5 SM2L2290 BK	4000 K	138 lm/W	9,800 lm	Wide beam
910505103270	SP530P LED62S/940 SRD U4 PI5 SM2L2850 BK	4000 K	141 lm/W	6,200 lm	Wide beam
910505103244	SP530P LED7S/940 PSD LE2 PI5 SM2L570 ALU	4000 K	125 lm/W	750 lm	Wide beam
910505103247	SP532P LED10S/930 PSD LE2 PI5 L570 ALU	3000 K	124 lm/W	1,050 lm	Wide beam
910505103259	SP530P LED50S/930 PSD PI5 SM2 L2250 WH	3000 K	133 lm/W	5,000 lm	Wide beam
910505103271	SP531P LED62S/930 PSD PI5 SM2L2810 WH	3000 K	135 lm/W	6,200 lm	Wide beam
910505103272	SP532P LED94S/940 PSD PI5 SM2L2810 WH	4000 K	140 lm/W	9,400 lm	Wide beam
910505103197	SP532P LED47S/940 PSD PI5 SM2 L1410 BK	4000 K	138 lm/W	4,700 lm	Wide beam
910505103198	SP531P LED15S/940 PSD PI5 SM2 L1130 BK	4000 K	104 lm/W	1,500 lm	Wide beam
910505103199	SP530P LED34S/940 PSD PI5 SM2 L1130 BK	4000 K	139 lm/W	3,400 lm	Wide beam
910505103201	SP532P LED29S/930 PSD	3000 K	132 lm/W	2,900 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
	LF2 PI5 SM2L1410BK				
910505103202	SP532P LED29S/940 PSD LF2 PI5 SM2L1410BK	4000 K	138 lm/W	2,900 lm	Wide beam
910505103207	SP532P LED36S/940 PSD LF2 PI5SMTTL1130BK	4000 K	136 lm/W	3,600 lm	Wide beam
910505103204	SP532P LED29S/940 PSD LF1 PI5SW2L1410ALU	4000 K	138 lm/W	2,900 lm	Wide beam
910505103205	SP532P LED36S/940 PSD LF2 PI5SMTTL1130AL	4000 K	136 lm/W	3,600 lm	Wide beam
910505103208	SP532P LED29S/940 PSD LF2 PI5 SM2L1410AL	4000 K	138 lm/W	2,900 lm	Wide beam
910505103209	SP534P LED43S/940 PSD LF1 PI5SW2L1410ALU	4000 K	132 lm/W	4,300 lm	Asymmetrical mirror
910505103211	SP532P LED47S/940 PSD	4000 K	138 lm/W	4,700 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
	LF1 PI5SW2L1410ALU				
910505103212	SP532P LED36S/940 PSD LF1 PI5SW2L1130ALU	4000 K	136 lm/W	3,600 lm	Wide beam
910505103279	SP532P LED36S/TW9 DIA LF1 PI5 L1130 ALU	Tunable white 2700-6500 K	124 lm/W	3,600 lm	Wide beam
910505103280	SP533P LED33S/TW9 DIA LF1 PI5 L1410 ALU	Tunable white 2700-6500 K	100 lm/W	3,300 lm	Wide beam
910505103214	SP532P LED47S/940 SRD U4 PI3 SM2L1450ALU	4000 K	138 lm/W	4,700 lm	Wide beam
910505103215	SP530P LED40S/940 SRD U4 PI3 SM2L1170ALU	4000 K	143 lm/W	4,000 lm	Wide beam
910505103216	SP532P LED66S/940 SRD U4 PI3 SM2L1450ALU	4000 K	139 lm/W	6,600 lm	Wide beam

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power Consumption
910505103203	SP532P LED47S/940 PSD LE1 PI5SM2L1410ALU	220 to 240 V	34 W
910505103206	SP534P LED34S/940 PSD LE1 PI5SM2L1130ALU	220 to 240 V	26 W
910505103210	SP532P LED29S/940 PSD LE1 PI5SM2L1410ALU	220 to 240 V	21 W
910505103213	SP534P LED43S/940 PSD LE1 PI5SM2L1410ALU	220 to 240 V	32.5 W
910505103246	SP530P LED17S/940 PSD LE2PI5 SM2 L570 BK	220 to 240 V	12.2 W
910505103248	SP532P LED24S/930 PSD LE2 PI5 SM2L570 BK	220 to 240 V	18.6 W
910505103161	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	35.5 W
910505103162	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	220 to 240 V	21 W

Order Code	Full Product Name	Input Voltage	Power Consumption
910505103163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	36 W
910505103164	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	34 W
910505103165	SP530P LED25S/940 POE SW2 L1130 ALU	51 to 54 V	16.8 W
910505103166	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	14.4 W
910505103167	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	30.5 W
910505103168	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	57 W
910505103169	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	26.5 W
910505103170	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	44 W

TrueLine, suspended

Order Code	Full Product Name	Input Voltage	Power Consumption
910505103171	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	24.5 W
910505103172	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	220 to 240 V	29.5 W
910505103173	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	220 to 240 V	38.5 W
910505103174	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	220 to 240 V	60 W
910505103175	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	220 to 240 V	26.5 W
910505103176	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	220 to 240 V	29.5 W
910505103177	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	31 W
910505103180	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	21 W
910505103181	SP532P LED21S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	16.4 W
910505103182	SP533P LED33S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	28 W
910505103183	SP532P LED29S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	21 W
910505103185	SP532P LED66S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	48 W
910505103186	SP533P LED54S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	46.5 W
910505103187	SP532P LED49S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	36.5 W
910505103188	SP532P LED66S/940 PSD PI5 SM2 L1410 WH	220 to 240 V	48 W
910505103189	SP532P LED47S/940 PSD PI5 SM2 L1410 WH	220 to 240 V	34 W
910505103191	SP530P LED31S/940 POE U3 SW2 L1450 ALU	51 to 54 V	21 W
910505103192	SP530P LED40S/940 POE U3 SW2 L1170 ALU	51 to 54 V	28 W
910505103193	SP530P LED40S/940 POE U0 SW2 L1170 ALU	51 to 54 V	28 W
910505103194	SP530P LED43S/940 POE U0 SW2 L1450 ALU	51 to 54 V	30 W
910505103196	SP530P LED40S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	28.5 W
910505103184	SP534P LED50S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	38.5 W
910505103281	SP532P LED66S/TW9 SIA PI3 U4 L1450 BK	220 to 240 V	57 W
910505103245	SP531P LED7S/940 PSD LE2 PI5 SM2 L570 WH	220 to 240 V	7.2 W
910505103249	SP533P LED12S/930 PSD LE2 PI5 SM2L570 WH	220 to 240 V	11 W

Order Code	Full Product Name	Input Voltage	Power Consumption
910505103256	SP530P LED30S/930 PSD LF1 PI5 L2250 BK	220 to 240 V	23 W
910505103282	SP530P LED50S/TW9 SIA SM2 U4 L2290 ALU	220 to 240 V	40 W
910505103283	SP530P LED86S/TW9 SIA SM2 U4 L2850 ALU	220 to 240 V	71 W
910505103257	SP531P LED30S/930 SRD U4LF1PI3 L2290 ALU	220 to 240 V	29 W
910505103260	SP532P LED72S/940 PSD PI5 SM2 L2250 ALU	220 to 240 V	52 W
910505103261	SP533P LED48S/940 PSD PI5 SM2 L2250 ALU	220 to 240 V	39.5 W
910505103263	SP533P LED82S/940 PSD PI5 SM2 L2250 ALU	220 to 240 V	69 W
910505103269	SP530P LED38S/930 PSD LF1 PI5 L2810 ALU	220 to 240 V	28 W
910505103273	SP532P LED58S/930 PSD LF1 PI5 L2810 ALU	220 to 240 V	44 W
910505103274	SP533P LED66S/930 PSD LF1 PI5 L2810 ALU	220 to 240 V	58 W
910505103258	SP530P LED50S/940 SRD U4 PI5 SM2L2290 BK	220 to 240 V	36 W
910505103262	SP532P LED98S/940 SRD U4 PI5 SM2L2290 BK	220 to 240 V	71 W
910505103270	SP530P LED62S/940 SRD U4 PI5 SM2L2850 BK	220 to 240 V	44 W
910505103244	SP530P LED7S/940 PSD LE2 PI5 SM2L570 ALU	220 to 240 V	6 W
910505103247	SP532P LED10S/930 PSD LE2 PI5 L570 ALU	220 to 240 V	8.5 W
910505103259	SP530P LED50S/930 PSD PI5 SM2 L2250 WH	220 to 240 V	37.5 W
910505103271	SP531P LED62S/930 PSD PI5 SM2L2810 WH	220 to 240 V	46 W
910505103272	SP532P LED94S/940 PSD PI5 SM2L2810 WH	220 to 240 V	67 W
910505103197	SP532P LED47S/940 PSD PI5 SM2 L1410 BK	220 to 240 V	34 W
910505103198	SP531P LED15S/940 PSD PI5 SM2 L1130 BK	220 to 240 V	14.4 W
910505103199	SP530P LED34S/940 PSD PI5 SM2 L1130 BK	220 to 240 V	24.5 W
910505103201	SP532P LED29S/930 PSD LF2 PI5 SM2L1410BK	220 to 240 V	22 W
910505103202	SP532P LED29S/940 PSD LF2 PI5 SM2L1410BK	220 to 240 V	21 W
910505103207	SP532P LED36S/940 PSD LF2 PI5SMTTL1130BK	220 to 240 V	26.5 W
910505103204	SP532P LED29S/940 PSD LF1 PI5SW2L1410ALU	220 to 240 V	21 W

Order Code	Full Product Name	Input Voltage	Power Consumption
910505103205	SP532P LED36S/940 PSD LF2 PI5SMTTL1130AL	220 to 240 V	26.5 W
910505103208	SP532P LED29S/940 PSD LF2 PI5 SM2L1410AL	220 to 240 V	21 W
910505103209	SP534P LED43S/940 PSD LF1 PI5SW2L1410ALU	220 to 240 V	32.5 W
910505103211	SP532P LED47S/940 PSD LF1 PI5SW2L1410ALU	220 to 240 V	34 W
910505103212	SP532P LED36S/940 PSD LF1 PI5SW2L1130ALU	220 to 240 V	26.5 W
910505103279	SP532P LED36S/TW9 DIA LF1 PI5 L1130 ALU	220 to 240 V	29 W
910505103280	SP533P LED33S/TW9 DIA LF1 PI5 L1410 ALU	220 to 240 V	33 W
910505103214	SP532P LED47S/940 SRD U4 PI3 SM2L1450ALU	220 to 240 V	34 W
910505103215	SP530P LED40S/940 SRD U4 PI3 SM2L1170ALU	220 to 240 V	28 W
910505103216	SP532P LED66S/940 SRD U4 PI3 SM2L1450ALU	220 to 240 V	47.5 W

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910505103203	SP532P LED47S/940 PSD LE1 PI5SM2L1410ALU	Aluminum
910505103206	SP534P LED34S/940 PSD LE1 PI5SM2L1130ALU	Aluminum
910505103210	SP532P LED29S/940 PSD LE1 PI5SM2L1410ALU	Aluminum
910505103213	SP534P LED43S/940 PSD LE1 PI5SM2L1410ALU	Aluminum
910505103246	SP530P LED17S/940 PSD LE2PI5 SM2 L570 BK	Black RAL 9004
910505103248	SP532P LED24S/930 PSD LE2 PI5 SM2L570 BK	Black RAL 9004
910505103161	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	Aluminum
910505103162	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	White RAL 9003
910505103163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	Aluminum
910505103164	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	Aluminum
910505103165	SP530P LED25S/940 POE SW2 L1130 ALU	Aluminum
910505103166	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	Aluminum
910505103167	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	Aluminum
910505103168	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	Aluminum
910505103169	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	Aluminum
910505103170	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	Aluminum
910505103171	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	Aluminum
910505103172	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	Aluminum
910505103173	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	Aluminum
910505103174	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	Aluminum
910505103175	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	White RAL 9003
910505103176	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	White RAL 9003
910505103177	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	Aluminum
910505103180	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	Aluminum
910505103181	SP532P LED21S/940 PSD PI5 SM2 L1130 ALU	Aluminum
910505103182	SP533P LED33S/940 PSD PI5 SM2 L1410 ALU	Aluminum
910505103183	SP532P LED29S/940 PSD PI5 SM2 L1410 ALU	Aluminum
910505103185	SP532P LED66S/940 PSD PI5 SM2 L1410 ALU	Aluminum
910505103186	SP533P LED54S/940 PSD PI5 SM2 L1410 ALU	Aluminum
910505103187	SP532P LED49S/940 PSD PI5 SM2 L1130 ALU	Aluminum
910505103188	SP532P LED66S/940 PSD PI5 SM2 L1410 WH	White RAL 9003
910505103189	SP532P LED47S/940 PSD PI5 SM2 L1410 WH	White RAL 9003
910505103191	SP530P LED31S/940 POE U3 SW2 L1450 ALU	Aluminum
910505103192	SP530P LED40S/940 POE U3 SW2 L1170 ALU	Aluminum
910505103193	SP530P LED40S/940 POE U0 SW2 L1170 ALU	Aluminum
910505103194	SP530P LED43S/940 POE U0 SW2 L1450 ALU	Aluminum
910505103196	SP530P LED40S/940 PSD PI5 SM2 L1130 ALU	Aluminum
910505103184	SP534P LED50S/940 PSD PI5 SM2 L1410 ALU	Aluminum
910505103281	SP532P LED66S/TW9 SIA PI3 U4 L1450 BK	Black RAL 9004
910505103245	SP531P LED7S/940 PSD LE2 PI5 SM2 L570 WH	White RAL 9003
910505103249	SP533P LED12S/930 PSD LE2 PI5 SM2L570 WH	White RAL 9003
910505103256	SP530P LED30S/930 PSD LF1 PI5 L2250 BK	Black RAL 9004
910505103282	SP530P LED50S/TW9 SIA SM2 U4 L2290 ALU	Aluminum
910505103283	SP530P LED86S/TW9 SIA SM2 U4 L2850 ALU	Aluminum
910505103257	SP531P LED30S/930 SRD U4LF1PI3 L2290 ALU	Aluminum
910505103260	SP532P LED72S/940 PSD PI5 SM2 L2250 ALU	Aluminum
910505103261	SP533P LED48S/940 PSD PI5 SM2 L2250 ALU	Aluminum
910505103263	SP533P LED82S/940 PSD PI5 SM2 L2250 ALU	Aluminum
910505103269	SP530P LED38S/930 PSD LF1 PI5 L2810 ALU	Aluminum
910505103273	SP532P LED58S/930 PSD LF1 PI5 L2810 ALU	Aluminum
910505103274	SP533P LED66S/930 PSD LF1 PI5 L2810 ALU	Aluminum
910505103258	SP530P LED50S/940 SRD U4 PI5 SM2L2290 BK	Black RAL 9004
910505103262	SP532P LED98S/940 SRD U4 PI5 SM2L2290 BK	Black RAL 9004
910505103270	SP530P LED62S/940 SRD U4 PI5 SM2L2850 BK	Black RAL 9004
910505103244	SP530P LED7S/940 PSD LE2 PI5 SM2L570 ALU	Aluminum
910505103247	SP532P LED10S/930 PSD LE2 PI5 L570 ALU	Aluminum
910505103259	SP530P LED50S/930 PSD PI5 SM2 L2250 WH	White RAL 9003
910505103271	SP531P LED62S/930 PSD PI5 SM2L2810 WH	White RAL 9003
910505103272	SP532P LED94S/940 PSD PI5 SM2L2810 WH	White RAL 9003
910505103197	SP532P LED47S/940 PSD PI5 SM2 L1410 BK	Black RAL 9004
910505103198	SP531P LED15S/940 PSD PI5 SM2 L1130 BK	Black RAL 9004
910505103199	SP530P LED34S/940 PSD PI5 SM2 L1130 BK	Black RAL 9004
910505103201	SP532P LED29S/930 PSD LF2 PI5 SM2L1410BK	Black RAL 9004
910505103202	SP532P LED29S/940 PSD LF2 PI5 SM2L1410BK	Black RAL 9004
910505103207	SP532P LED36S/940 PSD LF2 PI5SMTTL1130BK	Black RAL 9004
910505103204	SP532P LED29S/940 PSD LF1 PI5SW2L1410ALU	Aluminum
910505103205	SP532P LED36S/940 PSD LF2 PI5SMTTL1130AL	Aluminum
910505103208	SP532P LED29S/940 PSD LF2 PI5 SM2L1410AL	Aluminum
910505103209	SP534P LED43S/940 PSD LF1 PI5SW2L1410ALU	Aluminum
910505103211	SP532P LED47S/940 PSD LF1 PI5SW2L1410ALU	Aluminum
910505103212	SP532P LED36S/940 PSD LF1 PI5SW2L1130ALU	Aluminum
910505103279	SP532P LED36S/TW9 DIA LF1 PI5 L1130 ALU	Aluminum
910505103280	SP533P LED33S/TW9 DIA LF1 PI5 L1410 ALU	Aluminum
910505103214	SP532P LED47S/940 SRD U4 PI3 SM2L1450ALU	Aluminum

Order Code	Full Product Name	Housing Color
910505103215	SP530P LED40S/940 SRD U4 PI3 SM2L1170ALU	Aluminum

Order Code	Full Product Name	Housing Color
910505103216	SP532P LED66S/940 SRD U4 PI3 SM2L1450ALU	Aluminum

Approval and Application

Order Code	Full Product Name	Protection class IEC
910505103203	SP532P LED47S/940 PSD LE1 PI5SM2L1410ALU	Safety class I
910505103206	SP534P LED34S/940 PSD LE1 PI5SM2L1130ALU	Safety class I
910505103210	SP532P LED29S/940 PSD LE1 PI5SM2L1410ALU	Safety class I
910505103213	SP534P LED43S/940 PSD LE1 PI5SM2L1410ALU	Safety class I
910505103246	SP530P LED17S/940 PSD LE2PI5 SM2 L570 BK	Safety class I
910505103248	SP532P LED24S/930 PSD LE2 PI5 SM2L570 BK	Safety class I
910505103161	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103162	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	Safety class I
910505103163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	Safety class I
910505103164	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	Safety class I
910505103165	SP530P LED25S/940 POE SW2 L1130 ALU	Safety class III
910505103166	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103167	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	Safety class I
910505103168	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	Safety class I
910505103169	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103170	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103171	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103172	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	Safety class I
910505103173	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	Safety class I
910505103174	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	Safety class I
910505103175	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	Safety class I
910505103176	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	Safety class I
910505103177	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103180	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103181	SP532P LED21S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103182	SP533P LED33S/940 PSD PI5 SM2 L1410 ALU	Safety class I
910505103183	SP532P LED29S/940 PSD PI5 SM2 L1410 ALU	Safety class I
910505103185	SP532P LED66S/940 PSD PI5 SM2 L1410 ALU	Safety class I
910505103186	SP533P LED54S/940 PSD PI5 SM2 L1410 ALU	Safety class I
910505103187	SP532P LED49S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103188	SP532P LED66S/940 PSD PI5 SM2 L1410 WH	Safety class I
910505103189	SP532P LED47S/940 PSD PI5 SM2 L1410 WH	Safety class I
910505103191	SP530P LED31S/940 POE U3 SW2 L1450 ALU	Safety class III
910505103192	SP530P LED40S/940 POE U3 SW2 L1170 ALU	Safety class III
910505103193	SP530P LED40S/940 POE U0 SW2 L1170 ALU	Safety class III
910505103194	SP530P LED43S/940 POE U0 SW2 L1450 ALU	Safety class III
910505103196	SP530P LED40S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103184	SP534P LED50S/940 PSD PI5 SM2 L1410 ALU	Safety class I

Order Code	Full Product Name	Protection class IEC
910505103281	SP532P LED66S/TW9 SIA PI3 U4 L1450 BK	Safety class I
910505103245	SP531P LED7S/940 PSD LE2 PI5 SM2 L570 WH	Safety class I
910505103249	SP533P LED12S/930 PSD LE2 PI5 SM2L570 WH	Safety class I
910505103256	SP530P LED30S/930 PSD LF1 PI5 L2250 BK	Safety class I
910505103282	SP530P LED50S/TW9 SIA SM2 U4 L2290 ALU	Safety class I
910505103283	SP530P LED86S/TW9 SIA SM2 U4 L2850 ALU	Safety class I
910505103257	SP531P LED30S/930 SRD U4LF1PI3 L2290 ALU	Safety class I
910505103260	SP532P LED72S/940 PSD PI5 SM2 L2250 ALU	Safety class I
910505103261	SP533P LED48S/940 PSD PI5 SM2 L2250 ALU	Safety class I
910505103263	SP533P LED82S/940 PSD PI5 SM2 L2250 ALU	Safety class I
910505103269	SP530P LED38S/930 PSD LF1 PI5 L2810 ALU	Safety class I
910505103273	SP532P LED58S/930 PSD LF1 PI5 L2810 ALU	Safety class I
910505103274	SP533P LED66S/930 PSD LF1 PI5 L2810 ALU	Safety class I
910505103258	SP530P LED50S/940 SRD U4 PI5 SM2L2290 BK	Safety class I
910505103262	SP532P LED98S/940 SRD U4 PI5 SM2L2290 BK	Safety class I
910505103270	SP530P LED62S/940 SRD U4 PI5 SM2L2850 BK	Safety class I
910505103244	SP530P LED7S/940 PSD LE2 PI5 SM2L570 ALU	Safety class I
910505103247	SP532P LED10S/930 PSD LE2 PI5 L570 ALU	Safety class I
910505103259	SP530P LED50S/930 PSD PI5 SM2 L2250 WH	Safety class I
910505103271	SP531P LED62S/930 PSD PI5 SM2L2810 WH	Safety class I
910505103272	SP532P LED94S/940 PSD PI5 SM2L2810 WH	Safety class I
910505103197	SP532P LED47S/940 PSD PI5 SM2 L1410 BK	Safety class I
910505103198	SP531P LED15S/940 PSD PI5 SM2 L1130 BK	Safety class I
910505103199	SP530P LED34S/940 PSD PI5 SM2 L1130 BK	Safety class I
910505103201	SP532P LED29S/930 PSD LF2 PI5 SM2L1410BK	Safety class I
910505103202	SP532P LED29S/940 PSD LF2 PI5 SM2L1410BK	Safety class I
910505103207	SP532P LED36S/940 PSD LF2 PI5SMTTL1130BK	Safety class I
910505103204	SP532P LED29S/940 PSD LF1 PI5SW2L1410ALU	Safety class I
910505103205	SP532P LED36S/940 PSD LF2 PI5SMTTL1130AL	Safety class I
910505103208	SP532P LED29S/940 PSD LF2 PI5 SM2L1410AL	Safety class I
910505103209	SP534P LED43S/940 PSD LF1 PI5SW2L1410ALU	Safety class I
910505103211	SP532P LED47S/940 PSD LF1 PI5SW2L1410ALU	Safety class I
910505103212	SP532P LED36S/940 PSD LF1 PI5SW2L1130ALU	Safety class I
910505103279	SP532P LED36S/TW9 DIA LF1 PI5 L1130 ALU	Safety class I
910505103280	SP533P LED33S/TW9 DIA LF1 PI5 L1410 ALU	Safety class I
910505103214	SP532P LED47S/940 SRD U4 PI3 SM2L1450ALU	Safety class I
910505103215	SP530P LED40S/940 SRD U4 PI3 SM2L1170ALU	Safety class I
910505103216	SP532P LED66S/940 SRD U4 PI3 SM2L1450ALU	Safety class I

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.