The new generation of Mains T5 LEDtube lighting

MASTER LEDtube Mains T5

The new Philips Master LEDtube Mains T5 brings simplicity to your lighting project. You don't need to pay attention to the driver technology anymore. Thanks to a unique design, Philips MASTER LEDtube Mains T5 installs in luminaires operating on mains power connection. So simple to operate! . Perfectly safe, reliable & easy to install Philips MASTER LEDtube Mains T5 is the ideal alternative to standard fluorescent tubes to maximize value over lifetime with high energy saving and lower maintenance costs.

Benefits

- Reduced operational cost thanks to lower energy consumption
- Lower maintenance cost thanks to longer lifetime than conventional lamps
- Fastest and easiest way to upgrade existing luminaires to LED
- technology; completely safe product and installation process

Features

- Replacement of existing T5 lamps: operates with mains power connection
- Energy savings compared with fluorescent tubes
- Long lifetime
- No mercury

Application

- Offices, shops, classroms
- Industrial facilities and warehouses

Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube 1200mm HE 16.5W 830 T5	15.8 mm	19 mm	1,149 mm	1,156.1 mm	1,163.2 mm
MAS LEDtube 1200mm HE 16.5W 830 T5 EU	15.7 mm	19 mm	1,149 mm	1,156.1 mm	1,163.2 mm
MAS LEDtube 1200mm HE 16.5W 840 T5	15.8 mm	19 mm	1,149 mm	1,156.1 mm	1,163.2 mm
MAS LEDtube 1200mm HE 16.5W 840 T5 EU	15.7 mm	19 mm	1,149 mm	1,156.1 mm	1,163.2 mm
MAS LEDtube 1200mm HE 16.5W 865 T5	15.8 mm	19 mm	1,149 mm	1,156.1 mm	1,163.2 mm
MAS LEDtube 1200mm HE 16.5W 865 T5 EU	15.7 mm	19 mm	1,149 mm	1,156.1 mm	1,163.2 mm
MAS LEDtube 1200mm HO 26W 830 G5 VWV BR	15.8 mm	18.2 mm	1,149 mm	1,156.1 mm	1,163.2 mm
MAS LEDtube 1200mm HO 26W 830 T5	15.5 mm	17.1 mm	1,149 mm	1,156 mm	1,163 mm
MAS LEDtube 1200mm HO 26W 840 G5 VWV BR	15.8 mm	18.2 mm	1,149 mm	1,156.1 mm	1,163.2 mm
MAS LEDtube 1200mm HO 26W 840 T5	15.5 mm	17.1 mm	1,149 mm	1,156 mm	1,163 mm
MAS LEDtube 1200mm HO 26W 865 G5 VWV BR	15.8 mm	18.2 mm	1,149 mm	1,156.1 mm	1,163.2 mm
MAS LEDtube 1200mm HO 26W 865 T5	15.5 mm	17.1 mm	1,149 mm	1,156 mm	1,163 mm
MAS LEDtube 1500mm HE 20W 830 T5	15.8 mm	19 mm	1,449 mm	1,454.9 mm	1,463.2 mm
MAS LEDtube 1500mm HE 20W 830 T5 EU	15.7 mm	19 mm	1,449 mm	1,456.1 mm	1,463.2 mm
MAS LEDtube 1500mm HE 20W 840 T5	15.8 mm	19 mm	1,449 mm	1,454.9 mm	1,463.2 mm
MAS LEDtube 1500mm HE 20W 840 T5 EU	15.7 mm	19 mm	1,449 mm	1,456.1 mm	1,463.2 mm
MAS LEDtube 1500mm HE 20W 865 T5	15.8 mm	19 mm	1,449 mm	1,454.9 mm	1,463.2 mm
MAS LEDtube 1500mm HE 20W 865 T5 EU	15.7 mm	19 mm	1,449 mm	1,456.1 mm	1,463.2 mm
MAS LEDtube 1500mm HO 26W 830 T5	15.5 mm	17.1 mm	1,449 mm	1,456 mm	1,463 mm
MAS LEDtube 1500mm HO 26W 840 T5	15.5 mm	17.1 mm	1,449 mm	1,456 mm	1,463 mm
MAS LEDtube 1500mm HO 26W 865 T5	15.5 mm	17.1 mm	1,449 mm	1,456 mm	1,463 mm
MAS LEDtube 1500mm UO 36W 830 T5	15.5 mm	18.8 mm	1,449 mm	1,456.1 mm	1,463.2 mm
MAS LEDtube 1500mm UO 36W 840 T5	15.5 mm	18.8 mm	1,449 mm	1,456.1 mm	1,463.2 mm
MAS LEDtube 1500mm UO 36W 865 T5	15.5 mm	18.8 mm	1,449 mm	1,456.1 mm	1,463.2 mm
MAS LEDtube 600mm HE 8W 830 T5	15.8 mm	19 mm	549 mm	556.1 mm	563.2 mm

Dimensional drawing

Product	D1	D2	A1	A2	A3
MAS LEDtube 600mm HE 8W 830 T5 EU	15.7 mm	19 mm	549 mm	556.1 mm	563.2 mm
MAS LEDtube 600mm HE 8W 840 T5	15.8 mm	19 mm	549 mm	556.1 mm	563.2 mm
MAS LEDtube 600mm HE 8W 840 T5 EU	15.7 mm	19 mm	549 mm	556.1 mm	563.2 mm
MAS LEDtube 600mm HE 8W 865 T5	15.8 mm	19 mm	549 mm	556.1 mm	563.2 mm
MAS LEDtube 600mm HE 8W 865 T5 EU	15.7 mm	19 mm	549 mm	556.1 mm	563.2 mm
MAS LEDtube 600mm HO 10.5W 830 T5		19 mm	549 mm	556.1 mm	563.2 mm
MAS LEDtube 600mm HO 10.5W 840 T5		19 mm	549 mm	556.1 mm	563.2 mm
MAS LEDtube 600mm HO 10.5W 865 T5		19 mm	549 mm	556.1 mm	563.2 mm
MAS LEDtube 900mm HE 11.5W 830 T5 EU	15.7 mm	19 mm	849 mm	856.1 mm	863.2 mm
MAS LEDtube 900mm HE 11.5W 840 T5 EU	15.7 mm	19 mm	849 mm	856.1 mm	863.2 mm
MAS LEDtube 900mm HE 11.5W 865 T5 EU	15.7 mm	19 mm	849 mm	856.1 mm	863.2 mm
MAS LEDtube 900mm HO 18.5W 830 T5		19 mm	849 mm	856.1 mm	863.2 mm
MAS LEDtube 900mm HO 18.5W 840 T5		19 mm	849 mm	856.1 mm	863.2 mm
MAS LEDtube 900mm HO 18.5W 865 T5		19 mm	849 mm	856.1 mm	863.2 mm

General Information	
Cap-Base	G5
Switching Cycle	200,000
Light Technical	
Beam Angle (Nom)	200 degree(s)
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	T5

General Information

Order Code	Full Product Name	Nominal lifetime
929002474802	MAS LEDtube 1500mm UO 36W 830 T5	50,000 hour(s)
929002474902	MAS LEDtube 1500mm UO 36W 840 T5	50,000 hour(s)
929002475002	MAS LEDtube 1500mm UO 36W 865 T5	50,000 hour(s)
929001908502	MAS LEDtube 1200mm HO 26W 830 T5	50,000 hour(s)
929001908602	MAS LEDtube 1200mm HO 26W 840 T5	50,000 hour(s)
929001908702	MAS LEDtube 1200mm HO 26W 865 T5	50,000 hour(s)
929001908802	MAS LEDtube 1500mm HO 26W 830 T5	50,000 hour(s)
929001908902	MAS LEDtube 1500mm HO 26W 840 T5	50,000 hour(s)
929001909002	MAS LEDtube 1500mm HO 26W 865 T5	50,000 hour(s)
929002420608	MAS LEDtube 600mm HE 8W 830 T5	50,000 hour(s)
929002420708	MAS LEDtube 600mm HE 8W 840 T5	50,000 hour(s)
929002420808	MAS LEDtube 600mm HE 8W 865 T5	50,000 hour(s)
929002420908	MAS LEDtube 1200mm HE 16.5W 830 T5	50,000 hour(s)
929002421008	MAS LEDtube 1200mm HE 16.5W 840 T5	50,000 hour(s)
929002421108	MAS LEDtube 1200mm HE 16.5W 865 T5	50,000 hour(s)
929002421202	MAS LEDtube 1500mm HE 20W 830 T5 EU	50,000 hour(s)
929002421208	MAS LEDtube 1500mm HE 20W 830 T5	50,000 hour(s)

MASTER LEDtube Mains T5

Order Code	Full Product Name	Nominal lifetime
929002421302	MAS LEDtube 1500mm HE 20W 840 T5 EU	50,000 hour(s)
929002421308	MAS LEDtube 1500mm HE 20W 840 T5	50,000 hour(s)
929002421402	MAS LEDtube 1500mm HE 20W 865 T5 EU	50,000 hour(s)
929002421408	MAS LEDtube 1500mm HE 20W 865 T5	50,000 hour(s)
929003044102	MAS LEDtube 600mm HE 8W 830 T5 EU	50,000 hour(s)
929003044202	MAS LEDtube 600mm HE 8W 840 T5 EU	50,000 hour(s)
929003044302	MAS LEDtube 600mm HE 8W 865 T5 EU	50,000 hour(s)
929003044402	MAS LEDtube 1200mm HE 16.5W 830 T5 EU	50,000 hour(s)
929003044502	MAS LEDtube 1200mm HE 16.5W 840 T5 EU	50,000 hour(s)
929003044602	MAS LEDtube 1200mm HE 16.5W 865 T5 EU	50,000 hour(s)
929003532412	MAS LEDtube 1200mm HO 26W 830 G5 VWV BR	25,000 hour(s)
929003532512	MAS LEDtube 1200mm HO 26W 840 G5 VWV BR	25,000 hour(s)
929003532612	MAS LEDtube 1200mm HO 26W 865 G5 VWV BR	25,000 hour(s)
929003734002	MAS LEDtube 900mm HE 11.5W 830 T5 EU	50,000 hour(s)
929003734102	MAS LEDtube 900mm HE 11.5W 840 T5 EU	50,000 hour(s)
929003734202	MAS LEDtube 900mm HE 11.5W 865 T5 EU	50,000 hour(s)
929003734302	MAS LEDtube 600mm HO 10.5W 830 T5	50,000 hour(s)
929003734402	MAS LEDtube 600mm HO 10.5W 840 T5	50,000 hour(s)
929003734502	MAS LEDtube 600mm HO 10.5W 865 T5	50,000 hour(s)
929003734602	MAS LEDtube 900mm HO 18.5W 830 T5	50,000 hour(s)
929003734702	MAS LEDtube 900mm HO 18.5W 840 T5	50,000 hour(s)
929003734802	MAS LEDtube 900mm HO 18.5W 865 T5	50,000 hour(s)

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Code	Luminous Flux
929002474802	MAS LEDtube 1500mm UO 36W 830 T5	3000 K	830	5,200 lm
929002474902	MAS LEDtube 1500mm UO 36W 840 T5	4000 K	840	5,600 lm
929002475002	MAS LEDtube 1500mm UO 36W 865 T5	6500 K	865	5,600 lm
929001908502	MAS LEDtube 1200mm HO 26W 830 T5	3000 K	830	3,600 lm
929001908602	MAS LEDtube 1200mm HO 26W 840 T5	4000 K	840	3,900 lm
929001908702	MAS LEDtube 1200mm HO 26W 865 T5	6500 K	865	3,900 lm
929001908802	MAS LEDtube 1500mm HO 26W 830 T5	3000 K	830	3,600 lm
929001908902	MAS LEDtube 1500mm HO 26W 840 T5	4000 K	840	3,900 lm
929001909002	MAS LEDtube 1500mm HO 26W 865 T5	6500 K	865	3,900 lm
929002420608	MAS LEDtube 600mm HE 8W 830 T5	3000 K	830	1,000 lm
929002420708	MAS LEDtube 600mm HE 8W 840 T5	4000 K	840	1,050 lm
929002420808	MAS LEDtube 600mm HE 8W 865 T5	6500 K	865	1,050 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Code	Luminous Flux
929002420908	MAS LEDtube 1200mm HE 16.5W 830 T5	3000 K	830	2,300 lm
929002421008	MAS LEDtube 1200mm HE 16.5W 840 T5	4000 K	840	2,500 lm
929002421108	MAS LEDtube 1200mm HE 16.5W 865 T5	6500 K	865	2,500 lm
929002421202	MAS LEDtube 1500mm HE 20W 830 T5 EU	3000 K	830	2,800 lm
929002421208	MAS LEDtube 1500mm HE 20W 830 T5	3000 K	830	2,800 lm
929002421302	MAS LEDtube 1500mm HE 20W 840 T5 EU	4000 K	840	3,000 lm
929002421308	MAS LEDtube 1500mm HE 20W 840 T5	4000 K	840	3,000 lm
929002421402	MAS LEDtube 1500mm HE 20W 865 T5 EU	6500 K	865	3,000 lm
929002421408	MAS LEDtube 1500mm HE 20W 865 T5	6500 K	865	3,000 lm
929003044102	MAS LEDtube 600mm HE 8W 830 T5 EU	3000 K	830	1,000 lm
929003044202	MAS LEDtube 600mm HE 8W 840 T5 EU	4000 K	840	1,050 lm
929003044302	MAS LEDtube 600mm HE 8W 865 T5 EU	6500 K	865	1,050 lm

MASTER LEDtube Mains T5

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Code	Luminous Flux
929003044402	MAS LEDtube 1200mm HE 16.5W 830 T5 EU	3000 K	830	2,300 lm
929003044502	MAS LEDtube 1200mm HE 16.5W 840 T5 EU	4000 K	840	2,500 lm
929003044602	MAS LEDtube 1200mm HE 16.5W 865 T5 EU	6500 K	865	2,500 lm
929003532412	MAS LEDtube 1200mm HO 26W 830 G5 VWV BR	3000 K	830	3,700 lm
929003532512	MAS LEDtube 1200mm HO 26W 840 G5 VWV BR	4000 K	840	3,900 lm
929003532612	MAS LEDtube 1200mm HO 26W 865 G5 VWV BR	6500 K	865	3,900 lm
929003734002	MAS LEDtube 900mm HE 11.5W 830 T5 EU	3000 K	830	1,600 lm
929003734102	MAS LEDtube 900mm HE 11.5W 840 T5 EU	4000 K	840	1,700 lm
929003734202	MAS LEDtube 900mm HE 11.5W 865 T5 EU	6500 K	865	1,700 lm
929003734302	MAS LEDtube 600mm HO 10.5W 830 T5	3000 K	830	1,500 lm
929003734402	MAS LEDtube 600mm HO 10.5W 840 T5	4000 K	840	1,600 lm
929003734502	MAS LEDtube 600mm HO 10.5W 865 T5	6500 K	865	1,600 lm
929003734602	MAS LEDtube 900mm HO 18.5W 830 T5	3000 K	830	2,600 lm
929003734702	MAS LEDtube 900mm HO 18.5W 840 T5	4000 K	840	2,800 lm
929003734802	MAS LEDtube 900mm HO 18.5W 865 T5	6500 K	865	2,800 lm

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Voltage (Nom)	Power Consumption	Wattage Equivalent
929002474802	MAS LEDtube 1500mm UO 36W 830 T5	50 to 60 Hz	-	36 W	-
929002474902	MAS LEDtube 1500mm UO 36W 840 T5	50 to 60 Hz	-	36 W	-
929002475002	MAS LEDtube 1500mm UO 36W 865 T5	50 to 60 Hz	-	36 W	-
929001908502	MAS LEDtube 1200mm HO 26W 830 T5	50 to 60 Hz	-	26 W	-
929001908602	MAS LEDtube 1200mm HO 26W 840 T5	50 to 60 Hz	-	26 W	-
929001908702	MAS LEDtube 1200mm HO 26W 865 T5	50 to 60 Hz	-	26 W	-
929001908802	MAS LEDtube 1500mm HO 26W 830 T5	50 to 60 Hz	-	26 W	-
929001908902	MAS LEDtube 1500mm HO 26W 840 T5	50 to 60 Hz	-	26 W	-
929001909002	MAS LEDtube 1500mm HO 26W 865 T5	50 to 60 Hz	-	26 W	-
929002420608	MAS LEDtube 600mm HE 8W 830 T5	50 to 60 Hz	-	8 W	-
929002420708	MAS LEDtube 600mm HE 8W 840 T5	50 to 60 Hz	-	8 W	-
929002420808	MAS LEDtube 600mm HE 8W 865 T5	50 to 60 Hz	-	8 W	-
929002420908	MAS LEDtube 1200mm HE 16.5W 830 T5	50 to 60 Hz	-	16.5 W	-
929002421008	MAS LEDtube 1200mm HE 16.5W 840 T5	50 to 60 Hz	-	16.5 W	-
929002421108	MAS LEDtube 1200mm HE 16.5W 865 T5	50 to 60 Hz	-	16.5 W	-
929002421202	MAS LEDtube 1500mm HE 20W 830 T5 EU	50 to 60 Hz	-	20 W	-
929002421208	MAS LEDtube 1500mm HE 20W 830 T5	50 to 60 Hz	-	20 W	-
929002421302	MAS LEDtube 1500mm HE 20W 840 T5 EU	50 to 60 Hz	-	20 W	-

MASTER LEDtube Mains T5

Order Code	Full Product Name	Line Frequency	Voltage (Nom)	Power Consumption	Wattage Equivalent
929002421308	MAS LEDtube 1500mm HE 20W 840 T5	50 to 60 Hz	-	20 W	-
929002421402	MAS LEDtube 1500mm HE 20W 865 T5 EU	50 to 60 Hz	-	20 W	-
929002421408	MAS LEDtube 1500mm HE 20W 865 T5	50 to 60 Hz	-	20 W	-
929003044102	MAS LEDtube 600mm HE 8W 830 T5 EU	50 to 60 Hz	-	8 W	-
929003044202	MAS LEDtube 600mm HE 8W 840 T5 EU	50 to 60 Hz	-	8 W	-
929003044302	MAS LEDtube 600mm HE 8W 865 T5 EU	50 to 60 Hz	-	8 W	-
929003044402	MAS LEDtube 1200mm HE 16.5W 830 T5 EU	50 to 60 Hz	-	16.5 W	-
929003044502	MAS LEDtube 1200mm HE 16.5W 840 T5 EU	50 to 60 Hz	-	16.5 W	-
929003044602	MAS LEDtube 1200mm HE 16.5W 865 T5 EU	50 to 60 Hz	-	16.5 W	-
929003532412	MAS LEDtube 1200mm HO 26W 830 G5 VWV BR	-	-	26 W	54 W
929003532512	MAS LEDtube 1200mm HO 26W 840 G5 VWV BR	-	-	26 W	54 W
929003532612	MAS LEDtube 1200mm HO 26W 865 G5 VWV BR	-	-	26 W	54 W
929003734002	MAS LEDtube 900mm HE 11.5W 830 T5 EU	50 to 60 Hz	220 V	11.5 W	-
929003734102	MAS LEDtube 900mm HE 11.5W 840 T5 EU	50 to 60 Hz	220 V	11.5 W	-
929003734202	MAS LEDtube 900mm HE 11.5W 865 T5 EU	50 to 60 Hz	220 V	11.5 W	-
929003734302	MAS LEDtube 600mm HO 10.5W 830 T5	-	-	10.5 W	-
929003734402	MAS LEDtube 600mm HO 10.5W 840 T5	-	-	10.5 W	-
929003734502	MAS LEDtube 600mm HO 10.5W 865 T5	-	-	10.5 W	-
929003734602	MAS LEDtube 900mm HO 18.5W 830 T5	-	-	18.5 W	-
929003734702	MAS LEDtube 900mm HO 18.5W 840 T5	-	-	18.5 W	-
929003734802	MAS LEDtube 900mm HO 18.5W 865 T5	-	-	18.5 W	-

Temperature

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929002474802	MAS LEDtube 1500mm UO 36W 830 T5	-20 °C to 45 °C	75 °C
929002474902	MAS LEDtube 1500mm UO 36W 840 T5	-20 °C to 45 °C	75 °C
929002475002	MAS LEDtube 1500mm UO 36W 865 T5	-20 °C to 45 °C	75 °C
929001908502	MAS LEDtube 1200mm HO 26W 830 T5	-20 to +45 °C	65 °C
929001908602	MAS LEDtube 1200mm HO 26W 840 T5	-20 to +45 °C	65 °C
929001908702	MAS LEDtube 1200mm HO 26W 865 T5	-20 to +45 °C	65 °C
929001908802	MAS LEDtube 1500mm HO 26W 830 T5	-20 to +45 °C	65 °C
929001908902	MAS LEDtube 1500mm HO 26W 840 T5	-20 to +45 °C	65 °C

MASTER LEDtube Mains T5

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929001909002	MAS LEDtube 1500mm HO 26W 865 T5	-20 to +45 °C	65 °C
929002420608	MAS LEDtube 600mm HE 8W 830 T5	-20 °C to 45 °C	60 °C
929002420708	MAS LEDtube 600mm HE 8W 840 T5	-20 °C to 45 °C	60 °C
929002420808	MAS LEDtube 600mm HE 8W 865 T5	-20 °C to 45 °C	60 °C
929002420908	MAS LEDtube 1200mm HE 16.5W 830 T5	-20 °C to 45 °C	70 °C
929002421008	MAS LEDtube 1200mm HE 16.5W 840 T5	-20 °C to 45 °C	70 °C
929002421108	MAS LEDtube 1200mm HE 16.5W 865 T5	-20 °C to 45 °C	70 °C
929002421202	MAS LEDtube 1500mm HE 20W 830 T5 EU	-20 to +45 °C	55 °C
929002421208	MAS LEDtube 1500mm HE 20W 830 T5	-20 °C to 45 °C	75 °C
929002421302	MAS LEDtube 1500mm HE 20W 840 T5 EU	-20 to +45 °C	55 °C
929002421308	MAS LEDtube 1500mm HE 20W 840 T5	-20 °C to 45 °C	75 °C
929002421402	MAS LEDtube 1500mm HE 20W 865 T5 EU	-20 to +45 °C	55 °C
929002421408	MAS LEDtube 1500mm HE 20W 865 T5	-20 °C to 45 °C	75 °C
929003044102	MAS LEDtube 600mm HE 8W 830 T5 EU	-20 to +45 °C	50 °C
929003044202	MAS LEDtube 600mm HE 8W 840 T5 EU	-20 to +45 °C	50 °C
929003044302	MAS LEDtube 600mm HE 8W 865 T5 EU	-20 to +45 °C	50 °C
929003044402	MAS LEDtube 1200mm HE 16.5W 830 T5 EU	-20 to +45 °C	55 °C
929003044502	MAS LEDtube 1200mm HE 16.5W 840 T5 EU	-20 to +45 °C	55 °C
929003044602	MAS LEDtube 1200mm HE 16.5W 865 T5 EU	-20 to +45 °C	55 °C
929003532412	MAS LEDtube 1200mm HO 26W 830 G5 VWV BR	-20 to +45 °C	70 °C
929003532512	MAS LEDtube 1200mm HO 26W 840 G5 VWV BR	-20 to +45 °C	70 °C
929003532612	MAS LEDtube 1200mm HO 26W 865 G5 VWV BR	-20 to +45 °C	70 °C
929003734002	MAS LEDtube 900mm HE 11.5W 830 T5 EU	-20 to +45 °C	45 °C
929003734102	MAS LEDtube 900mm HE 11.5W 840 T5 EU	-20 to +45 °C	45 °C
929003734202	MAS LEDtube 900mm HE 11.5W 865 T5 EU	-20 to +45 °C	45 °C
929003734302	MAS LEDtube 600mm HO 10.5W 830 T5	-20 to +45 °C	60 °C
929003734402	MAS LEDtube 600mm HO 10.5W 840 T5	-20 to +45 °C	60 °C
929003734502	MAS LEDtube 600mm HO 10.5W 865 T5	-20 to +45 °C	60 °C
929003734602	MAS LEDtube 900mm HO 18.5W 830 T5	-20 to +45 °C	60 °C
929003734702	MAS LEDtube 900mm HO 18.5W 840 T5	-20 to +45 °C	60 °C
929003734802	MAS LEDtube 900mm HO 18.5W 865 T5	-20 to +45 °C	60 °C

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929002474802	MAS LEDtube 1500mm UO 36W 830 T5	36 kWh
929002474902	MAS LEDtube 1500mm UO 36W 840 T5	36 kWh
929002475002	MAS LEDtube 1500mm UO 36W 865 T5	36 kWh
929001908502	MAS LEDtube 1200mm HO 26W 830 T5	26 kWh
929001908602	MAS LEDtube 1200mm HO 26W 840 T5	26 kWh
929001908702	MAS LEDtube 1200mm HO 26W 865 T5	26 kWh
929001908802	MAS LEDtube 1500mm HO 26W 830 T5	26 kWh
929001908902	MAS LEDtube 1500mm HO 26W 840 T5	26 kWh
929001909002	MAS LEDtube 1500mm HO 26W 865 T5	26 kWh
929002420608	MAS LEDtube 600mm HE 8W 830 T5	8 kWh
929002420708	MAS LEDtube 600mm HE 8W 840 T5	8 kWh
929002420808	MAS LEDtube 600mm HE 8W 865 T5	8 kWh
929002420908	MAS LEDtube 1200mm HE 16.5W 830 T5	17 kWh
929002421008	MAS LEDtube 1200mm HE 16.5W 840 T5	17 kWh
929002421108	MAS LEDtube 1200mm HE 16.5W 865 T5	17 kWh
929002421202	MAS LEDtube 1500mm HE 20W 830 T5 EU	20 kWh
929002421208	MAS LEDtube 1500mm HE 20W 830 T5	20 kWh
929002421302	MAS LEDtube 1500mm HE 20W 840 T5 EU	20 kWh
929002421308	MAS LEDtube 1500mm HE 20W 840 T5	20 kWh
929002421402	MAS LEDtube 1500mm HE 20W 865 T5 EU	20 kWh
929002421408	MAS LEDtube 1500mm HE 20W 865 T5	20 kWh
929003044102	MAS LEDtube 600mm HE 8W 830 T5 EU	8 kWh
929003044202	MAS LEDtube 600mm HE 8W 840 T5 EU	8 kWh
929003044302	MAS LEDtube 600mm HE 8W 865 T5 EU	8 kWh
929003044402	MAS LEDtube 1200mm HE 16.5W 830 T5 EU	17 kWh
929003044502	MAS LEDtube 1200mm HE 16.5W 840 T5 EU	17 kWh

MASTER LEDtube Mains T5

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929003044602	MAS LEDtube 1200mm HE 16.5W 865 T5 EU	17 kWh
929003532412	MAS LEDtube 1200mm HO 26W 830 G5 VWV BR	-
929003532512	MAS LEDtube 1200mm HO 26W 840 G5 VWV BR	-
929003532612	MAS LEDtube 1200mm HO 26W 865 G5 VWV BR	-
929003734002	MAS LEDtube 900mm HE 11.5W 830 T5 EU	12 kWh
929003734102	MAS LEDtube 900mm HE 11.5W 840 T5 EU	12 kWh
929003734202	MAS LEDtube 900mm HE 11.5W 865 T5 EU	12 kWh
929003734302	MAS LEDtube 600mm HO 10.5W 830 T5	11 kWh
929003734402	MAS LEDtube 600mm HO 10.5W 840 T5	11 kWh
929003734502	MAS LEDtube 600mm HO 10.5W 865 T5	11 kWh
929003734602	MAS LEDtube 900mm HO 18.5W 830 T5	19 kWh
929003734702	MAS LEDtube 900mm HO 18.5W 840 T5	19 kWh
929003734802	MAS LEDtube 900mm HO 18.5W 865 T5	19 kWh













MASTER LEDtube Mains T5



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.