The best LED replacement for HID and SON road lamps with MASTER - LED HID SON-T

MASTER - LED HID SON-T

Philips MASTER - LED HID SON-T lamps are an easy LED solution with a short payback period to replace High-Intensity Discharge (HID) and High-Pressure Sodium (SON) lamps. MASTER – LED HID SON-T solutions bring the energy efficiency and long lifetime benefits of LED to HID replacement, providing instant savings for a low initial investment. With the right lamp size and light distribution, you can easily retrofit MASTER – LED HID SON-T lamps into existing SON and SON-T systems, enhancing the lighting quality with LED without changing the luminaire's ballast (for IF replacements) or reflector.

Benefits

- Cost-saving lamps with short payback time
- Low initial investment
- Easy way to enhance lighting quality

Features

- High energy efficiency
- Long lifetime of 50,000 hours
- Right size and light distribution for retrofits
- Direct LED replacement, no need to change the luminaire
- Pleasant white light with CRI70
- Surge protection 6KV

MASTER - LED HID SON-T

Application

- Road and Street
- Tunnel
- Parking Garages

Warnings and Safety

- Please refer to the installation guide or consult a Philips Lighting representative for the wiring diagram and instructions.

Versions

Trueforce LED E27

LEDTrueForce E40 68W

LEDTForce Road GM T70 E39

Dimensional drawing



Product	D	C
MAS LED SON-T EM 10.8Klm 65W 727 E40	71 mm	262 mm
MAS LED SON-T EM 12Klm 65W 740 E40	71 mm	262 mm
MAS LED SON-T EM 8.1Klm 50W 727 E40	71 mm	262 mm
MAS LED SON-T EM 9Klm 50W 740 E40	71 mm	262 mm
MAS LED SON-T IF 10.8Klm 65W 727 E40	71 mm	262 mm
MAS LED SON-T IF 12Klm 65W 740 E40	71 mm	262 mm
MAS LED SON-T IF 8.1Klm 50W 727 E40	71 mm	262 mm
MAS LED SON-T IF 9Klm 50W 740 E40	71 mm	262 mm
TForce LED Road 112-68W E40 730	71 mm	262 mm
TForce LED Road 120-68W E40 740	71 mm	262 mm
TForce LED Road 55W E40 730 MV	71 mm	262 mm
TForce LED Road 55W E40 740 MV	71 mm	262 mm
TForce LED Road 68W E40 730 MV	71 mm	262 mm
TForce LED Road 68W E40 740 MV	71 mm	262 mm
TForce LED Road 68W E40 765 MV	71 mm	262 mm
TForce LED Road 84-55W E40 730	71 mm	262 mm
TForce LED Road 90-55W E40 740	71 mm	262 mm

Dimensional drawing



Product	D	C
MAS LED SON-T EM 3.6Klm 23W 727 E27	61 mm	200 mm
MAS LED SON-T EM 4Klm 23W 740 E27	61 mm	200 mm
MAS LED SON-T EM 5.4Klm 34W 727 E27	61 mm	200 mm
MAS LED SON-T EM 6Klm 34W 740 E27	61 mm	200 mm
MAS LED SON-T IF 3.6Klm 23W 727 E27	61 mm	200 mm
MAS LED SON-T IF 4Klm 23W 740 E27	61 mm	200 mm
MAS LED SON-T IF 5.4Klm 34W 727 E27	61 mm	200 mm
MAS LED SON-T IF 6Klm 34W 740 E27	61 mm	200 mm
TForce LED Road 25W E27 730 MV	61 mm	200 mm
TForce LED Road 25W E27 740 MV	61 mm	200 mm
TForce LED Road 35W E27 730 MV	61 mm	200 mm
TForce LED Road 35W E27 740 MV	61 mm	200 mm
TForce LED Road 40-25W E27 730	61 mm	200 mm
TForce LED Road 42-25W E27 740	61 mm	200 mm
TForce LED Road 55-35W E27 730	61 mm	200 mm
TForce LED Road 60-35W E27 740	61 mm	200 mm



Product	D	C
Tforce LED Road 65W E39 750 JP	71 mm	262 mm

General Information	
Switching Cycle	50,000
Light Technical	
Color rendering index (CRI)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear

General Information

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929001999402	TForce LED Road 40-25W E27 730	E27	50,000 hour(s)
929001999502	TForce LED Road 42-25W E27 740	E27	50,000 hour(s)

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003467012	MAS LED SON-T IF 3.6Klm 23W 727 E27	E27	70,000 hour(s)
929003467112	MAS LED SON-T IF 4Klm 23W 740 E27	E27	70,000 hour(s)

MASTER - LED HID SON-T

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929002007402	TForce LED Road 84-55W E40 730	E40	50,000 hour(s)
929002007502	TForce LED Road 90-55W E40 740	E40	50,000 hour(s)
929002068708	TForce LED Road 55W E40 740 MV	E40	50,000 hour(s)
929002221608	TForce LED Road 55W E40 730 MV	E40	50,000 hour(s)
929003467412	MAS LED SON-T IF 8.1Klm 50W 727 E40	E40	70,000 hour(s)
929003467512	MAS LED SON-T IF 9Klm 50W 740 E40	E40	70,000 hour(s)
929003468418	MAS LED SON-T EM 8.1Klm 50W 727 E40	E40	70,000 hour(s)
929003468518	MAS LED SON-T EM 9Klm 50W 740 E40	E40	70,000 hour(s)
929001898402	TForce LED Road 55-35W E27 730	E27	50,000 hour(s)
929001898502	TForce LED Road 60-35W E27 740	E27	50,000 hour(s)
929002068508	TForce LED Road 35W E27 740 MV	E27	50,000 hour(s)
929002221708	TForce LED Road 35W E27 730 MV	E27	50,000 hour(s)
929003041408	TForce LED Road 25W E27 730 MV	E27	50,000 hour(s)
929003041508	TForce LED Road 25W E27 740 MV	E27	50,000 hour(s)
929003467212	MAS LED SON-T IF 5.4Klm 34W 727 E27	E27	70,000 hour(s)
929003467312	MAS LED SON-T IF 6Klm 34W 740 E27	E27	70,000 hour(s)

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003467818	MAS LED SON-T EM 3.6Klm 23W 727 E27	E27	70,000 hour(s)
929003467918	MAS LED SON-T EM 4Klm 23W 740 E27	E27	70,000 hour(s)
929003468118	MAS LED SON-T EM 5.4Klm 34W 727 E27	E27	70,000 hour(s)
929003468218	MAS LED SON-T EM 6Klm 34W 740 E27	E27	70,000 hour(s)
929002007602	TForce LED Road 112-68W E40 730	E40	50,000 hour(s)
929002007702	TForce LED Road 120-68W E40 740	E40	50,000 hour(s)
929002277608	TForce LED Road 68W E40 730 MV	E40	50,000 hour(s)
929002277708	TForce LED Road 68W E40 740 MV	E40	50,000 hour(s)
929002277808	TForce LED Road 68W E40 765 MV	E40	50,000 hour(s)
929003467612	MAS LED SON-T IF 10.8Klm 65W 727 E40	E40	70,000 hour(s)
929003467712	MAS LED SON-T IF 12Klm 65W 740 E40	E40	70,000 hour(s)
929003468718	MAS LED SON-T EM 10.8Klm 65W 727 E40	E40	70,000 hour(s)
929003468818	MAS LED SON-T EM 12Klm 65W 740 E40	E40	70,000 hour(s)
929003692008	Tforce LED Road 65W E39 750 JP	E39	50,000 hour(s)

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Code	Luminous Flux
929001999402	TForce LED Road 40-25W E27 730	3000 K	730	4,000 lm
929001999502	TForce LED Road 42-25W E27 740	4000 K	740	4,200 lm
929003467012	MAS LED SON-T IF 3.6Klm 23W 727 E27	2700 K	727	3,600 lm
929003467112	MAS LED SON-T IF 4Klm 23W 740 E27	4000 K	740	4,000 lm
929002007402	TForce LED Road 84-55W E40 730	3000 K	730	8,400 lm
929002007502	TForce LED Road 90-55W E40 740	4000 K	740	9,000 lm
929002068708	TForce LED Road 55W E40 740 MV	4000 K	740	9,000 lm
929002221608	TForce LED Road 55W E40 730 MV	3000 K	730	8,400 lm
929003467412	MAS LED SON-T IF 8.1Klm 50W 727 E40	2700 K	727	8,100 lm
929003467512	MAS LED SON-T IF 9Klm 50W 740 E40	4000 K	740	9,000 lm
929003468418	MAS LED SON-T EM 8.1Klm 50W 727 E40	2700 K	727	8,100 lm
929003468518	MAS LED SON-T EM 9Klm 50W 740 E40	4000 K	740	9,000 lm
929001898402	TForce LED Road 55-35W E27 730	3000 K	730	5,500 lm
929001898502	TForce LED Road 60-35W E27 740	4000 K	740	6,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Code	Luminous Flux
929002068508	TForce LED Road 35W E27 740 MV	4000 K	740	6,000 lm
929002221708	TForce LED Road 35W E27 730 MV	3000 K	730	5,500 lm
929003041408	TForce LED Road 25W E27 730 MV	3000 K	730	4,000 lm
929003041508	TForce LED Road 25W E27 740 MV	4000 K	740	4,200 lm
929003467212	MAS LED SON-T IF 5.4Klm 34W 727 E27	2700 K	727	5,400 lm
929003467312	MAS LED SON-T IF 6Klm 34W 740 E27	4000 K	740	6,000 lm
929003467818	MAS LED SON-T EM 3.6Klm 23W 727 E27	2700 K	727	3,600 lm
929003467918	MAS LED SON-T EM 4Klm 23W 740 E27	4000 K	740	4,000 lm
929003468118	MAS LED SON-T EM 5.4Klm 34W 727 E27	2700 K	727	5,400 lm
929003468218	MAS LED SON-T EM 6Klm 34W 740 E27	4000 K	740	6,000 lm
929002007602	TForce LED Road 112-68W E40 730	3000 K	730	11,200 lm
929002007702	TForce LED Road 120-68W E40 740	4000 K	740	12,000 lm
929002277608	TForce LED Road 68W E40 730 MV	3000 K	730	11,200 lm
929002277708	TForce LED Road 68W E40 740 MV	4000 K	740	12,000 lm

MASTER - LED HID SON-T

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Code	Luminous Flux
929002277808	TForce LED Road 68W E40 765 MV	6500 K	765	12,000 lm
929003467612	MAS LED SON-T IF 10.8Klm 65W 727 E40	2700 K	727	10,800 lm
929003467712	MAS LED SON-T IF 12Klm 65W 740 E40	4000 K	740	12,000 lm
929003468718	MAS LED SON-T EM 10.8Klm 65W 727 E40	2700 K	727	10,800 lm
929003468818	MAS LED SON-T EM 12Klm 65W 740 E40	4000 K	740	12,000 lm
929003692008	Tforce LED Road 65W E39 750 JP	5000 K	750	12,000 lm

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Starting Time (Nom)
929001999402	TForce LED Road 40-25W E27 730	50 Hz	50 Hz	25 W	0.5 s
929001999502	TForce LED Road 42-25W E27 740	50 Hz	50 Hz	25 W	0.5 s
929003467012	MAS LED SON-T IF 3.6Klm 23W 727 E27	50 Hz	50 Hz	23 W	0.5 s
929003467112	MAS LED SON-T IF 4Klm 23W 740 E27	50 Hz	50 Hz	23 W	0.5 s
929002007402	TForce LED Road 84-55W E40 730	50 Hz	50 Hz	55 W	0.5 s
929002007502	TForce LED Road 90-55W E40 740	50 Hz	50 Hz	55 W	0.5 s
929002068708	TForce LED Road 55W E40 740 MV	50 to 60 Hz	50 to 60 Hz	55 W	0.5 s
929002221608	TForce LED Road 55W E40 730 MV	50 to 60 Hz	50 to 60 Hz	55 W	0.5 s
929003467412	MAS LED SON-T IF 8.1Klm 50W 727 E40	50 Hz	50 Hz	50 W	0.5 s
929003467512	MAS LED SON-T IF 9Klm 50W 740 E40	50 Hz	50 Hz	50 W	0.5 s
929003468418	MAS LED SON-T EM 8.1Klm 50W 727 E40	50 to 60 Hz	50 to 60 Hz	50 W	0.5 s
929003468518	MAS LED SON-T EM 9Klm 50W 740 E40	50 to 60 Hz	50 to 60 Hz	50 W	0.5 s
929001898402	TForce LED Road 55-35W E27 730	50 Hz	50 Hz	35 W	0.5 s
929001898502	TForce LED Road 60-35W E27 740	50 Hz	50 Hz	35 W	0.5 s
929002068508	TForce LED Road 35W E27 740 MV	50 to 60 Hz	50 to 60 Hz	35 W	0.5 s
929002221708	TForce LED Road 35W E27 730 MV	50 to 60 Hz	50 to 60 Hz	35 W	0.5 s
929003041408	TForce LED Road 25W E27 730 MV	50 to 60 Hz	50 to 60 Hz	25 W	0.5 s
929003041508	TForce LED Road 25W E27 740 MV	50 to 60 Hz	50 to 60 Hz	25 W	0.5 s
929003467212	MAS LED SON-T IF 5.4Klm 34W 727 E27	50 Hz	50 Hz	34 W	0.5 s
929003467312	MAS LED SON-T IF 6Klm 34W 740 E27	50 Hz	50 Hz	34 W	0.5 s
929003467818	MAS LED SON-T EM 3.6Klm 23W 727 E27	50 to 60 Hz	50 to 60 Hz	23 W	0.5 s
929003467918	MAS LED SON-T EM 4Klm 23W 740 E27	50 to 60 Hz	50 to 60 Hz	23 W	0.5 s

MASTER - LED HID SON-T

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Starting Time (Nom)
929003468118	MAS LED SON-T EM 5.4Klm 34W 727 E27	50 to 60 Hz	50 to 60 Hz	34 W	0.5 s
929003468218	MAS LED SON-T EM 6Klm 34W 740 E27	50 to 60 Hz	50 to 60 Hz	34 W	0.5 s
929002007602	TForce LED Road 112-68W E40 730	50 Hz	50 Hz	68 W	0.5 s
929002007702	TForce LED Road 120-68W E40 740	50 Hz	50 Hz	68 W	0.5 s
929002277608	TForce LED Road 68W E40 730 MV	50 to 60 Hz	50 to 60 Hz	68 W	0.5 s
929002277708	TForce LED Road 68W E40 740 MV	50 to 60 Hz	50 to 60 Hz	68 W	0.5 s
929002277808	TForce LED Road 68W E40 765 MV	50 to 60 Hz	50 to 60 Hz	68 W	0.5 s

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Starting Time (Nom)
929003467612	MAS LED SON-T IF 10.8Klm 65W 727 E40	50 Hz	50 Hz	65 W	0.5 s
929003467712	MAS LED SON-T IF 12Klm 65W 740 E40	50 Hz	50 Hz	65 W	0.5 s
929003468718	MAS LED SON-T EM 10.8Klm 65W 727 E40	50 to 60 Hz	50 to 60 Hz	65 W	0.5 s
929003468818	MAS LED SON-T EM 12Klm 65W 740 E40	50 to 60 Hz	50 to 60 Hz	65 W	0.5 s
929003692008	Tforce LED Road 65W E39 750 JP	50 to 60 Hz	-	65 W	3 s

Temperature

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929001999402	TForce LED Road 40-25W E27 730	-	95 °C
929001999502	TForce LED Road 42-25W E27 740	-	95 °C
929003467012	MAS LED SON-T IF 3.6Klm 23W 727 E27	-30 to +45 °C	46 °C
929003467112	MAS LED SON-T IF 4Klm 23W 740 E27	-30 to +45 °C	46 °C
929002007402	TForce LED Road 84-55W E40 730	-	97 °C
929002007502	TForce LED Road 90-55W E40 740	-	97 °C
929002068708	TForce LED Road 55W E40 740 MV	-	97 °C
929002221608	TForce LED Road 55W E40 730 MV	-	97 °C
929003467412	MAS LED SON-T IF 8.1Klm 50W 727 E40	-30 to +45 °C	52 °C
929003467512	MAS LED SON-T IF 9Klm 50W 740 E40	-30 to +45 °C	52 °C

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929003468418	MAS LED SON-T EM 8.1Klm 50W 727 E40	-30 to +45 °C	52 °C
929003468518	MAS LED SON-T EM 9Klm 50W 740 E40	-30 to +45 °C	52 °C
929001898402	TForce LED Road 55-35W E27 730	-	95 °C
929001898502	TForce LED Road 60-35W E27 740	-	95 °C
929002068508	TForce LED Road 35W E27 740 MV	-	95 °C
929002221708	TForce LED Road 35W E27 730 MV	-	95 °C
929003041408	TForce LED Road 25W E27 730 MV	-	45 °C
929003041508	TForce LED Road 25W E27 740 MV	-	45 °C
929003467212	MAS LED SON-T IF 5.4Klm 34W 727 E27	-30 to +45 °C	59 °C
929003467312	MAS LED SON-T IF 6Klm 34W 740 E27	-30 to +45 °C	59 °C

MASTER - LED HID SON-T

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929003467818	MAS LED SON-T EM 3.6Klm 23W 727 E27	-30 to +45 °C	46 °C
929003467918	MAS LED SON-T EM 4Klm 23W 740 E27	-30 to +45 °C	46 °C
929003468118	MAS LED SON-T EM 5.4Klm 34W 727 E27	-30 to +45 °C	59 °C
929003468218	MAS LED SON-T EM 6Klm 34W 740 E27	-30 to +45 °C	59 °C
929002007602	TForce LED Road 112-68W E40 730	-	103 °C
929002007702	TForce LED Road 120-68W E40 740	-	103 °C
929002277608	TForce LED Road 68W E40 730 MV	-	60 °C
929002277708	TForce LED Road 68W E40 740 MV	-	60 °C
929002277808	TForce LED Road 68W E40 765 MV	-	60 °C
929003467612	MAS LED SON-T IF 10.8Klm 65W 727 E40	-30 to +45 °C	55 °C
929003467712	MAS LED SON-T IF 12Klm 65W 740 E40	-30 to +45 °C	55 °C
929003468718	MAS LED SON-T EM 10.8Klm 65W 727 E40	-30 to +45 °C	55 °C
929003468818	MAS LED SON-T EM 12Klm 65W 740 E40	-30 to +45 °C	55 °C
929003692008	Tforce LED Road 65W E39 750 JP	-40 to +45 °C	58 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929001999402	TForce LED Road 40-25W E27 730	Others
929001999502	TForce LED Road 42-25W E27 740	Others
929003467012	MAS LED SON-T IF 3.6Klm 23W 727 E27	T60
929003467112	MAS LED SON-T IF 4Klm 23W 740 E27	T60
929002007402	TForce LED Road 84-55W E40 730	Others
929002007502	TForce LED Road 90-55W E40 740	Others
929002068708	TForce LED Road 55W E40 740 MV	Others
929002221608	TForce LED Road 55W E40 730 MV	Others
929003467412	MAS LED SON-T IF 8.1Klm 50W 727 E40	T70
929003467512	MAS LED SON-T IF 9Klm 50W 740 E40	T70
929003468418	MAS LED SON-T EM 8.1Klm 50W 727 E40	T70
929003468518	MAS LED SON-T EM 9Klm 50W 740 E40	T70
929001898402	TForce LED Road 55-35W E27 730	Others
929001898502	TForce LED Road 60-35W E27 740	Others
929002068508	TForce LED Road 35W E27 740 MV	Others
929002221708	TForce LED Road 35W E27 730 MV	Others
929003041408	TForce LED Road 25W E27 730 MV	T-shape
929003041508	TForce LED Road 25W E27 740 MV	T-shape
929003467212	MAS LED SON-T IF 5.4Klm 34W 727 E27	T60
929003467312	MAS LED SON-T IF 6Klm 34W 740 E27	T60
929003467818	MAS LED SON-T EM 3.6Klm 23W 727 E27	T60
929003467918	MAS LED SON-T EM 4Klm 23W 740 E27	T60
929003468118	MAS LED SON-T EM 5.4Klm 34W 727 E27	T60
929003468218	MAS LED SON-T EM 6Klm 34W 740 E27	T60
929002007602	TForce LED Road 112-68W E40 730	Others
929002007702	TForce LED Road 120-68W E40 740	Others
929002277608	TForce LED Road 68W E40 730 MV	T-shape
929002277708	TForce LED Road 68W E40 740 MV	T-shape
929002277808	TForce LED Road 68W E40 765 MV	T-shape
929003467612	MAS LED SON-T IF 10.8Klm 65W 727 E40	T70
929003467712	MAS LED SON-T IF 12Klm 65W 740 E40	T70
929003468718	MAS LED SON-T EM 10.8Klm 65W 727 E40	T70
929003468818	MAS LED SON-T EM 12Klm 65W 740 E40	T70
929003692008	Tforce LED Road 65W E39 750 JP	T70

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929001999402	TForce LED Road 40-25W E27 730	25 kWh
929001999502	TForce LED Road 42-25W E27 740	25 kWh
929003467012	MAS LED SON-T IF 3.6Klm 23W 727 E27	23 kWh
929003467112	MAS LED SON-T IF 4Klm 23W 740 E27	23 kWh
929002007402	TForce LED Road 84-55W E40 730	55 kWh
929002007502	TForce LED Road 90-55W E40 740	55 kWh
929002068708	TForce LED Road 55W E40 740 MV	55 kWh
929002221608	TForce LED Road 55W E40 730 MV	55 kWh
929003467412	MAS LED SON-T IF 8.1Klm 50W 727 E40	50 kWh
929003467512	MAS LED SON-T IF 9Klm 50W 740 E40	50 kWh
929003468418	MAS LED SON-T EM 8.1Klm 50W 727 E40	50 kWh
929003468518	MAS LED SON-T EM 9Klm 50W 740 E40	50 kWh
929001898402	TForce LED Road 55-35W E27 730	35 kWh
929001898502	TForce LED Road 60-35W E27 740	35 kWh
929002068508	TForce LED Road 35W E27 740 MV	35 kWh
929002221708	TForce LED Road 35W E27 730 MV	35 kWh
929003041408	TForce LED Road 25W E27 730 MV	25 kWh
929003041508	TForce LED Road 25W E27 740 MV	25 kWh

MASTER - LED HID SON-T

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929003467212	MAS LED SON-T IF 5.4Klm 34W 727 E27	34 kWh
929003467312	MAS LED SON-T IF 6Klm 34W 740 E27	34 kWh
929003467818	MAS LED SON-T EM 3.6Klm 23W 727 E27	23 kWh
929003467918	MAS LED SON-T EM 4Klm 23W 740 E27	23 kWh
929003468118	MAS LED SON-T EM 5.4Klm 34W 727 E27	34 kWh
929003468218	MAS LED SON-T EM 6Klm 34W 740 E27	34 kWh
929002007602	TForce LED Road 112-68W E40 730	68 kWh
929002007702	TForce LED Road 120-68W E40 740	68 kWh
929002277608	TForce LED Road 68W E40 730 MV	68 kWh
929002277708	TForce LED Road 68W E40 740 MV	68 kWh
929002277808	TForce LED Road 68W E40 765 MV	68 kWh
929003467612	MAS LED SON-T IF 10.8Klm 65W 727 E40	65 kWh
929003467712	MAS LED SON-T IF 12Klm 65W 740 E40	65 kWh
929003468718	MAS LED SON-T EM 10.8Klm 65W 727 E40	65 kWh
929003468818	MAS LED SON-T EM 12Klm 65W 740 E40	65 kWh
929003692008	Tforce LED Road 65W E39 750 JP	-





MASTER - LED HID SON-T





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.