



Green savings, you can bank

Philips GreenLED
Energy saving downlighters






50% energy saving over CFLs



4 times more life over CFLs



ZERO maintenance



ZERO Mercury

Product features



GreenLED

GreenLED is a breakthrough offering which combines modern product design, the latest LED technology and reliable heat management to deliver a long lasting efficient solution for offices and retail spaces. Offering substantial energy savings compared to CFL/halogen, good light quality, complete stylistic freedom and significant maintenance savings, the product is an ideal value for money replacement for conventional CFL options.

Key benefits


- Good quality lighting- highly efficient optical system ensuring an effective low glare lighting solution.
- Energy saving solution- high efficiency white reflector, high transmittive diffuser and high power LED's delivers an effective energy efficient solution.
- Attractive payback- 6 months, effective replacement for conventional CFL solutions resulting in significant power saving and reduced operational costs.
- Maintenance free service life- 40,000 burning hours of high efficiency LED's ensure uninterrupted service life.
- Easy installation- compact, low depth design allows installation in all kinds of ceiling systems.
- Saves more than Rs 1000 per year.*
- No Mercury- green earth.

*12 hours daily working and Rs 6 per unit electricity charges

Specification and product dimensions

Type	BBS170 1xDLED- 5000 PSU WH
Source	Non replaceable high wattage LED
Color Temperature	5700 K, 4000 K
Driver	Constant current electronic driver
CRI	>70
Optical System	High efficiency white reflector
System Wattage	15W
Lumen output	850lm
Color	White

Material	Die-cast aluminium housing
Mounting	Recessed
Electronic driver	Voltage : 240V / 50Hz Voltage range : 160V - 270V Power factor : >0.9



Technical data

Type	Wattage	Nominal Voltage	Nominal Power Factor
BBS170 1XDLED -5000 PSU WH	15W	240V	0.9

Ordering data

Type	I2NC	Qty/box	Dimensions (mm)	Nett. Wt.	Gross Wt.
BBS170 1XDLED -5000 PSU WH	919515810044	8	465 X 465 X 325	0.63Kg.	8Kg.

North

Philips Electronics India Ltd,

Regional Sales Manager
9th Floor, DLF - 9B, DLF Cyber City
DLF Phase 3, Gurgaon 122002
Tel :- 91 124 460 6000
Fax :- 91 124 460 6666
lighting.india@philips.com

West

Philips Electronics India Ltd,

Regional Sales Manager
Technopolis Knowledge Park,
Mahakali Caves Road,
Chakala, Andheri East, Mumbai 400093
Tel :- 91 22 6691 2000
Fax :- 91 22 6691 2389 / 6691 2398
lighting.india@philips.com

Philips Electronics India Ltd,

8th Floor, DLF - 9B, DLF Cyber City
DLF phase 3, Gurgaon 122002
Tel :- 91 124 460 6000
Fax :- 91 124 460 6666

Contact customer service executive at

1800 102 2929 (Toll free)
1860 180 1111, 0124- 4291111
"Standard call rates apply"

South

Philips Electronics India Ltd,

Temple Towers, 5th Floor,
Old No. 476, New No. 672,
Anna Salai, Nandanam, Chennai 600 035
Tel :- 91 45 6650 1000
Fax :- 91 44 6650 1075
lighting.india@philips.com

Philips Electronics India Ltd,

Area Sales Manager
Philips Innovation Campus
Manyata Tech Park, Nagavara
Bengaluru- 560045
Tel : 080-4189 0000
Fax :- 080 6692 9930
lighting.india@philips.com

Philips Electronics India Ltd,

Area Sales Manager
6-3-1109 / 1 / P/103, 3rd Floor,
Jewalpwani Towers, Rajbhavan Road,
Somajiguda, Hyderabad
Tel :- 040 6646 7676 / 4825
Fax :- 040 6678 7974
lighting.india@philips.com

East

Philips Electronics India Ltd,

Regional Sales Manager
7, Justice Chandra Madhab Road,
Kolkata 700 020
Tel :91 33 2486 7621-24
Fax :91 33 2486 8318
lighting.india@philips.com



© 2012 Koninklijke Philips Electronics N.V.

All rights reserved, reproduction, copying, usage, modifying, hiring, renting, public performance, transmission and/or broadcasting in whole or in part is prohibited without the written consent of Philips Design. PHILIPS and the Philips shield are registered trademarks or Koninklijke Philips Electronics N.V.

URL : www.lighting.philips.co.in