




Philips Hue White
Wireless dimming kit E27

1 x E27 bulb

Dimmer switch included
Warm white light (2700K)



8718696554975

Dimmable light

with easy control

Get started with Philips Hue wireless dimming kit and enjoy smooth wireless dimming. Control the bulb with the included dimmer switch, or connect everything to a Philips Hue bridge for control from your smart device.

Easy control and comfort

- Installation free dimming
- Place the switch anywhere
- Use as a remote control
- Control up to 10 Philips Hue lights simultaneously
- Full control from smart device with Hue bridge



PHILIPS

Highlights

Installation free dimming



Experience guaranteed smooth dimming with Philips Hue. Not too bright. Not too dark. Just right. No need for wires, an electrician or installation

Place switch anywhere



The Philips Hue dimmer switch works as a normal wall switch and dimmer. You can place it anywhere you want, using screws or the adhesive tape on the back plate of the switch

Use as a remote control




Pick up the remote and use it wherever you want for your comfort. The control unit of the switch is magnetic and can be removed from the base plate.

Add up to 10 Hue lights



You can connect up to 10 Philips Hue lights to your Philips Hue dimmer switch and control them simultaneously.

Full control with Hue bridge



Connect your Philips Hue lights with the bridge to unlock the endless possibilities of the system.

Specifications

The bulb

- Fitting: E27
- Form factor: A60
- Lifetime: 25000 hour(s)
- Color temperature: 2700K
- Wattage: 9 W
- Lumen output: 806 lm
- Software upgradable: when connected to Hue bridge
- Start up: Instant 100% light output
- Height: 110 mm
- Diameter: 62 mm
- Input voltage: 220V-240V
- Max. standby power: <0.5 W

The switch

- Batteries included: 1 x CR2450
- Frequency band: 2400 – 2483.5 MHz
- Lifetime: 50000 clicks
- Max. lights per switch: 10 if not linked to Hue bridge
- Minimal battery lifetime: min 3 year(s)
- Software upgradeable: when connected to Hue bridge
- Switch depth: 11 mm
- Switch height: 92 mm
- Switch width: 35 mm
- Wall plate depth: 14 mm
- Wall plate height: 115 mm
- Wall plate width: 70 mm
- Zigbee Light link: protocol IEEE 802.15.4
- Range: 12m

What's in the box

- Hue dimmer switch: 1
- Hue white bulbs: 1

Environmental

- Operational humidity: 5% < H < 95% (non condensing)
- Operational temperature: -10°C – 45°C

Guarantee

- 2 years



Issue date 2017-11-11

Version: 3.0.1

12 NC: 9290 011 37011
EAN: 87 18696 55497 5

© 2017 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com