




Philips myLiving  
Spot light

**STAR**  
white  
LED

myLiving



56242/31/86



## In light of perfection

Star's sleek, polished lamps are fully rotatable to any angle for you to instantly add striking accents to your room with its bright focused light. Available in 1, 2, or 4 lamp combinations.

### Match your interior style

- Coordinated range
- Suitable for both walls and ceilings

### Energy saving

- 80% energy saving

### Ease of use

- Flexibility to direct light where you need it the most

### Pure, natural light


- Warm white light effect

**PHILIPS**

Spot light  
STAR white, LED

# Highlights

## Coordinated range



Complete range of coordinated designs available for you to choose.

## Freedom of placement

Suitable for both walls and ceilings

## Flexible directional light




This product allows you to adjust the light to any direction that you like.

## 80% energy saving



Up to 80% energy saving compared to standard incandescent light sources.

## Warm white light effect



Light up your home with warm white light effects thanks to the latest LED innovation. Philips introduces the latest generation of warm white light high power LEDs, reaching a colour temperature of 2700 Kelvin. This innovation brings the Philips lighting fixtures to the next level, allowing you to combine elegance and ambience creation with light and energy efficiency.

562423186

# Specifications

## Design and finishing

- Material: aluminium
- Color: white

## Product dimensions & weight

- Height: 8.2 cm
- Length: 19.8 cm
- Width: 6.0 cm
- Net weight: 0.495 kg

## Technical specifications

- Mains power: Range 220 V - 240 V, 50-60 Hz
- Bulb technology: LED, Safety Extra Low Voltage
- Number of bulbs: 2
- Wattage bulb included: 4 W
- Light color: warm white
- Lamp lifetime up to: 15,000 hrs
- Beam angle: 50°
- Fixture dimmable: No
- LED
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: I - earthed
- Light source equivalent to traditional bulb of: 35 W

## Service

- Warranty: 1 year(s)

## Packaging dimensions & weight

- Height: 21.8 cm
- Length: 9.3 cm
- Width: 7.3 cm
- Weight: 0.580 kg

## Miscellaneous

- Especially designed for: Living- & Bedroom
- Style: Modern
- Type: Spot light



Issue date 2015-01-21

Version: 3.0.1

12 NC: 9150 043 54101  
EAN: 87 18291 48997 9

© 2015 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)