PHILIPS

Lighting

PrimaVision Compact for CDM

HID-PV C 50 /I CDM 220-240V 50/60Hz

High-quality, compact and lightweight HID electronic gear for optimal and reliable performance of 20, 35, 50 and 70 W CDM lamps

Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	0.25 mA
Inrush Current Width	0.25 ms
Inrush Current Peak (Max)	26 A
Number of Products on MCB (16A Type B) (Nom)	24

Wiring	
Cable Length From Device to Lamp	2.0 m
Connector Type	Insert

Temperature	
Ambient temperature range	-20 °C to 50 °C
T-Case Lifetime (Nom)	75 °C
T-Case Maximum (Max)	75 °C

Mechanical and Housing	
Housing	/I

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Safety Standard	IEC 61347-2-3
Environmental Standard	ISO 14001
Approval Marks	CE marking ENEC certificate

Product Data	
Order product name	HID-PV C 50 /I CDM 220-240V 50/60Hz
Full product name	HID-PV C 50 /I CDM 220-240V 50/60Hz
Full product code	872790093365900
Order code	93365900
Material Nr. (12NC)	913700665166
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900933659
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900933666

PrimaVision Compact for CDM

Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-PV C 50 /I CDM 220-240V 50/60Hz	4.8 mm	34.5 mm	188.0 mm	170.0 mm	82.7 mm

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.