

# HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

## BSN 100 L33-A2-TS 230V 50Hz

Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps (no ignitor needed for SON-I lamps)

### Product data

| Operating and Electrical | |
|---|---|
| **Input Voltage** | 230 V |
| **Line Frequency** | 50 Hz |
| **Input Frequency** | 50 Hz |

| Wiring | |
|---|---|
| **Connector Type** | Screw |

| Approval and Application | |
|---|---|
| **Approval Marks** | CE marking ENEC certificate |

| Product Data | |
|---|---|
| **Order product name** | BSN 100 L33-A2-TS 230V 50Hz |

| | |
|---|---|
| **Full product name** | BSN 100 L33-A2-TS 230V 50Hz |
| **Full product code** | 871869674094100 |
| **Order code** | 74094100 |
| **Material Nr. (12NC)** | 913700752526 |
| **Numerator - Quantity Per Pack** | 1 |
| **EAN/UPC - Product/Case** | 8718696740941 |
| **Numerator - Packs per outer box** | 6 |
| **EAN/UPC - Case** | 8718696740958 |

# HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

## Dimensional drawing




| Product | A1 | A2 | B1 | C1 | D1 |
|---|---|---|---|---|---|
| BSN 100 L33-A2-TS 230V 50Hz | 123 mm | 108 mm | 65 mm | 53 mm | 6.2 mm |

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.