Reflector Flood

65BR30/FL55 120V 12/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Beam Angle (Nom)	55 degree(s)
Luminous Flux	620 lm
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	65 W
Warm-up time to 60% light	instant full light s
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	BR30

Product Data	
Order product name	65BR30/FL55 120V 12/1
Full product name	65BR30/FL55 120V 12/1
Order code	248765
Material Nr. (12NC)	920681036369
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677225193
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677225198

Reflector Flood

Dimensional drawing

Product
65BR30/FL55 120V 12/1



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.