PHILIPS

Lighting

鹵素反射燈

6423 150W GZ6.35 15V 1CT/10X5F

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

产品数据

一般資訊	
燈座基底	GZ6.35 [GZ6.35]
操作位置	P90/P15
壽命 (故障率 50%) (標稱)	50 h

照明技術	
相關色彩溫度 (規範)	3380 K
演色性指數 (CRI)	100

運轉與電力	
耗電量	150 W
電壓 (標稱)	15 V
電壓 (標稱)	15 V

控制與調光	
可調光	是

機械與外罩	
燈泡材質	石英-UV 開放式
反射罩表層	滑順
燈泡形狀	R50 [R 50mm]

產品資料	
下訂產品名稱	6423 150W GZ6.35 15V 1CT/10X5F
完整產品名稱	6423 150W GZ6.35 15V 1CT/10X5F
完整產品代碼	871150042733560
訂單代碼	923916818504
材質 Nr. (12NC)	923916818504
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500427335

鹵素反射燈

分子 - 每一外盒包裝	50
EAN/UPC - 箱	8711500427342

二维绘图



Product	D (max)	C (max)
6423 150W GZ6.35 15V 1CT/10X5F	50 mm	42 mm

© 2023 Signify Holding 保留一切權利。 Signify 不對本協議所含括資訊之準確性及完整性提供任何聲明或保證，對以此訊息為依據採取的任何行動亦概不負責。 除非 Signify 同意，本文件提及之資訊並非任何商業合約，亦不構成任何報價或合約任一部分。 Philips 與 Philips Shield Emblem 均屬 Koninklijke Philips N.V 註冊商標。