Plusline ES Compact

Plusline 78mm 2y 48W R7s 230V 1BB

Mains-voltage halogen linear lamp with superior quality and reliability. Offers very long lifetime and crisp halogen light. Ideal solution for decorative luminaires.

Product data

General Information	
Cap-Base	R7s
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Luminous Flux	780 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	15.6 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	48.0 W
Lamp Current (Nom)	0.21 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T11

Approval and Application	
Energy Consumption kWh/1000 h	48 kWh

Product Data	
Order product name	Plusline 78mm 2y 48W R7s 230V 1BB
Full product name	Plusline 78mm 2y 48W R7s 230V 1BB
Full product code	872790085231800
Order code	85231800
Material Nr. (12NC)	924587044210
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900852318
Numerator - Packs per outer box	100
EAN/UPC - Case	8727900852332

Plusline ES Compact

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline 78mm 2y 48W R7s 230V 1BB	11 mm	76.5 mm	74.9 mm	73.3 mm	78 mm

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.