PHILIPS

Lighting

MASTER TL-D Super 80

G A↑G

MASTER TL-D Super 80 38W/830 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	15,000 hour(s)

Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	3,300 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.44
Chromaticity Coordinate Y (Nom)	0.403
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	88 lm/W
Color rendering index (CRI)	82

Operating and Electrical	
Power Consumption	38.2 W
Lamp Current (Nom)	0.430 A

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T8

Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Nom)	1.7 mg
Energy Consumption kWh/1000 h	39 kWh
EPREL Registration Number	423432

Product Data	
Order product name	MASTER TL-D Super 80 38W/830 SLV/25
Full product name	MASTER TL-D Super 80 38W/830 1SL/25
Full product code	871150055880040
Order code	55880040
Material Nr. (12NC)	927923583014
Numerator - Quantity Per Pack	1

MASTER TL-D Super 80

EAN/UPC - Product/Case	8711500558800
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500558817

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 38W/830 SLV/25	28 mm	1,047.0 mm	1,054.1 mm	1,051.7 mm	1,061.2 mm

Photometric data



Spectral Power Distribution Colour - MASTER TL-D Super 80 38W/830 SLV/25

Lifetime



Life Expectancy Diagram - MASTER TL-D Super 80 38W/830 SLV/25



Life Expectancy Diagram - MASTER TL-D Super 80 38W/830 SLV/25

MASTER TL-D Super 80

Lifetime



Lumen Maintenance Diagram - MASTER TL-D Super 80 38W/830 SLV/25

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.