PHILIPS

Lighting

T5 High Output

F54T5/865/HO/ALTO 40PK

Philips T5 HO lamps are environmentally-responsible, ultra-slim and have extraordinary light output and longer life.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G5
Features	HO Alto® [High Output Alto]

Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	4,650 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6300 K
Luminous Efficacy (rated) (Nom)	77 lm/W
Color rendering index (CRI)	82

Operating and Electrical	
Power Consumption	54.1 W
Lamp Current (Nom)	0.455 A

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5

Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg

Product Data	
Order product name	F54T5/865/HO/ALTO 40PK
Full product name	F54T5/865/HO/ALTO 40PK
Order code	147454
Material Nr. (12NC)	927993186522
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677147457
Numerator - Packs per outer box	40
EAN/UPC - Case	50046677147452

T5 High Output

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F54T5/865/HO/ ALTO 40PK	11/16 inch	45-1/4 inch	45-9/16 inch	45-7/16 inch	45-13/16 inch

Photometric data



Spectral Power Distribution Colour - F54T5/865/HO/ALTO 40PK

Lifetime



Life Expectancy Diagram - F54T5/865/HO/ALTO 40PK



Lumen Maintenance Diagram - F54T5/865/HO/ALTO 40PK

T5 High Output

Lifetime

Life Expectancy Diagram - F54T5/865/HO/ALTO 40PK

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.