MASTERColour CDM-T

MASTERC CDM-T 250W/942 G12 1CT/12

Range of single-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G12
Operating Position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	15,000 h

Light Technical	
Color Code	942 [CCT of 4200K]
Luminous Flux	26,250 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.371
Chromaticity Coordinate Y (Nom)	0.366
Correlated Color Temperature (Nom)	4200 K
Luminous Efficacy (rated) (Nom)	105 lm/W
Color rendering index (CRI)	91
Arc Length O (Nom)	12.3 mm

Operating and Electrical	
Power Consumption	250.0 W
Voltage (Nom)	93 V
Voltage (Nom)	93 V

Controls and Dimming	
Dimmable	No

MASTERColour CDM-T

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T24

Approval and Application	
Energy Efficiency Class	F
Mercury (Hg) Content (Max)	20 mg
Mercury (Hg) Content (Nom)	20.0 mg
Energy Consumption kWh/1000 h	250 kWh
EPREL Registration Number	473354

Product Data	
Order product name	MASTERC CDM-T 250W/942 G12 1CT/12

Full product name	MASTERC CDM-T 250W/942 G12 1CT/12
Full product code	871150021112515
Local code description	CDMT250W942
Order code	928094205131
Material Nr. (12NC)	928094205131
Local order code	CDMT250W942
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500211125
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500211132

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 250W/942 G12 1CT/12	25 mm	12.3 mm	71.5 mm	73.5 mm	72.5 mm	135 mm

Photometric data





Light Distribution Diagram - MASTERC CDM-T 250W/942 G12 1CT/12



Spectral Power Distribution Colour - MASTERC CDM-T 250W/942 G12 1CT/12

MASTERColour CDM-T

Lifetime





Lumen Maintenance Diagram - MASTERC CDM-T 250W/942 G12 1CT/12

Life Expectancy Diagram - MASTERC CDM-T 250W/942 G12 1CT/12

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.