PHILIPS

Lighting

Ecofit Ledtubes T8

LEDtube 600mm 8W 740 T8 AP C G

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	15000 hour(s)
Switching Cycle	50000
Rated Lifetime (Hours)	15000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	740 [CCT of 4000K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	800 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<7
Color rendering index (CRI)	73
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	8 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V

Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	60 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	600 mm
Bulb Shape	T8

Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No

Ecofit Ledtubes T8

Approval Marks	RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh
EyeComfort	Yes

Order code	929001184708
Material Nr. (12NC)	929001184708
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696525050
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696525067

Product Data

Order product name	LEDtube 600mm 8W 740 T8 AP C G
Full product name	LEDtube 600mm 8W 740 T8 AP C G
Full product code	871869652505000

Dimensional drawing

Product	D1	D2	A1	A2	A3	C	D
LEDtube 600mm 8W 740 T8 AP C G	25.68 mm	28 mm	588.5 mm	595.5 mm	602.5 mm	602.5 mm	27.8 mm

Photometric data



General uniform lighting - LEDtube 600mm 8W 740 T8 AP C G



Light Distribution Diagram - LEDtube 600mm 8W 740 T8 AP C G



Spectral Power Distribution Colour - LEDtube 600mm 8W 740 T8 AP C G

Lifetime



Life Expectancy Diagram - LEDtube 600mm 8W 740 T8 AP C G



Life Expectancy Diagram - LEDtube 600mm 8W 740 T8 AP C G



Life Expectancy Diagram - LEDtube 600mm 8W 740 T8 AP C G



Lumen Maintenance Diagram - LEDtube 600mm 8W 740 T8 AP C G



Lumen Maintenance Diagram - LEDtube 600mm 8W 740 T8 AP C G

Ecofit Ledtubes T8

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com
2023, April 15 - data subject to change