PHILIPS

Lighting

# MASTER LEDtube EM/ Mains T8

## MAS LEDtube 1200mm HO 14W840 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lamping in general lighting applications.

### Warnings and Safety

- -
- -

### Product data

| General Information | |
|---|---|
| **Cap-Base** | G13 [Medium Bi-Pin Fluorescent] |
| **Nominal lifetime** | 50,000 hour(s) |
| **Switching Cycle** | 200,000 |
| **Lighting Technology** | LED |
| **EU RoHS compliant** | Yes |

| Light Technical | |
|---|---|
| **Color Code** | 840 [CCT of 4000K] |
| **Beam Angle (Nom)** | 160 degree(s) |
| **Luminous Flux** | 2,100 lm |
| **Color Designation** | Cool White (CW) |
| **Correlated Color Temperature (Nom)** | 4000 K |
| **Luminous Efficacy (rated) (Nom)** | 150.00 lm/W |
| **Color Consistency** | <6 |
| **Color rendering index (CRI)** | 83 |

| | |
|---|---|
| **LLMF At End Of Nominal Lifetime (Nom)** | 70 % |

| Operating and Electrical | |
|---|---|
| **Line Frequency** | 50 to 60 Hz |
| **Input Frequency** | 50 to 60 Hz |
| **Power Consumption** | 14 W |
| **Lamp Current (Max)** | 72 mA |
| **Lamp Current (Min)** | 59 mA |
| **Starting Time (Nom)** | 0.5 s |
| **Warm-up time to 60% light** | 0.5 s |
| **Power Factor (Fraction)** | 0.9 |
| **Voltage (Nom)** | 220-240 V |

| Temperature | |
|---|---|
| **Ambient temperature range** | -20 °C to 45 °C |
| **T-Case Maximum (Nom)** | 35 °C |

# MASTER LEDtube EM/Mains T8

| Controls and Dimming | |
|---|---|
| **Dimmable** | No |

| Mechanical and Housing | |
|---|---|
| **Bulb Finish** | Frosted |
| **Bulb Material** | Plastic |
| **Product Length** | 1,200 mm |
| **Bulb Shape** | T8 |

| Approval and Application | |
|---|---|
| **Energy Saving Product** | Yes |
| **Approval Marks** | RoHS compliance |
| **Energy Consumption kWh/1000 h** | 14 kWh |

| Product Data | |
|---|---|
| **Order product name** | MAS LEDtube 1200mm HO 14W840 T8 |
| **Full product name** | MAS LEDtube 1200mm HO 14W840 T8 |
| **Full product code** | 871869668726000 |
| **Order code** | 929001299308 |
| **Material Nr. (12NC)** | 929001299308 |
| **Numerator - Quantity Per Pack** | 1 |
| **EAN/UPC - Product/Case** | 8718696687260 |
| **Numerator - Packs per outer box** | 10 |
| **EAN/UPC - Case** | 8718696687277 |

## Dimensional drawing




| Product | D1 | D2 | A1 | A2 | A3 |
|---|---|---|---|---|---|
| MAS LEDtube 1200mm HO 14W840 T8 | 25.8 mm | 28 mm | 1,198.2 mm | 1,205.3 mm | 1,212.4 mm |

## Photometric data



General uniform lighting - MAS LEDtube 1200mm HO 14W840 T8




Light Distribution Diagram - MAS LEDtube 1200mm HO 14W840 T8

# MASTER LEDtube EM/Mains T8

## Photometric data




Spectral Power Distribution Colour - MAS LEDtube 1200mm HO 14W840 T8

## Lifetime




Life Expectancy Diagram - MAS LEDtube 1200mm HO 14W840 T8




Life Expectancy Diagram - MAS LEDtube 1200mm HO 14W840 T8




Life Expectancy Diagram - MAS LEDtube 1200mm HO 14W840 T8




Lumen Maintenance Diagram - MAS LEDtube 1200mm HO 14W840 T8

# MASTER LEDtube EM/Mains T8

## Lifetime




**Lumen Maintenance Diagram - MAS LEDtube 1200mm HO 14W840 T8**

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.