


**PHILIPS**


**GreenSpace  
Accent Pendant**

**PT320P**












Model	Lumen package	Color Temperature [K]	Weight [kg]
	LED17S	827/830/840/CRW/PW930	1
PT320T	LED19S	FMT/ROSE	1
PT320C*	LED27S	827/830/840/CRW/PW930/CH/ROSE/FR/PC930	1
	LED39S	827/830/840/CH/PW930/PC930	1

Product info




\* Ceiling adapter is only available with PSU driver






LED175/827,830,840,PW930		LED175/CRW LED195/ROSE LED275/ROSE,PW930,PC930		LED275/827,830,840,CH,FR		LED395/827,830,840,CH,FR		LED195/FMT LED275/CRW LED395/PW930,PC930	
20W PSU		36W PSU		28W PSU		34W PSU		50W PSU	
I <sub>peak</sub> [A]	18.6	I <sub>peak</sub> [A]	18.6	I <sub>peak</sub> [A]	6.1	I <sub>peak</sub> [A]	11	I <sub>peak</sub> [A]	18
T <sub>ref</sub> [us]	240	T <sub>ref</sub> [us]	240	T <sub>ref</sub> [us]	310	T <sub>ref</sub> [us]	306	T <sub>ref</sub> [us]	250
MCB	Max products [pcs]*	MCB	Max products [pcs]*	MCB	Max products [pcs]*	MCB	Max products [pcs]*	MCB	Max products [pcs]*
B-16A type B	≤34	B-16A type B	≤34	B-16A type B	≤34	B-16A type B	≤34	B-16A type B	≤30
PSU									
LED175/827,830,840,CH,PW930		LED175/CRW LED195/ROSE LED275/827,830,840,CH,FR,ROSE,PW930, PC930		LED195/FMT LED275/CRW LED395/827,830,840,CH,FR,PW930,PC930					
20W PSD-VLC-E		36W PSD-VLC-E		50W PSD-VLC-E					
I <sub>peak</sub> [A]	20.4	I <sub>peak</sub> [A]	20.4	I <sub>peak</sub> [A]	24.9				
T <sub>ref</sub> [us]	195	T <sub>ref</sub> [us]	195	T <sub>ref</sub> [us]	186				
MCB	Max products [pcs]*	MCB	Max products [pcs]*	MCB	Max products [pcs]*				
B-16A type B	≤24	B-16A type B	≤24	B-16A type B	≤27				
PSD-VLC									



9 Optical unit cleaning

The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.



Only use a soft cloth!



© 2019, Signify Holding  
 All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.. All other trademarks are owned by Signify Holding or their respective owners.

Signify Holding.  
 The Netherlands