MASTER LEDspot PAR

MAS LEDspot D 6-50W E27 827 PAR20 25D

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	25,000 hour(s)
Switching Cycle	25,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	520 lm
Luminous Intensity (Nom)	1,500 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	86.67 lm/W
Color Consistency	<6
Color rendering index (CRI)	80

LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	6 W
Lamp Current (Nom)	32 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.85
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	80 °C

MASTER LEDspot PAR

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	PAR20 [PAR 2.5 inch/63mm]

Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	6 kWh

Product Data	
Order product name	MAS LEDspot D 6-50W E27 827 PAR20 25D

Full product name	MAS LEDspot D 6-50W E27 827 PAR20 25D
Full product code	871869671408900
Order code	929001317408
Material Nr. (12NC)	929001317408
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696714089
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696714096

Dimensional drawing



Product	D	C
MAS LEDspot D 6-50W E27 827 PAR20 25D	64 mm	85 mm

Photometric data



Accent Lighting Spots - MAS LEDspot D 6-50W E27 827 PAR20 25D



Spectral Power Distribution Colour - MAS LEDspot D 6-50W E27 827 PAR20 25D

MASTER LEDspot PAR

Photometric data



Light Distribution Diagram - MAS LEDspot D 6-50W E27 827 PAR20 25D

Lifetime



Life Expectancy Diagram - MAS LEDspot D 6-50W E27 827 PAR20 25D



Lumen Maintenance Diagram - MAS LEDspot D 6-50W E27 827 PAR20 25D

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.