


WHD	E	08-039	ALD	8/26/08
WHD	F	09-065	ALD	8/4/09
WHD	G	10-137-006	ARG	3/15/11
APPR	REV	ISO DOC	BY	DATE



**HOUSE SIDE**

**STREET SIDE**

**ACCESS DOOR**

**NOTES:**  
 1. (4) ANCHOR RODS:  
 SUGGESTED BOLT CIRCLE: 9 1/2" DIAMETER  
 MAXIMUM DIAMETER: 9 1/2" DIAMETER  
 MINIMUM DIAMETER: 7" DIAMETER


(3) ANCHOR RODS:  
 USE ONLY ON AN 8" DIAMETER BOLT CIRCLE.

2. PHILIPS STRONGLY RECOMMENDS USING LEVELING NUTS TO MOUNT THE POST BASE. IF FOUNDATION IS NOT LEVEL, INCREASE "X" DIMENSION ACCORDINGLY WHEN USING LEVELING NUTS WITH WASHERS.

X = 2 3/4" WITH LEVELING NUTS  
 X = 2" WITHOUT LEVELING NUTS

3. IF USING GROUTING TO CONCEAL GAP BETWEEN BASE AND FOUNDATION, ALLOW FOR WATER DRAINAGE.

**\*WARNING\***  
**NOT TO SCALE**  
**CONSULT FACTORY FOR**  
**FULL SIZE TEMPLATE.**



<b>PHILIPS</b> 100 Craftway, P.O. Box 128 Littlestown, Pennsylvania 17340-0128	CONFIDENTIAL: This drawing is confidential and proprietary to Philips and may not be reproduced in whole or in part without the express written consent of Philips. All rights reserved. © 2011 by Philips Electronics.		TITLE: TEMP.P1915	
	DRAWN BY: T.A. GOLDEN CHECKED BY: B. DORON APPR BY: E. HADDAD	DATE: 7/15/98 DATE: 8/4/09 DATE: 7/15/98	DRW SIZE: C	MATERIAL: 17 X 22 WHITE BOND PAPER,
*UNLESS OTHERWISE SPECIFIED: *ALL DIMENSIONS ARE IN INCHES. *ALL THREADS ARE UNC-2B OR UNF-2B AFTER COATING. *ALL THREADS ARE TO BE VERIFIED WITH A THREAD GAGE.	EF-04-01-11 Rev.09	SCALE 1:1	SHEET 1 OF 1	PART NO: T01700944

\* DO NOT SCALE THIS DRAWING \*

SCALE 1:7