LED PAR30 S/L

10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	25,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	40 degree(s)
Luminous Flux	800 lm
Luminous Intensity (Nom)	1,600 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	80.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	10 W
Lamp Current (Nom)	86 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	153 °F

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	PAR30L [PAR 3.75 inch/95mm Long]

Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh

Product Data	
Order product name	10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB

LED PAR30 S/L

Full product name	10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB
Order code	529735
Material Nr. (12NC)	929001322004
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	046677529734
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677529739

Dimensional drawing



Product	D	C
10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB	3-3/4 inch	4-11/16 inch

Photometric data



Light Distribution Diagram - 10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB



Accent Lighting Spots - 10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB



Spectral Power Distribution Colour - 10PAR30L/LED/827/F40/DIM/ULW/ 120V 6/1FB

LED PAR30 S/L

Lifetime



Life Expectancy Diagram - 10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB



Lumen Maintenance Diagram - 10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.