PHILIPS

Lighting

MASTER LEDtube InstantFit HF T5

Master LEDtube HF 1200mm HO 26W 830 T5

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance, which cannot be distinguished from traditional fluorescent. These T5 lighting tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings thanks to low energy consumption and an exceptionally long lifetime make these T5 LED tubes the choice for every demanding application.

Product data

General Information	
Cap-Base	G5 [G5]
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	160 degree(s)
Luminous Flux	3,700 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	142.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	83
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	35000-80000 Hz
Input Frequency	35000-80000 Hz
Power Consumption	26 W
Lamp Current (Max)	700 mA
Lamp Current (Min)	450 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	50-60 V

Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	45 °C

Controls and Dimming	
Dimmable	No

MASTER LEDtube InstantFit HF T5

Mechanical and Housing	
Bulb Material	Plastic
Product Length	1,200 mm
Bulb Shape	T5

Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance TUV CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	31 kWh

Product Data	
Order product name	MAS LEDtube HF 1200mm HO 26W 830 T5

Full product name	Master LEDtube HF 1200mm HO 26W 830 T5
Full product code	871869670527800
Order code	70527800
Material Nr. (12NC)	929001338302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696705278
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696705285

Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube HF 1200mm HO 26W 830 T5	15.2 mm	21 mm	1,147.8 mm	1,154.9 mm	1,162 mm

Photometric data



General uniform lighting - MAS LEDtube HF 1200mm HO 26W 830 T5



Light Distribution Diagram - MAS LEDtube HF 1200mm HO 26W 830 T5

MASTER LEDtube InstantFit HF T5

Photometric data

Spectral Power Distribution Colour - MAS LEDtube HF 1200mm HO 26W 830 T5

Lifetime



Life Expectancy Diagram - MAS LEDtube HF 1200mm HO 26W 830 T5

Lumen Maintenance Diagram - MAS LEDtube HF 1200mm HO 26W 830 T5



Life Expectancy Diagram - MAS LEDtube HF 1200mm HO 26W 830 T5



Life Expectancy Diagram - MAS LEDtube HF 1200mm HO 26W 830 T5

MASTER LEDtube InstantFit HF T5

Lifetime



Lumen Maintenance Diagram - MAS LEDtube HF 1200mm HO 26W 830 T5

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.