

PHILIPS

Econic Outdoor Wall Light

Hue White and color
ambiance

LED integrated


White and color light

Mains powered

Smart control with Hue bridge*



17438/30/P7



Limitless possibilities

Now expand Hue to your outdoors. The Econic wall light can be connected to your existing Hue bridge to enjoy all features e.g. away from home control and scheduling, and to create any ambiance. Hue bridge not included

Limitless possibilities

- Paint your outdoors with 16 million colors
- Unwind with warm to cool white light
- Special light for special occasions

Easy control and comfort

- Set timers for your convenience
- Control it your way
- Smart control, home and away
- Set your lights to welcome you home

Full control from smart device with Hue bridge

- Requires a Philips Hue bridge

Specially designed for your outdoors

- Weather-proof (IP44)
- High-quality aluminium and tempered glass
- High light output

Highlights

Paint your outdoors



With Philips Hue outdoor lighting there's no limit to the magic you can add. Play with 16 million colors and all shades of white light to create the effect you want. Highlight objects, trees or pathways to make your space stand out. Use the Hue app to save your favorite light settings and recall them whenever you want with the tap of a finger.

Warm to cool white light



Extend your evenings with Philips Hue outdoor lighting. Set the right ambiance on your patio, balcony or porch and relax. From the warm white light of a summer sun, to the ice cool daylight of winter: you can enjoy any shade of white light to fit your mood throughout the year.

Special light for special occasions



Holiday cheer starts here — with smart light! Use your Philips Hue lights to transform your home into a festive experience: bright reds and greens for Christmas, subtle pastels for spring, or even an eerie purple glow to create the most haunted house on the block on Halloween.

Set timers for convenience



Enjoy longer evenings outside, finish yard work or just bring the garbage outside after sunset. Have your Philips Hue lights turn on automatically by setting schedules or use sunset / sunrise routine. And of course, you can also turn off or dim your lights this way. You'll never again have to worry whether you've left any lights on.

Control it your way



Connect your Philips Hue lights with the Bridge and start discovering the endless possibilities. Control your lights from your smartphone or tablet via the Philips Hue app, or add the indoor switches to your system to change your lights. Set timers, notifications, alarms, and more for the full Philips Hue experience. Philips Hue even works with Amazon Alexa, Apple HomeKit and the Google Assistant to allow you to control your lights with your voice.

Smart control, home and away



Light up your outdoors and see what's going on outside. By connecting your outdoor lights with the Hue Bridge you can control them in any way you like. With the Philips Hue outdoor sensor, our indoor remote control options such as the Philips Hue app or using your voice (Amazon Alexa, Apple HomeKit or Google Assistant) you can control your outdoor lights. You can set light schedules to mimic your presence. Control your outdoor lighting from the comfort of your home or from any other location.

Set your lights to welcome you



Experience the comfort of your lights turning on automatically when you arrive and turning off when you leave. Unload your car, enter your house, all with the comfort of the right light. Either use the Philips Hue outdoor sensor, or set the Hue app to Home or Away mode to switch on all your lights, or let geolocation do it for you, all without touching a button. It's as easy as that.

Requires a Philips Hue bridge




Connect your Philips Hue lights with the Bridge to control your lights from your smart phone or tablet via the Philips Hue app. Or control your Philips Hue lights with the Philips Hue dimmer indoor switch for on/off and dimming functionalities.

Weather-proof (IP44)



This Philips Hue outdoor fixture is specially designed for use in outdoor environments and has undergone rigorous tests to ensure its performance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This lamp is designed with IP44: it is protected against water splashed from any direction. This product is most common and ideal for general outdoor use.

quality aluminium and glass



The products are made specifically for outdoor use. We are using high-quality aluminium and tempered glass to ensure the best performance in the outdoor conditions. As well as smart use of materials to optimize radio frequency.

High light output



This Philips Hue light provides you with enough output to light up your garden comfortably. Use this Philips Hue light to help you light up your entrances, create more ambiance and bring your outdoors to the next level by setting the scene for your moment.

Specifications

Design and finishing

- Color: Black
- Material: Glass

Extra feature/accessory incl.

- Dimmable with Hue app and switch: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Garden & Patio
- Type: Wall Lights

Product dimensions and weight

- Net weight: 2.580 kg
- Height: 11.5 cm
- Length: 26 cm
- Width: 26 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lumen output at 4000K: 1,140 lm
- Lifetime up to: 25,000 hour(s)
- Light color: 2000-6500 Hue White Color Ambiance
- Mains power: Range 220 V - 240 V, 50-60 Hz
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 1
- Wattage bulb included: 15 W
- Maximum wattage replacement bulb: 15 W
- IP code: IP44, protection from splashed water
- Class of protection: I - earthed
- Replaceability of light source: Non-Replaceable LED light source
- Replaceability of control gears: Non-Replaceable control gear
- Lumen output at 2700K: 1,040 lm

What's supported

- Compatible with Effects: Yes
- Philips Hue App: IOS 15 and above, Android 10.0 and above

Packaging dimensions and weight

- EAN/UPC - product: 8718696170564
- Net weight: 2.58 kg
- Gross weight: 3.05 kg
- Height: 355 mm
- Length: 200 mm
- Width: 345 mm
- Material number (12NC): 915005731901



Issue date: 2024-02-04
Version: 0.611

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com