

# PHILIPS

Appear Outdoor  
wall light

Hue White and color  
ambiance

LED integrated

White and color light

Mains powered

Smart control with Hue Bridge\*



17463/30/V7



## Limitless possibilities

The Appear wall light offers 16 million colors of subtle yet powerful light by directing its beams both up and down, creating a sharp, directed triangle of light against the wall of your front or back patio.

### Limitless possibilities

- Unwind with warm to cool white light
- Decorate for the holidays with light
- Come home to a house filled with light
- Unique architectural light shapes

### Easy control and comfort

- Control it your way

### Full control from smart device with Hue bridge

- Requires a Philips Hue bridge

### Specially designed for your outdoors

- Weather-proof (IP44)
- High-quality aluminum and superior synthetics

# Highlights

## Warm to cool white light



Extend your evenings with Philips Hue outdoor lighting. Set the right ambiance on your patio, balcony or porch and relax. From the warm white light of a summer sun, to the ice cool daylight of winter: you can enjoy any shade of white light to fit your mood throughout the year.

## Decorate for the holidays with light



Holiday cheer starts here — with smart light! Use your Philips Hue lights to transform your home into a festive experience: bright reds and greens for Christmas, subtle pastels for spring, or even an eerie purple glow to create the most haunted house on the block on Halloween.

## Come home with light



Set your Philips Hue app to recognize when you're nearing home. Before you even step out of your car or walk up the path, your selected smart lights turn on automatically.

## Unique architectural light shapes



Create an architectural focal point with outdoor fixtures that offer razor-sharp, triangular light effects against any wall or surface.

## Control it your way



Connect your Philips Hue lights with the Bridge and start discovering the endless possibilities. Control your lights from your smartphone or tablet via the Philips Hue app, or add the indoor switches to your system to change your lights. Set timers, notifications, alarms, and more for the full Philips Hue experience. Philips Hue even works with Amazon Alexa, Apple Homekit and the Google Assistant to allow you to control your lights with your voice.

## Requires a Philips Hue bridge




Connect your Philips Hue lights with the Bridge to control your lights from your smart phone or tablet via the Philips Hue app. Or control your Philips Hue lights with the Philips Hue dimmer indoor switch for on/off and dimming functionalities.

**Weather-proof (IP44)**

This Philips Hue outdoor fixture is specially designed for use in outdoor environments and has undergone

rigorous tests to ensure its performance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This lamp is designed with IP44: it is protected against water splashed from any direction. This product is most common and ideal for general outdoor use.

**High-quality**

The products are made specifically for outdoor use. We are using the highest quality materials to ensure the best performance in the outdoor conditions as well as smart use of materials to optimize radio frequency.

## Specifications

**Design and finishing**

- Color: Black
- Material: Metal

**Extra feature/accessory incl.**

- Bi-directional light beams: Yes
- Dimmable with Hue app and switch: Yes

**Light characteristics**

- Color rendering index (CRI): 80

**Miscellaneous**

- Especially designed for: Garden & Patio
- Type: Wall Lights

**Product dimensions and weight**

- Net weight: 2.612 lb
- Height: 9.4 inch
- Length: 4.6 inch
- Width: 4.3 inch

**Service**

- Warranty: 2 year(s)

**Technical specifications**

- Lumen output at 4000K: 1,180 lm
- Lifetime up to: 25,000 hour(s)
- Light color: 2000-6500 Hue White Color Ambiance
- Mains power: Range 100 V - 127 V, 50-60 Hz
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 2
- Wattage bulb included: 8 W
- Maximum wattage replacement bulb: 8 W
- IP code: IP44, protection from splashed water
- Class of protection: I - earthed

**What's supported**

- Compatible with Effects: Yes
- Philips Hue App: IOS 15 and above, Android 10.0 and above

**Packaging dimensions and weight**

- EAN/UPC - product: 046677803018
- Net weight: 1.19 kg
- Gross weight: 1.35 kg
- Height: 295 mm
- Length: 115 mm
- Width: 135 mm
- Material number (12NC): 915005843101



Issue date: 2024-02-02  
Version: 0.225

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)