PHILIPS

Lighting

T8

14T8/COR/48-850/MF18/G 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	850 [CCT of 5000K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	1,800 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	128.00 lm/W
Color Consistency	<5
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	14 W
Lamp Current (Max)	130 mA
Lamp Current (Min)	47 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
UL Type	Type B - bypass the ballast

Temperature	
Ambient temperature range	-4 °F to 113 °F
T-Case Maximum (Nom)	158 °F

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass

T8

Product Length	47-1/4 inch
Bulb Shape	Tube, double-ended

Approval and Application

Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate DLC compliance
Energy Consumption kWh/1000 h	- kWh

Product Data

Order product name	14T8/COR/48-850/MF18/G 10/1
Full product name	14T8/COR/48-850/MF18/G 10/1
Order code	477349
Material Nr. (12NC)	929001845734
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677477349
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677477344

Dimensional drawing



Product	D1	D2	A1	A2	A3
14T8/COR/48-850/ MF18/G 10/1	1-1/16 inch	1-1/8 inch	47-3/16 inch	47-1/2 inch	47-3/4 inch

Photometric data



General uniform lighting - 14T8/COR/48-850/MF18/G 10/1



Light Distribution Diagram - 14T8/COR/48-850/MF18/G 10/1

Photometric data



Spectral Power Distribution Colour - 14T8/COR/48-850/MF18/G 10/1

Lifetime



Life Expectancy Diagram - 14T8/COR/48-850/MF18/G 10/1



Life Expectancy Diagram - 14T8/COR/48-850/MF18/G 10/1



Life Expectancy Diagram - 14T8/COR/48-850/MF18/G 10/1



Lumen Maintenance Diagram - 14T8/COR/48-850/MF18/G 10/1

Lifetime



Lumen Maintenance Diagram - 14T8/COR/48-850/MF18/G 10/1

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.