TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

TForce HB 100-85W E40 865 120D GM

Philips TrueForce LED Industrial and Retail lamps give you a quick and easy payback solution to replace HID lamps in Highbay application. The solution gives you the LED benefits of energy-efficiency and long-lifetime, plus they come for a low initial investment. With unique lamp design and compatibility, you can directly retrofit HID lamps with TrueForce LED lamps without changing the fixtures or gear. Multiple beam angle options and high colour rendering index enhance the lighting distribution while creating a comfortable, safe and high productivity environment.

Warnings and Safety

• EM version requires an EM ballast to operate. Please refer to the installation guide or consult a Philips Lighting representative.

Product data

General Information	
Cap-Base	E40 [E40]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	120 degree(s)

Luminous Flux	10,000 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	117.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Input Frequency	50 to 60 Hz
Power Consumption	85 W
Lamp Current (Nom)	715 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	110-277 V

Temperature	
T-Case Maximum (Nom)	90 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	Others

Approval and Application	
Energy Consumption kWh/1000 h	85 kWh

Product Data	
Order product name	TForce HB 100-85W E40 865 120D GM
Full product name	TForce HB 100-85W E40 865 120D GM
Full product code	871869682660700
Order code	929001875908
Material Nr. (12NC)	929001875908
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696826607
Numerator - Packs per outer box	2
EAN/UPC - Case	8718696826614

Dimensional drawing



Product	D	C
TForce HB 100-85W E40 865 120D GM	190 mm	270 mm

Photometric data



General uniform lighting - TForce HB 100-85W E40 865 120D GM



Spectral Power Distribution Colour - TForce HB 100-85W E40 865 120D GM

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Photometric data



Light Distribution Diagram - TForce HB 100-85W E40 865 120D GM

Lifetime



Lumen Maintenance Diagram - TForce HB 100-85W E40 865 120D GM



Life Expectancy Diagram - TForce HB 100-85W E40 865 120D GM

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.