MASTER LEDtube EM/ Mains T8

MASTER LEDtube 1200mm HO VWV 18W 865 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. For those that are looking for value for money within limited budget and re-lamping efforts for better light effect and lifetime.

Warnings and Safety

- -

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	60,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	160 degree(s)
Luminous Flux	2,100 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	116.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80

LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	18 W
Lamp Current (Max)	183 mA
Lamp Current (Min)	69 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.90
Voltage (Nom)	100-277 V

Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	60 °C

MASTER LEDtube EM/Mains T8

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Product Length	1,200 mm
Bulb Shape	T8

Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance CE marking UL certificate KEMA Keur certificate
Energy Consumption kWh/1000 h	18 kWh

Product Data	
Order product name	MAS LEDtube 1200mm HO VWV 18W 865 T8
Full product name	MASTER LEDtube 1200mm HO VWV 18W 865 T8
Full product code	871869681121400
Order code	81121400
Material Nr. (12NC)	929001877412
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696811214
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696811221

Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube 1200mm HO VWV 18W 865 T8	25.8 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm

Photometric data



Light Distribution Diagram - MAS LEDtube 1200mm HO VWV 18W 865 T8



Spectral Power Distribution Colour - MAS LEDtube 1200mm HO VWV 18W 865 T8

MASTER LEDtube EM/Mains T8

Photometric data



General uniform lighting - MAS LEDtube 1200mm HO VWV 18W 865 T8

Lifetime



Life Expectancy Diagram - MAS LEDtube 1200mm HO VWV 18W 865 T8



Life Expectancy Diagram - MAS LEDtube 1200mm HO VWV 18W 865 T8



Lumen Maintenance Diagram - MAS LEDtube 1200mm HO VWV 18W 865 T8



Lumen Maintenance Diagram - MAS LEDtube 1200mm HO VWV 18W 865 T8

MASTER LEDtube EM/Mains T8

Lifetime



Life Expectancy Diagram - MAS LEDtube 1200mm HO VWV 18W 865 T8

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.