A-Shape LED

10A19/LED/850/FR/P/ND 4/2FB

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	11,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	11,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	850 [CCT of 5000K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	1,000 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	10 W
Lamp Current (Nom)	175 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	167 °F

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19 [A 19mm]

Approval and Application	
Energy Consumption kWh/1000 h	- kWh
EyeComfort	Yes

Product Data	
Order product name	10A19/LED/850/FR/P/ND 4/2FB
Full product name	10A19/LED/850/FR/P/ND 4/2FB

A-Shape LED

Order code	463000
Material Nr. (12NC)	929001958103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677463007

Numerator - Packs per outer box	4
EAN/UPC - Case	50046677463002

Dimensional drawing



Product	D	C
10A19/LED/850/FR/P/ND 4/2FB	2-3/8 inch	4-3/8 inch

Photometric data



General uniform lighting - 10A19/LED/850/FR/P/ND 4/2FB



Light Distribution Diagram - 10A19/LED/850/FR/P/ND 4/2FB



Spectral Power Distribution Colour - 10A19/LED/850/FR/P/ND 4/2FB

A-Shape LED

Lifetime



Life Expectancy Diagram - 10A19/LED/850/FR/P/ND 4/2FB



Lumen Maintenance Diagram - 10A19/LED/850/FR/P/ND 4/2FB

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.