

PHILIPS

Wall light

Linea

31098 TrunkLinea 7W 6500K

white

LED



31098/31/66



Light and relaxed

Philips myLiving Decolinea Trunk LED batten cove light is all about performance. Shadow free and connectable up to 12 pieces at a time. Available in 4 lengths and up to 15,000 hours usage, it is the ideal replacement of the T5 batten.

Easy installation

- Easy installation

Long lifespan


- Extremely long life 20,000 hours

Energy saving

- Built-in LED, as part of the system

Highlights

Easy installation



No more hassle in installation. Just fix or hang securely on the wall and plug in, now this luminaire is ready to light on.

Extremely long life



A light source you can trust. Philips LED lights offer an extremely long-life of at least 20,000 hours (which equals 20 years on basis of an average use of 3 hours / day with an amount of at least of 13,000 on/off switching cycles). It feels so comfortable to think that you won't have to worry about maintenance or lamp replacement

while having the perfect light ambiance in your home.

Integrated LED light source



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

Specifications

Design and finishing

- Color: white
- Material: synthetics

Extra feature/accessory incl.

- Diffused light effect: Yes
- LED integrated: Yes

Miscellaneous

- Especially designed for: Living- & Bedroom, Home office & Study
- Style: Contemporary
- Type: Wall light
- EyeComfort: No

Product dimensions & weight

- Height: 3.6 cm
- Length: 58.4 cm
- Net weight: 0.145 kg
- Width: 2.2 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 500 lm
- Mains power: Range 220 V - 240 V, 50-60 Hz
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 1
- Wattage bulb included: 6 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated

Packaging dimensions and weight

- EAN/UPC - product: 6947830426379
- Net weight: 0.145 kg
- Gross weight: 0.184 kg
- Height: 24.000 mm
- Length: 38.000 mm
- Width: 590.000 mm
- Material number (12NC): 915004986501



Issue date: 2023-03-07
Version: 0.442

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com