


PHILIPS

Ceiling light

WAWEL LED WHT17W
TUNABLE

white

LED



31821/31/P5



Quality lighting for a cozy home

Philips myLiving WAWEL LED ceiling light comes with integrated LED to optimize light output and uniformity. Control its brightness according to your mood with step tunable and memory functions.

Light effect

- Even light distribution

Advanced LED light

- Tunable 2700-6500K

Energy saving

- 80% energy saving, compared to traditional light sources

Highlights

Even light distribution



80% energy saving



Tunable



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year. So reduce your energy bill and start saving Now.

This lamp is tunable. You can tune it to your preferred light color; from warm white (2700K) to cool daylight (6500K).

Specifications

Design and finishing

- Color: white
- Material: plastic

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: No

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional, Living- & Bedroom
- Style: Functional
- Type: Ceiling light
- EyeComfort: No

Product dimensions & weight

- Height: 6.6 cm
- Length: 35 cm
- Net weight: 0.9 kg
- Width: 35 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Lifetime up to: 20,000 hour(s)
- Diameter: 350 mm
- Total lumen output fixture: 1600
- Light color: 2700/4000/6500
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 17
- IP code: IP20, protection against objects bigger than 12 mm, no protection against water

- Class of protection: I - earthed

Packaging dimensions and weight

- EAN/UPC - product: 8718696162774
- Net weight: 0.888 kg
- Gross weight: 1.180 kg
- Height: 400.000 mm
- Length: 69.000 mm
- Width: 395.000 mm
- Material number (12NC): 915005315604



Issue date: 2021-09-22
Version: 0.687

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com