Reflector diam 63 mm

REFL 40W E27 230V NR63 30D 1CT/30

Reflector lamps based on advanced spotlighting technology

Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Beam Angle (Nom)	30 degree(s)
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	NR63 [NR 63mm]

Product Data	
Order product name	Refl 40W E27 230V NR63 30D 1CT/30
Full product name	REFL 40W E27 230V NR63 30D 1CT/30
Full product code	871150004360378
Order code	250837
Material Nr. (12NC)	926000006213
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500043603
Numerator - Packs per outer box	30
EAN/UPC - Case	8711500343956

Reflector diam 63 mm

Dimensional drawing



Product	D
Refl 40W E27 230V NR63 30D 1CT/30	2-1/2 inch

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.