TL-X XL

TL-X XL 20W/33-640 SLV/25

Single-pin low-pressure mercury discharge lamps with a tubular 38 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	FA6
Flux measurement reference	Sphere
Life to 50% failures (nom.)	26,000 h

Light Technical	
Colour Code	33-640
Luminous Flux	940 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	47 lm/W
Colour rendering index (CRI)	60

Operating and Electrical	
Power Consumption	20.0 W
Lamp current (nom.)	0.380 A
Voltage (nom.)	58 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb shape	T12
Net Weight (Piece)	124.000 g

Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	12 mg
Mercury (Hg) content (nom.)	12.0 mg
Energy consumption kWh/1,000 hours	20 kWh
EPREL Registration Number	423514
CE mark	Yes

Product Data	
Order product name	TL-X XL 20W/33-640 SLV/25
Full product name	TL-X XL 20W/33-640 SLV/25
Full EOC	871150026135940
Order code	928037703332
Material no. (12 NC)	928037703332

TL-X XL

Local order code	TLX2033XL
Numerator – quantity per pack	1
EAN/UPC — Product/Case	8711500261359
Numerator – packs per outer box	25

EAN/UPC - Case	8711500261366

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-X XL 20W/33-640 SLV/25	40.5 mm	574 mm	592.5 mm	589 mm	611 mm

Photometric data



Spectral Power Distribution Colour - TL-X XL 20W/33-640 SLV/25

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.