SON-T

SON-T 1000W E40 1SL/4

High Pressure Sodium lamp with clear tubular outer bulb

Warnings and Safety

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	E40
Operating position	UNIVERSAL [Any or Universal (U)]
Life to 50% failures (nom.)	20,000 h

Light Technical	
Colour Code	220 [CCT of 2000K]
Correlated Colour Temperature (Nom)	2000 K
Luminous efficacy (rated) (nom.)	130 lm/W
Colour rendering index (CRI)	-
Arc Length O (Nom)	153 mm

Operating and Electrical	
Power Consumption	960.0 W
Voltage (nom.)	100 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T65
Net Weight (Piece)	414.000 g

Approval and Application	
Mercury (Hg) content (nom.)	23 mg
Energy consumption kWh/1,000 hours	1,056 kWh
CE mark	Yes

Product Data	
Order product name	SON-T 1000W E40 1SL/4
Full product name	SON-T 1000W E40 1SL/4
Full EOC	871150018412245
Order code	928154509228
Material no. (12 NC)	928154509228
Local order code	1000SONT
Numerator – quantity per pack	1
EAN/UPC — Product/Case	8711500184122
Numerator – packs per outer box	4

SON-T

EAN/UPC - Case	8711500184139

Dimensional drawing



Product	D (max)	O	L	C (max)
SON-T 1000W E40 1SL/4	66 mm	153 mm	240 mm	390 mm

Photometric data



Light Distribution Diagram - SON-T 1000W E40 1SL/4



Spectral Power Distribution Colour - SON-T 1000W E40 1SL/4

Lifetime



LDLE_SON-T_1000W-Life expectancy diagram



Lumen Maintenance Diagram - SON-T 1000W E40 1SL/4

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.